

## NT 35/1 Tact Te

Multi-purpose wet & dry vacuum cleaner with power tool take-off and Tact automatic filter clean system for heavy duty dust extraction.

### Equipment:

- Suction hose 2.5 m
- Filter bag Paper
- Wet and dry floor tool 300 mm
- Crevice tool
- Connector for electric tools
- Auto shutdown when max. level is reached
- Automatic on/off control for electric power tools
- Antistatic system
- Eco filter system
- Flat pleated filter Paper
- Bend
- Safety class I
- Caster with brake
- Filter cleaning Tact Filter Clean
- Maintenance -free suction fans  
1 piece(s)



**Order no.: 1.184-859.0**

### Technical data

Air flow rate (l/s)	74
Vacuum (mbar/kPa)	254/25
Container capacity (l)	35
Max. intake performance (W)	1380
Standard nominal size (mm)	35
Length of cord access.	-
Sound level (db(A))	67
Container material	
Quantity of motors	1
Frequency (Hz)	50-60
Voltage (V)	220-240
Weight (kg)	12.5
Dimensions (L x W x H) (mm)	520x380x580

## Details

### Description

The NT 35/1 Tact Te is a tough, high performance vacuum cleaner capable of removing wet or dry dirt very quickly. With Kärcher's unique TACT automatic filter clean system as standard, the NT 35/1 is designed for continuous removal of even very fine dust without blocking up the filter, minimising downtime and therefore increasing productivity. The NT 35/1 Tact Te features a power tool take-off socket with automatic power tool on/off function which enables the vacuum to be switched on and off through the power tool – saving energy, reducing noise, and ensuring that dust made by power tools goes straight into the NT 35/1. The perfect machine for trade, crafts, industry, and anywhere else that portable, high performance dust control is required.

---

### Features & Benefits

Tact system (Auto Filter Clean System)

The filter cleans itself with powerful blasts of air. This automatic process guarantees constantly high suction power. Further benefits: low maintenance costs, long filter service life.

On-board practical storage

Large on-board storage area for tool and accessory storage.

---

## Accessories

### Adapter (tube -> nozzle)

#### Adapter ID 35 - 40 (tube -> nozzle)

From DN 35 to DN 40: Plastic adapter (electrically non-conductive). Suitable for NT vacuum cleaners.

Order no. 6.902-084.0



### Adapter for electric power tools, clip on, el.

#### Power tool adapter C 35, el.

3-way plastic adapter. For DN 26 to DN 36. For connecting power tools to an industrial C or C-DN 35 suction hose. Suitable for NT vacuum cleaners.

Order no. 5.453-042.0



#### Adapter for electric power tools, C 35, el.

Inner Ø 25.4 mm, outer Ø 34.6 mm/ 38 mm, el. Only NT-vacuums.

Order no. 5.453-048.0



#### Connecting sleeve for electric tool C 35, el.

Inner Ø 28.6 mm, outer Ø 37.3 mm/ 38.8 mm, el. Only NT-vacuums.

Order no. 5.453-049.0



#### Adapter for electric power tools, C 35, el.

Inner Ø 27 mm, outer Ø 36.5 mm/ 38.8 mm, el. Only NT-vacuums.

Order no. 5.453-050.0



#### Connecting sleeve for electric tool C 35, el.

Inner Ø 32 mm, outer Ø 39 mm, el. Only NT-vacuums.

Order no. 5.453-051.0



#### Connecting sleeve for electric tools C 35, el.

Inner Ø 28 mm, outer Ø 34 mm/ 38.8 mm, el. Only NT-vacuums.

Order no. 5.453-052.0



### Adapter for electric power tools, screwable

#### Power tool adapter, threaded, DN 35

3-way plastic adapter with fitting instructions. For DN 26 to DN 36. For connecting to an industrial DN 35 suction hose.

Order no. 5.453-016.0



## Adapter for electric power tools, screwable

### Adapter for electric power tools, screwable, ID 35

Inner Ø 28.6 mm, outer Ø 37.3/38.8 mm.

Order no. 5.453-026.0



### Power tool adapter, threaded, DN 35

Electrically conductive power tool adapter, threaded. Internal diameter: 32 mm. External diameter: 39 mm.

Order no. 6.902-059.0



### Power tool adapter, threaded, DN 35

2-way power tool adapter, threaded. For connecting to an industrial DN 35 suction hose. Internal diameter: 28 mm. External diameter: 34 mm and 38.8 mm. Suitable for NT vacuum cleaners.

Order no. 6.902-095.0



## All-purpose brushes

### All-purpose brush

Natural bristles (ox hair), bristle element 120 x 45 mm.

Order no. 6.903-863.0



## All-purpose nozzles (wet/dry)

### Wet and dry floor tool

All-purpose plastic nozzle (DN 35) with 300 mm working width. With side rollers, brush strips (6.903-278.0) and squeegees (6.903-277.0). Only for NT vacuum cleaners.

Order no. 6.906-512.0



### All-purpose nozzle (wet/dry)

All-purpose aluminium nozzle with 370 mm working width. With height-adjustable side rollers, brush strips (6.903-064.0) and oil-resistant squeegees (6.903-081.0). Only for NT vacuum cleaners.

Order no. 6.903-018.0



### All-purpose nozzle (wet/dry)

All-purpose aluminium nozzle (DN 40) with 450 mm working width. With height-adjustable side rollers, brush strips (6.903-065.0) and oil-resistant squeegees (6.906-146.0). Only for NT vacuum cleaners.

Order no. 6.906-383.0



### All-purpose nozzle (wet and dry), DN 35

All-purpose aluminium nozzle (DN 35) with 370 mm working width. With height-adjustable side rollers, brush strips (6.903-064.0) and oil-resistant squeegees (6.903-081.0). Only for NT vacuum cleaners.

Order no. 6.906-384.0



## All-purpose nozzles (wet/dry)

### All-purpose nozzle (wet/dry)

All-purpose plastic nozzle (DN 35) with 360 mm working width. With side rollers, brush strips (6.905-878.0) and squeegees (6.905-877.0). Only for NT vacuum cleaners.



Order no. 6.906-513.0

### All-purpose nozzle (wet/dry)

All-purpose plastic nozzle (DN 40) with 360 mm working width. With side rollers, brush strips (6.905-878.0) and squeegees (6.905-877.0). Only for NT vacuum cleaners.



Order no. 6.906-554.0

## Bend metal

### Bend, DN 35, metal

Robust, chromium-plated metal bend (DN 35), can be used instead of a plastic bend (with clip system adapter 5.407-112.0; C 35-DN 35, plastic, el.).



Order no. 6.900-519.0

### Bend, DN 40, metal

Robust, chromium-plated metal bend (DN 40), can be used instead of a plastic bend (with clip system adapter 5.407-111.0; C 40-DN 40, plastic, el.).



Order no. 6.900-276.0

## Bend stainless

### Bend, stainless steel ID 35

Stainless steel and crooked, ID 35



Order no. 6.903-141.0

### Bend, stainless steel ID 40

Stainless steel and crooked, ID 40



Order no. 6.902-079.0

## Coarse filter for wet pickup

### Coarse dirt filter for wet pick up

Coarse dirt filter with perforated metal plate and foam seal suitable for wet pick up - NT 611 Eco K KF models.



Order no. 6.904-287.0

## Combi-nozzles (dry)

### Combination floor tool (dry)

Combination floor tool with changeover function, plastic (272 mm). With stainless steel base plate, thread catcher 6.905-417.0 and DN 35 connection.



Order no. 6.906-511.0

## Connecting sleeve C-DN (clip on taper), EL (electroconductive)

### C-ID 35 adapter

Connects C 35 hose for ID 35, electrically conductive.



Order no. 5.407-112.0

## Connecting sleeve C-DN (clip on taper), EL (electroconductive)

### C 40 adapter

Electrically conductive adapter (C 40) with DN 35 connection for connecting DN 35 accessories to an industrial C 40 or C-DN 40 suction hose. Suitable for NT vacuum cleaners.



Order no. 5.407-109.0

### C-DN 40 adapter

Connects C 40 hose for ID 40, electrically conductive.

Order no. 5.407-111.0



## Connecting sleeves

### Adapter, DN 32/35, with internal thread

Electrically non-conductive adapter with internal thread. For connecting two suction hoses without connectors. Suitable for DN 32 or DN 35.



Order no. 6.902-077.0

### Adapter, DN 40 with internal thread

Electrically non-conductive adapter with screw thread at both ends. For connecting 2 DN 40 suction hoses without connectors.



Order no. 6.900-286.0

### Connecting sleeve, ID 61, with female thread

For connecting 2 suction hoses, thread on both sides

Order no. 6.902-078.0



## Crevice nozzles

### Crevice tool

Plastic crevice tool (DN 35) for vacuuming in crevices and corners. Length: 210 mm.

Order no. 6.900-385.0



### Crevice tool

Plastic crevice tool (DN 35) for vacuuming in crevices and corners. Length: 370 mm.

Order no. 6.900-922.0



### Crevice tool

Plastic crevice tool (DN 40) for vacuuming in crevices and corners. Length: 290 mm.

Order no. 6.903-033.0



### Crevice tool

Metal crevice tool (DN 40) for vacuuming in crevices and corners. Length: 400 mm.

Order no. 6.905-817.0



### Crevice tool ID 35.

Plastic crevice tool (DN 35) for vacuuming in crevices and corners. Length: 250 mm.

Order no. 6.906-240.0



## Extension hoses (Clip-system)

### Extension hose, C 32, C 35 clip system

Electrically non-conductive standard extension hose for all C-32 and C-35 hoses with clip system.

Order no. 6.906-237.0



### Extension hose C 32-, C 35-Clip-system, el.

for all C-32 and C-35 hoses, electrically conductive.

Order no. 6.906-277.0



## Flat pleated filter (paper)

### Flat pleated filter packed - dust class M

Paper flat pleated filter (dust class M) suitable for NT 361, NT 561, NT 611 Eco/Te/M and NT 35/1, NT 45/1, NT 55/1 Eco/Eco Te/Eco M.

Order no. 6.904-367.0



## Flat pleated filter (PES)

### Flat pleated filter (PES)

Flat pleated filter (PES) – BIA-C dust class M: rotproof polyester fleece, ideal for wet use and abrasives. Standard for NT 35/1 Eco BS and NT 55/1 Eco BS.

Order no. 6.904-360.0



## Fleece filter bags (3 ply)

### Fleece filter bags, x 5

3-ply tear-resistant fleece filter bags (dust class M). For dry pick up, suitable for the following models: NT 361 Eco, Eco TE, TE-A and NT 361 Eco M, NT 35/1 Eco, Eco Te, Eco M. Contents: x5

Order no. 6.904-351.0



## HEPA filter for dust class H

### HEPA surface filter

HEPA surface filter - dust class H (H 14) - with glass-fibre layers increases filter capacity when vacuuming health-endangering and carcinogenic dust.

Order no. 6.904-242.0



## Inaktiv

### Auto kit

Component parts of kit: 4m suction hose (4.440-263) - car cleaning tool (6.900-952) - upholstery tool ID 35 (6.900-233) - reducer ID 40/35 (6.902-017)

Order no. 2.637-443.0



## Membrane filter / fabric filter

### Membrane filter/fabric filter

Polyester needle fleece membrane/fabric filter, washable up to 40°C, suitable for all NT 361 Eco to NT 611 Eco versions as an alternative to a filter bag.

Order no. 6.904-212.0



## Miscellaneous

### Extension cable

Extension cable, 20 m, 3x1.5 mm<sup>2</sup>. With splash-proof earthing pin plug, strain relief and anti-kink sleeve.



**Order no. 6.647-022.0**

## Nozzle sets

### Nozzle kit

Nozzle kit for all NT vacuum cleaners with DN 35 accessories includes crevice tool, upholstery tool, round brush (x3)



**Order no. 2.860-116.0**

## Other nozzles

### 45° rubber suction nozzle

Angled 45°, for suction of machines, oil-resistant



**Order no. 6.902-106.0**

## Paper filter (2 ply)

### Paper filter bags, x 5

5 paper filter bags. BIA-(U, S, G, C) dust class M. For all NT 361 Eco models (except Eco H).



**Order no. 6.904-210.0**

### Paper filter bags, 300 pcs

BIA-C dust class M approved. Large-scale consumer pack.



**Order no. 6.904-224.0**

### Paper filter bags

5 paper filter bags (BIA-C dust class M) with reinforced outer ply (e.g. cement dust). For all NT 361 Eco models (except Eco H).



**Order no. 6.904-259.0**

## Pipe dusting nozzles

### Pipe dusting nozzle, ID 35

Plastic, pipe diameter 100 mm



**Order no. 6.903-035.0**

### Pipe dusting nozzle

Plastic, pipe diameter 200 mm



**Order no. 6.903-036.0**

## Plastic bend

### Plastic bend

Plastic bend (DN 35) with C-35 clip system. For all industrial single-motor NT 361 to NT 611 Eco models (except NT Eco M and NT Eco H).



**Order no. 5.031-718.0**



## Plastic bend

### Plastic bend

Electrically conductive plastic bend (DN 35) with C-35 clip system. For all industrial single-motor NT 361 to NT 611 Eco models.

**Order no. 5.031-939.0**



### Plastic bend

Electrically conductive plastic bend (DN 40) with C-40 clip system, suitable for all NT vacuum cleaners.

**Order no. 5.032-427.0**



### Plastic bend

Plastic bend (DN 40) with C-40 clip system, suitable for all NT models.

**Order no. 5.031-904.0**



## Plastic sacks for dust-free disposal

### Plastic sacks for dust-free disposal

PE plastic sack.

**Order no. 6.596-886.0**



## Reducer (tube -> nozzle)

### Reducer

Reducer for accessory extension. Ideal for accessories with DN 35 connecting cone in combination with accessories with DN 40 connecting cone.

**Order no. 6.902-017.0**



### Reducer from ID 35 to 32

Reducer with internal connecting cone DN 32. Ideal for accessories from the industrial vacuum cleaner range in combination with industrial NT vacuum cleaners.

**Order no. 6.902-072.0**



## Reducing sleeves

### Reducer

Threaded reducer - from C-40 to DN 35. Suitable for NT vacuum cleaners.

**Order no. 5.407-108.0**



## Repair kits

### Repair set, C 35

Repair set (C35) includes threaded hose adapters (without bayonet adapter) for industrial NT vacuum cleaners with clip system.

**Order no. 2.639-682.0**



## Rubber suction tools, nose 45°

### Rubber suction tools, nose 45°

45° rubber suction nozzle (DN 35), oil-resistant and suitable for vacuuming machines. Only for NT vacuum cleaners.

**Order no. 6.902-104.0**



## Rubber suction tools, nose 45°

### Rubber suction tools, nose 45°

45° rubber suction nozzle (DN 40), oil-resistant and suitable for vacuuming machines. Only for NT vacuum cleaners.




Order no. 6.902-105.0

## Rubber tool

### Rubber nozzle, ID 40

Rubber.

Order no. 4.763-057.0



## Set reducing / extension sleeves

### Set reducing / extension sleeves

ID 40/35, ID 35/32 (tube -> nozzle), plastic.

Order no. 2.860-117.0



## Special filter bags, wet filter bags

### Special filter bag, wet filter bag

Approved for dust class L, general cleaning, wet and dry, tear-resistant.

Order no. 6.904-171.0



## Suction brushes

### Suction brush

Rotatable suction brush (DN 35) with natural bristles (cow hair). Bristle size 70x45 mm. Only CV and NT vacuum cleaners.

Order no. 6.903-862.0



## Suction hoses (Clip-system)

### Suction hose

4 m suction hose without bend and adapter. With bayonet at vacuum end and C 35 clip connection at accessory end.

Order no. 6.906-241.0



### Suction hose

2.5 m electrically conductive suction hose without bend and adapter with bayonet at vacuum end and C 35 clip connection at accessory end.

Order no. 6.906-275.0



### Suction hose (clip system), C 35, el.

4 m electrically conductive suction hose without bend and adapter with bayonet at vacuum end and C 35 clip connection at accessory end.

Order no. 6.906-500.0



### Suction hose

4 m suction hose with bayonet and C 40 clip connection. Without bend and adapter.

Order no. 6.906-321.0



### Suction hose

With bayonet and clip connection.

Order no. 6.906-714.0



## Suction hoses (Clip-system)

### Suction hose

Electrically conductive, 4 m suction hose with bayonet and C 40 clip connection. Without bend and adapter.



Order no. 6.906-546.0

### Suction hose (clip system), C 40, 10 m, el.

Suction hose with bayonet coupling, electrically conductive.



Order no. 6.906-877.0

### Suction hose (clip system), C 35

Electrically conductive, 10 m suction hose with bayonet and C 40 clip connection. Without bend and adapter.



Order no. 6.906-242.0

## Suction hoses complete

### Suction hose complete, ID 35, 2,5m

Temperature-resistant to 120 °C.



Order no. 4.440-339.0

### Suction hose, complete

Electrically non-conductive suction hose (3.5 m) with DN 27 adapter for power tools at accessory end and DN 27 bayonet at vacuum end. Connectors available on request.



Order no. 4.440-446.0

### Suction hose, complete

Electrically non-conductive suction hose (7 m) with DN 27 power tool adapter at accessory end and DN 27 bayonet at vacuum end. Connectors available on request.



Order no. 4.440-461.0

## Suction hoses complete (Clip-system)

### Suction hose

2.5 m standard suction hose with bend, bayonet at vacuum end and C 35 clip connection at accessory end. Without PDFC module. Standard for NT 27/1/Me Advance und NT 48/1.



Order no. 4.440-626.0

### Suction hose

2.5 m electrically conductive suction hose with bend, bayonet at vacuum end and C 35 clip connection at accessory end. Without module.



Order no. 4.440-653.0

## Suction tubes metal

### Suction tube

Chromium-plated metal suction tube (DN 35, 1x0.5 m), standard for virtually all single-motor industrial NT vacuum cleaners.

Order no. 6.900-514.0



## Suction tubes metal

### Suction tube

Chromium-plated metal suction tube (DN 40, 1x0.5 m), standard for virtually all two-motor industrial vacuum cleaners. Optional for industrial single-motor NT vacuum cleaners with DN 40 suction hose.



Order no. 6.900-275.0

## Suction tubes plastic

### Suction tube, DN 35

Plastic suction tube (DN 35, 1x0.5 m) only suitable for BV and T vacuum cleaners.



Order no. 6.900-384.0

## Suction tubes stainless steel

### Suction tube, ID 40

Stainless steel suction tube (DN 40, 0.5 m) only suitable for NT vacuum cleaners.



Order no. 6.902-081.0

### Suction tube

Stainless steel suction tube (DN 40, 1.0 m) only suitable for NT vacuum cleaners.



Order no. 6.906-531.0

### Suction tube, DN 35

Order no. 6.902-154.0



## Target group specific vacuum cleaner accessory sets

### Universal kit for industrial and commercial use

Accessory kit for industrial and commercial use.



Order no. 2.637-595.0

### Boiler cleaning kit

Accessory kit for vacuuming and cleaning boilers, oil stoves, etc.



Order no. 2.638-852.0

### Building trade kit

Building and ancillary trade accessory kit.



Order no. 2.637-352.0

### Professional cleaning kit ID 40

Individual parts: Suction hose 4 m (4.440-263.0), bend, metal (6.900-276.0), suction tube 2 x 0.5 m, metal (6.900-275.0), grout nozzle (6.903-033.0), floor nozzle with rollers (6.903-051.0).



Order no. 2.637-353.0

### Electrician's/ plumber's kit ID 35

Individual parts: suction hose 0.45 m (6.906-213.0), connection for electric tools (6.902-095.0), stepped sleeve (5.453-037.0), cable clip 5-pack (5.332-440.0)



Order no. 2.639-483.0

## Target group specific vacuum cleaner accessory sets

### Car cleaning kit

Contains: - Car cleaning nozzle ID 35 - Upholstery/crevice tool ID 35 - Suction brush ID 35 - Connecting sleeve C 35/ ID 35

Order no. 2.862-166.0



### Horse grooming kit, ID 35

Horse brush (6.903-046.0), curry comb/rubber curry comb (6.903-047.0 and 6.903-048.0), suction hose 4 m (4.440-391.0).

Order no. 2.637-248.0



### NT vacuum cleaner kit, DN 40, el.

Wet and dry vacuum cleaner kit, electrically conductive, DN 40.

Order no. 2.638-147.0



### Accessory set grinding ID 27, el.

Contains: - Suction hose with bajonett - Connectors for electric tools - Connection sleeve ID 27/35

Order no. 2.862-167.0



## Turbo nozzle

### Turbo nozzle

Plastic turbo upholstery nozzle (DN 35/32, 160 mm) with reduction sleeve.

Order no. 2.860-113.0



### Turbo nozzle, DN 32

Plastic turbo floor nozzle (DN 35/32, 270 mm) with reduction sleeve.

Order no. 2.860-114.0



## UBS non-conductive media

### ABS non-conductive media

For switching off when vacuuming non-conductive fluids such as oils and greases.

Order no. 2.641-560.0



## Y-adapter kit

### Y-adapter kit

Plastic distributor - suitable for NT vacuum cleaners.

**Order no. 2.637-217.0**

