



Part Number : [732870315](#)

Product Description : 2.92mm Attenuator, Plug to Jack, Straight, 40 GHz, 0.5 Watt, 10 dB, with Hex

Series Number : 73287

Status : Active

Product Category : RF / Coaxial Connectors



Documents & Resources

Drawings

[732870315_sd.pdf](#)

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Reviewed per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2025)4165-DC (25 June 2025)
EU RoHS	Not Reviewed per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	RF / Coaxial Connectors
Series	73287
Description	2.92mm Attenuator, Plug to Jack, Straight, 40 GHz, 0.5 Watt, 10 dB, with Hex
Application	RF
Keyword	Attenuators, Attenuator
Product Name	2.92mm,Attenuator
Style	Fixed Coaxial Attenuator
Type	Subminiature
UPC	198282631637

Electrical

Average Power Max (Watts)	0.5
Attenuation Level (dB)	10
Frequency	40 GHz
Impedance	50Ω
VSWR (max)	1.40:1

Physical

Body Style	With Hex
Cable Attachment	N/A
Gender	Plug/Jack
Keying to Mating Part	N/A
Orientation	Straight
Packaging Type	Bag
Panel Mount	No

Panel Mount Method	N/A
PCB Mounting	N/A
Reverse Polar	No
Wire/Cable Type	N/A

This document was generated on Oct 02, 2025