



ENGLISH

Datasheet

Stock No: 534-654

# RS Pro Insulated Crimp Blade Terminal 18.1mm Blade Length, 16 → 14 AWG, Blue



## Product Details

### RS Insulated Crimp Blade Terminals

A range of insulated crimp blade terminals made from copper with flared vinyl insulation. These insulated crimp blade wire connectors are colour coded for use with different wire sizes.

Red 0.5 - 1.5 mm<sup>2</sup>

Blue 1.5 - 2.5 mm<sup>2</sup>

Yellow 2.5 - 6.5 mm<sup>2</sup>

### RS Pro Range

Conversion table	
M3 / 6 BA	M5/ 2BA
M3.5/ 4BA	M6/ 0BA
M4/ 3BA	

Wire Sizes	
Mini Yellow	0.2 - 0.5 mm <sup>2</sup>
Red	0.5 - 1.5 mm <sup>2</sup>
Blue	1.5 - 2.5 mm <sup>2</sup>
Yellow	2.5 - 6.5 mm <sup>2</sup>

Technical Specification	
Temperature rating	+70°C
Body Material	Copper
Body Plating	Tin



ENGLISH

## Specifications:

Gender	Male
Wire Size	16 → 14 AWG
Insulation	Insulated
Shrouded	Unshrouded
Insulation Material	Vinyl
Colour	Blue
Overall Length	28mm
Inner Diameter	4.8mm
Blade Length	18.1mm
Blade Width	2.5mm
Contact Material	Copper
Contact Plating	Tin