



mecalelectro

Solenoid Latching – 8.MB0.AA.29



Stroke: 9 mm

Force at beginning of stroke (FM: 100/40//25/5%): 0.25/0.5/0.6/0.9 N

Holding force power off: 3.5 N

Power Consumption (FM: 100/40/25/5%): 5/10/15/20 W

Total mass: 20 g

Degree of protection / Energetic class: IP 40 / B

Standard supplies: 24Vcc

Possibles supplies: From 3 to 24Vcc

Pulse duration: 50 à 100

Standard: NF C 79300

Examples of applications: various automations, multiple locks