

- ▶ Exclusive Magnetic Levitation (MagLev™) Technology
- ▶ Revolutionary Patented VAPO Bearing
- ▶ Over 1,000 Patents in 23 Countries
- ▶ Smallest and Thinnest Brushless DC Fan Motor in the World



Low Power MagLev® Series (Green Motor)

Stock No.	Mfr.'s Type	Dimensions (mm)	Voltage (VDC)	Current (Amps)	Power (Watts)	Airflow (CFM)	Static Pressure (Inches H ₂ O)	Noise Level (dBA)	Type of Bearing
191-856	GM0517PDV1-8.GN	17 × 17 × 08	5	0.16	0.8	0.9	0.28	25.0	Vapo
	GM0502PEV1-8.N.GN	20 × 20 × 06	5	0.11	0.6	3.0	0.22	31.0	Vapo
191-913	GM0501PFV1-8.N.GN	20 × 20 × 10	5	0.21	1.1	1.9	0.29	25.0	Vapo
	GM0502PFV2-8.GN	25 × 25 × 10	5	0.08	0.4	3.0	0.18	16.0	Vapo
191-862	GM0502PFV1-8.GN	25 × 25 × 10	5	0.12	0.6	3.5	0.25	23.0	Vapo
	GM0503PFV2-8.GN	30 × 30 × 10	5	0.10	0.5	4.6	0.12	20.0	Vapo
191-705	GM0503PFV1-8.GN	30 × 30 × 10	5	0.14	0.7	5.5	0.15	23.0	Vapo
	GM1203PFV2-8.GN	30 × 30 × 10	12	0.04	0.5	4.6	0.12	20.0	Vapo
191-626	GM0535PFV2-8.GN	35 × 35 × 10	5	0.10	0.5	6.5	0.12	22.0	Vapo
	GM0535PFV1-8.GN	35 × 35 × 10	5	0.15	0.8	7.0	0.18	28.0	Vapo
	GM1235PFV1-8.GN	35 × 35 × 10	12	0.08	1.0	7.0	0.18	28.0	Vapo
	GM0503PFV2-8.N.GN	30 × 30 × 06	5	0.08	0.4	3.7	0.09	24.0	Vapo
	GM0503PEV1-8.N.GN	30 × 30 × 06	5	0.13	0.7	4.9	0.14	28.0	Vapo
	GM0504PEV2-8.GN	40 × 40 × 06	5	0.07	0.4	5.5	0.08	26.0	Vapo
	GM0504PEV1-8.GN	40 × 40 × 06	5	0.09	0.5	5.9	0.10	32.0	Vapo



Supplier: RS Components Ltd,
Birchington Road,
Corby,
Northants,
NN17 9RS.

Tel: +44 (0) 1536 402888
Fax: +44 (0) 1536 401588