

## DATASHEET

SOFT TINNED COPPER WIRE TO BSEN13602

RS Stock No 390555



DIAMETER : 0.345MM

TOLERANCE : +/- 0.004MM

ELONGATION: 20% MINIMUM

RESISTANCE : 188.1 OHMS/KM STANDARD RESISTANCE @ 20 DEG C.

YIELD : 0.20 kg/256 m

TENSILE : N/A

SURFACE FINISH: THE WIRE SHALL BE BRIGHT, CLEAN & FREE FROM HARMFUL DEFECTS.

COMPLIANCE : THE MATERIAL IS RoHS COMPLIANT

REELS : 0.20KG REELS