



Product data sheet

Power tools for trade & industry

Cordless Impact Wrench

GDS 18V-300 Professional



GBP 231.76*

* Price including VAT

Brushless impact wrench with strong 300 Nm of fastening torque

Part number: 0 601 9D8 200

[> More product information](#)

Technical Data

webshop-pdp-section-technical-data-table-key-
Technical data

No-load speed	0-2,400 rpm
Torque, max.	300 Nm
Impact rate	0-3,400 bpm
Tool holder	1/2" external square friction ring + pin hole

webshop-pdp-section-technical-data-table-key-
Size and weight

Weight excl. battery	1.3 kg
----------------------	--------

webshop-pdp-section-technical-data-table-key-
Battery and power

Battery voltage	18 V
-----------------	------

Noise/vibration information

Tightening screws and nuts of maximum permitted size

Vibration emission value ah	18,0 m/s ²
Uncertainty K	1,5 m/s ²



Product data sheet

Power tools for trade & industry

Advantages

- High fastening torque (up to 300 Nm), compact, lightweight, cordless: power and flexibility for great results
- Brushless motor guarantees high power, high runtimes, and a long tool lifetime
- Auto Bolt Release (ABR) shuts the tool off automatically in reverse mode to prevent nut runoff

