

ENGLISH

Datasheet

RS Pro Natural Nylon Screw Mount Cable Tie, 317.2mm x 7.8 mm RS Stock No: 601-108



Product Details

RS Pro nylon 66 screw mount cable tie in natural colour, measures 317.2 x 7.8 mm. It comes with a screw mounting hole and is suitable for binding cable or components and securing them in position. The cable tie can be secured to panel with a single bolt.

Features and Benefits

- Non-releasable
- Flammability rating UL94V-2
- Screw mount cable tie



ENGLISH

Specifications:

Colour	Natural
Fire Behaviour	Flame Retardant
Length	317.2 mm
Material	Nylon 66
Maximum Bundle Diameter	80 mm
Maximum Operating Temperature	+85°C
Minimum Operating Temperature	-40°C
Operating Temperature Range	-40 to +85°C
Product Name	Cable Tie
Quantity	100
Standards Met	UL 94 V-2, cURus, ABS, DNV, RoHS Compliant
Tensile Strength	539 N
Туре	Screw Mount
Width	7.8 mm