

NSYPLM54TG

wall-mounting enclosure polyester monobloc IP66
H530xW430xD200mm glazed door



Main

Range	Thalassa
Product name	Thalassa PLM
Device short name	PLM
Device application	Multi-purpose
Product or component type	Compact enclosure
Enclosure nominal height	530 mm
Enclosure nominal width	430 mm
Enclosure nominal depth	200 mm
Enclosure mounting	Wall mounted
Device composition	Lock 2 Door 1 Body 1
Body type	One piece moulded with notches in the rear Built-in canopy
Door type	Transparent
Lock type	3 mm double-bar lock

Complementary

Number of locks	2
Mounting plate description	Without mounting plate
Accessibility for operation	Front
Removable parts	Door by hinges
Material	Polyester reinforced with fibreglass body Tempered glass door
Colour	Grey RAL 7035
Standards	IEC 62208 NEMA classification 13 NEMA classification 4X
Product certifications	UL

Environment

IP degree of protection	IP66 IEC 60529
IK degree of protection	IK08 IEC 62262
fire resistance	960 °C IEC 62208
ambient air temperature for storage	-35...90 °C

Offer Sustainability

Sustainable offer status	Not Green Premium product
RoHS (date code: YYWW)	Compliant - since 1511 - Schneider Electric declaration of conformity

Contractual warranty

Warranty period	18 months
-----------------	-----------