

900 20

Lamp LED Li-MH USB charging connection

Code	ETIM
3108678	EC001959
EAN	UNSPSC
4010886954683	39-11-17-02
Country of origin	eCl@ss
Taiwan	27-11-90-01
Customs tariff number	
94054231	



Article description

- Versatile deployable LED/UV lamp of a slim design with extra functions
- In particular for the automotive and industrial fields but also for a variety of uses in leisure-time pursuits
- Continuously dimmable and switchable in blue-violet from LED to UV light (for tracking leaks in air-conditioners and heat pumps).
- Swing-out hooks on both sides, strong magnet at the 45° adjustable foot and strong tip mini-magnet for bringing up lost incidental parts where space is at a premium
- Charging either via the supplied power pack or a USB interface
- 620 lumen

Article information

Contents [Qty of pieces]	1	Lamp wattage	16 W
Net weight [kg]	0,295 kg	Power supply	100 - 240 VAC 50/60 Hz
Total length [mm]	477 mm	Battery type	Lithium-ion (Li-Ion)
Total width [mm]	50 mm	Battery capacity	3.350 mAh
Total height [mm]	40 mm	Burn time	3 h
Material	Plastic	Operating temperature	-5 °C to +50 °C >75% rel. Humidity
Batteries included in delivery	yes	Storage temperature	-20 °C to +70 °C >75% rel. Humidity
Charging time	3,5 h	Light type	Weiss / UV
Luminous flux	620 lm		