



DCH364M2

36V Li-Ion Heavy Duty 3 Mode Quick Change Chuck Dedicated Cordless Hammer

Selling Proposition

- Ideal for drilling anchors and fixing holes into concrete, brick and masonry from 4mm to 26mm
- Rotation stop mode for light chiselling in plaster, tiles and render and impact stop mode for rotary only drilling in wood and metal
- Best in class vibration, 7.1m/s² reduces user fatigue and maximises operating periods
- Quick release SDS-Plus toolholder and keyless chuck supplied for easy switching between hammer / rotary hammer and rotary only applications
- 36 Volt Lithium Ion battery, delivers high performance, long life and maximum runtime

Standard Equipment

- 2 x 4.0Ah Li-Ion battery packs
- Charger
- Multi-position side handle
- Quick release SDS plus toolholder
- Quick release 13mm 3 jaw chuck

Warranty Specifications

- 30 Day No Risk Satisfaction Guarantee
- 1 Year Free Service Contract
- 1 Year Warranty

Specifications

Battery	Li-Ion
Voltage	36 V
Battery Capacity	4.0 Ah
Power Output	600 Watt
No Load Speed	0-1100 rpm
Impact energy (EPTA 05/2009)	2.3 J
Blows per Minute	0-4500 bpm
Tool Holder	SDS-Plus