

Features

- Easy fuse replacement
- RoHS-compliant and Halogen-free
- Wide operating temperature range
- Heat-resistant fuseholder, UL94 V-0
- 260°C reflow capable fuseholder
- Holder sized to fit a range of Nano2 type fuses

RS PRO Non-Resettable Fuses

RS Stock No.: 0139952



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

- *Fuse with Holder Assembly offers a solution for efficient installation and easy replacement of miniature Nano2 surface mount fuses.*
- *Fuse and holder combination can be installed on a PC board as an efficient single step.*
- *Fuse replacement can be accomplished without exposing the PC board to the detrimental effects of solder heat.*
- *Ambient temperature is -55°C to +125 °C.*
- *Reflow Condition: Do not exceed 260°.*

General Specifications

Fuse Type	Surface mount fuse holder with miniature nano2 fuse
-----------	---

Mechanical Specifications

Product size	L*W*H 10*5*3.8mm
--------------	------------------

Electrical Specifications

Fuse Type	See table below for full details
Ampere Rating	See table below for full details
Voltage Rating	250VAC
Breaking Capacity	50A@250VAC; 200A@125VAC

RS Stock No	0139952	0139954	0139955	0139960	0139957	0139958
MPN	0139952	0139954	0139955	0139960	0139957	0139958
Ampere Rating	1A	2A	3A	3.5A	4A	5A
Opening	Time-Lag	Time-Lag	Time-Lag	Time-Lag	Time-Lag	Time-Lag

Approvals

Declarations	MFR Declaration of Conformity
Agency Approvals	E340427

Drawing

Unit: mm

