

Features

- Switched
- Switched
- Double Pole
- 13A Fused
- Urea Mouldings

RS PRO Fused Spurs

RS Stock No.: 0845484



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

- *Isolate local appliance*
- *Suitable for domestic, commercial and industrial installations.*
- *Suitable for appliances up to 250V~ 13A*
- *Urea mouldings make the spur suitable for use in applications where Antibacterial & Antiviral Certified material is required*
- *Suitable for use with standard UK 13A plug tops*

General Specifications

Plate Dimensions (mm)	86 (W) x 86 (H) x 9.5 (D)
Plate Fixing Centres (mm)	60.3
Style	Rounded Profile
Anti Microbial Certified	Yes
Product Marking	Fused
Warranty (Years)	25

Mechanical Specifications

Termination Type	Screw
Terminal Size (mm)	Ø5
Terminal Torque Value (Nm)	2
Terminal Capacity - Solid (mm²)	3 x 2.5 or 2 x 4
Twin Earth Terminals	Yes
Switched	Yes
Double Pole Switch	Yes
Minimum Back Box Depth (mm)	25
Ingress Protection	IP20
Operational Temperature (°C)	-5 to +40

Electrical Specifications

Frequency (Hz)	50
Resistive Load Rating (A)	13

Approvals

Standards Met	BS 1363-4, BS 1362
---------------	--------------------