

Cable - FLK 50-PA/EZ-DR/HF/KS/1000/YOC - 2904994

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Assembled halogen-free round cable with two molded 50-pos. socket strips (bridged contacts). The cable is suitable for the SDV 531 card; cable length: 10.0 m

Illustration shows the product FLK 50-PA/EZ-DR/KS/ 200/YUC



Key commercial data

| | |
|----------------------|---|
| Packing unit | 1 |
| GTIN |  4 046356 906975 |
| Custom tariff number | 85444290 |

Technical data

General

| | |
|---|---|
| Nominal voltage U_N | 30 V DC |
| Max. current carrying capacity per path | 500 mA (Up to 55°C ambient temperature) |
| Max. conductor resistance | 0.16 Ω /m |
| Length of cable | 10 m |
| Single wire, cross section | 0.14 mm ² |
| AWG | 26 |
| Conductor construction: Number of litz wires: | 7 |
| Single wire, material | Cu tin-plated |
| External diameter | 11 mm |
| Shielding | yes |
| Standards/specifications | Halogen-free sheath IEC 60754-1 |
| Outer sheath, material | PVC |
| External sheath, color | Gray RAL 7035 |

Environmental conditions

| | |
|---|------------------|
| Ambient temperature (operation) | -20 °C ... 50 °C |
| Ambient temperature (storage/transport) | -20 °C ... 70 °C |
| Flame resistance | IEC 60332-3 |

Cable - FLK 50-PA/EZ-DR/HF/KS/1000/YOC - 2904994

Technical data

Environmental conditions

| | |
|---------------------|------------------------------------|
| Resistance to oil | DIN VDE 0472 Part 803, test type B |
| Gasoline resistance | Against occasional splashes |

Connector, module side

| | |
|---------------------|--------------------------------|
| Number of positions | 50 |
| Connectors | IDC/FLK socket strip (2.54 mm) |
| Number of plugs | 1 |

Connector, controller side

| | |
|---------------------|--------------------------------|
| Number of positions | 50 |
| Connectors | IDC/FLK socket strip (2.54 mm) |
| Number of plugs | 1 |

Connection data

| | |
|-------------------|------------------|
| Connection method | Screw connection |
| Torque | 0.5 Nm |

Classifications

eCl@ss

| | |
|------------|----------|
| eCl@ss 4.1 | 27260701 |
| eCl@ss 5.1 | 27260701 |
| eCl@ss 6.0 | 27260704 |
| eCl@ss 8.0 | 27249205 |

ETIM

| | |
|----------|----------|
| ETIM 4.0 | EC000237 |
| ETIM 5.0 | EC000237 |

Accessories

Spare parts

Screw set - VF-SCREW-YOKOGAWA/M3X18/DCS - 2902873



Replacement screw M3x18 for Yokogawa system cable, front adapter control side.

Cable - FLK 50-PA/EZ-DR/HF/KS/1000/YOC - 2904994

Accessories

Screw set - VF-SCREW-YOKOGAWA/M4X25/KS - 2902874



Replacement screw M4x25 for Yokogawa system cable, module side.

Drawings

Connection diagram

| 50-pos. connector to the I/O card | 50-pos. connector to the module | Wire color |
|---|---------------------------------------|---------------|
| 1 | 50 | black |
| 2 | 49 | brown |
| 3 | 48 | red |
| 4 | 47 | orange |
| 5 | 46 | yellow |
| 6 | 45 | green |
| 7 | 44 | blue |
| 8 | 43 | violet |
| 9 | 42 | gray |
| 10 | 41 | white |
| 11 | 40 | white-black |
| 12 | 39 | white-brown |
| 13 | 38 | white-red |
| 14 | 37 | white-orange |
| 15 | 36 | white-yellow |
| 16 | 35 | white-green |
| 17 | 34 | white-blue |
| 18 | 33 | white-violet |
| 19 | 32 | white-gray |
| 20 | 31 | brown-black |
| 21 | 30 | brown-red |
| 22 | 29 | brown-orange |
| 23 | 28 | brown-yellow |
| 24 | 27 | brown-green |
| 25 | 26 | brown-blue |
| 26 | 25 | brown-violet |
| 27 | 24 | brown-gray |
| 28 | 23 | brown-white |
| 29 | 22 | green-black |
| 30 | 21 | green-brown |
| 31 | 20 | green-red |
| 32 | 19 | green-orange |
| 33 | 18 | green-blue |
| 34 | 17 | green-violet |
| 35 | 16 | green-gray |
| 36 | 15 | green-white |
| 37 | 14 | yellow-black |
| 38 | 13 | yellow-brown |
| 39 | 12 | yellow-red |
| 40 | 11 | yellow-orange |
| 41 | 10 | yellow-blue |
| 42 | 9 | yellow-violet |
| 43 | 8 | yellow-gray |
| 44 | 7 | yellow-white |
| 45 | 6 | gray-black |
| 46 | 5 | gray-brown |
| 47 | 4 | gray-red |
| 48 | 3 | gray-orange |
| 49 | 2 | gray-yellow |
| 50 | 1 | gray-green |