

# KERN FKB65K1



High resolution bench scale with large weighing range and robust stainless steel weighing plate



## Environmental conditions

Maximum humidity:	80 %
Maximum operating temperature:	40 °C
Minimum ambient temperature:	-10 °C

## Power supply

Battery:	4x1.5 V AA
Charging time:	8 h
Input voltage:	100 V - 240 V AC 50 / 60 Hz
Mains adapter:	Mains adapter external
Mains adapter/adapter included:	US UK EURO CH
Operating time:	20 h
Operating time (Backlight off):	48 h
Operating time (Backlight on):	24 h
Rechargeable battery:	Rchrg. battery optional - intern

## Services (optional)

DAkkS Certificate:	963-129
--------------------	---------

## Category

Brand:	KERN
Category:	Balances
Product Group:	Bench scale

## Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	470 x 470 x 190 mm
Gross weight:	7,600 kg
Net weight:	6,500 kg
Shipping method:	Parcel service

## Construction

Dimensions housing (WxDxH):	350 x 390 x 120 mm
Dimensions of weighing plate (WxDxH):	340 x 240 x 21 mm
Level indicator:	yes
Material weighing plate:	stainless steel
Revolving screw feet:	yes
Weighing surface (WxD):	340 x 240 mm

## Measuring system

Adjustment options:	External calibration
Eccentric loading at 1/3 [Max]:	5 g
Linearity:	3 g
Readability [d]:	1 g
Recommended adjusting weight:	60 kg (F2)
Repeatability:	1 g
Resolution:	65000
Stabilisation time under laboratory conditions:	3 s
Warm up time:	2 h
Weighing capacity [Max]:	65 kg
Weighing system:	Strain gauge
Weighing units:	ffa oz ozt kg g lb dwt gn

## Display

Display digit height (large):	2,500 cm
-------------------------------	----------

## Counting

Counting resolution:	32500
Minimum piece weight at piece counting (Laboratory):	2 g
Minimum piece weight at piece counting (Normal):	20 g
Reference weight:	yes

## Functions

Counting function:	yes
Percentage determination:	yes
Vibration-free weighing (Animal weighing program):	yes
Weighing with tolerance range:	yes


# KERN FKB65K1



High resolution bench scale with large weighing range and robust stainless steel weighing plate

## Piktogramme

### STANDARD



### OPTION

