

Features

- Class CC
- 10X38 mm size
- RoHS compliant

RS PRO Cartridge Fuses

RS Stock No.: 0199221



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

RS PRO offer this range of miniature ceramic 600V AC cartridge fuses. These fuses are fast acting and are used in semiconductors and line protection, with currents from 1A – 30A.

RS PRO have a range of cartridge fuses types to suit all your requirements.

Electrical Specifications


Current Rating	12A
Voltage Rating	600V AC
Fuse Type	Fast-Acting Fuses Class CC
Fuse Size	10x38 mm
Testing Standard	UL 248-4
Body Material	Ceramic
Fuse Speed	CC

Electrical Characteristics


% of CURRENT RATING	BLOWING TIME
110%	15 minutes Min.
135%	1 hour Max.
200%	4 minutes Max.

Approvals

Compliance/Certifications	UL  , RoHS
Declarations	UL 248-4



HC10NR AVERAGE I-T CHARACTERISTICS CURVE (FOR REFERENCE ONLY)



Similar Products

Stock no.	Product name	Current
0199212	Fast-Acting Fuses Class CC	600V AC, 20A
0199213	Fast-Acting Fuses Class CC	600V AC, 30A
0180079	Fast-Acting Fuses Class CC	600V AC, 1A
0199227	Fast-Acting Fuses Class CC	600V AC, 10A
0199233	Fast-Acting Fuses Class CC	600V AC, 25A
0180085	Fast-Acting Fuses Class CC	600V AC, 5A
0199235	Fast-Acting Fuses Class CC	600V AC, 7A
0199238	Fast-Acting Fuses Class CC	600V AC, 15A
0199244	Fast-Acting Fuses Class CC	600V AC, 3A
0199221	Fast-Acting Fuses Class CC	600V AC, 12A
0180069	Fast-Acting Fuses Class CC	600V AC, 2A

Due to our policy of continuous product improvement, we reserve the right to discontinue or change product specifications or designs at any time without notice and without incurring obligations. You should always contact us for the most up-to-date information on our products