

KSW14400EU

This new addition to the range is an excellent cooling fan but with 14400m³/hr at 480Pa it's one of the most powerful ventilation fans available. Available in either 110v or 230V the KSW14400EU can be supplied with up to 10m lengths of ducting and features a rugged steel construction, lockable castors and swivelling head that can be locked into position.

Max Airflow m³/hr 14400

Dimensions H:870 W:550D:770 (mm)

Weight (kg) 61

Electric Supply 110 or 230V 50Hz

Plug Type Euro Plug

