



www.hellermanntyton.co.uk | Products | Cable Ties and Fixings | Cable Ties inside serrated

## Cable Ties Polyamide 6.6 standard T50L



### T-Series in PA66 natural, Article number: 111-05409

- Available in a wide range of material and sizes
- Made from 100% high quality plastic, allows for good recycling
- Inside serration for a strong hold onto bundles
- Easy application either manually or with a processing tool
- Simply to insert due to bent tail

These cable ties are used for routing, bundling and securing of cables, pipes and hoses.



[Catalogue page \(April 2011\)](#) [All catalogue pages](#)

[Print](#)

### Base Data

Application Method	Quick, simple fixing by hand or with HellermannTyton tensioning tools
Application Tool	MK3SP, MK3PNSP2, MK7P, MK7, MK7HT, MK20, MK6, MK6PN, MK9, MK9HT, MK21
Colour	Natural (NA)
Fixation Method (FF)	None
Identification Plate Position	none
Product Family	T-Series in PA66 natural
Product Group	Cable Ties Polyamide 6.6 standard
Releasable Closure (Yes/No)	No
Tie Closure	plastic pawl
Type	T50L.NN3P
Variant	Inside Serrated

### Product Dimensions

Bundle $\varnothing$ max.	110.0 mm
Bundle $\varnothing$ min.	1.5 mm
Length (L)	390 mm
Min.Tensile Strength (N)	225 N
Width (W)	4.6 mm

### Logistic and Packaging

Carton Quantity	4000 pcs.
EAN code	5022660019029
Pack Cont.	100
Quantity of Europallet	80000 pcs.
Quantity per	pc
Weight (Kg)	2.7 kg

### Material and Specifications

Flammability	UL94 V2
Material	PA66
Material	Polyamide 6.6 (PA66)
Operating Temperature	-40 °C to +85 °C, (+105 °C, 500 h)
Specification	UL ZODZ2.E64963, DIN 30015955, GL 87 847-88 HH, GL 86 137-81 HH

© HellermannTyton 2013