



Main

Range of product	OsiSense XC
Series name	Standard format
Product or component type	Limit switch head
Device short name	ZCKE
Head type	Plunger head
Product compatibility	XCKJ
Associated body	ZCKJ4H7 ZCKJ2 ZCKJD35H7 ZCKJ5H29 ZCKJ1H29 ZCKJ7 ZCKJ41 ZCKJ41H29 ZCKJ4H29 ZCKJD35H29 ZCKJD31H29 ZCKJD37 ZCKJ9H29 ZCKJD35 ZCKJ11H7 ZCKJ9H7 ZCKJ11 ZCKJ1 ZCKJ4 ZCKJ6H29 ZCKJ6 ZCKJ21 ZCKJ9 ZCKJD39 ZCKJ7H29 ZCKJ21H7 ZCKJ41H7 ZCKJ2H29 ZCKJ21H29 ZCKJ5H7 ZCKJD39H7

ZCKJD31
 ZCKJ2H7
 ZCKJD39H29
 ZCKJ8H29
 ZCKJ8
 ZCKJD37H7
 ZCKJ11H29
 ZCKJ8H7
 ZCKJ7H7
 ZCKJ6H7
 ZCKJ5
 ZCKJD37H29
 ZCKJ1H7
 ZCKJD31H7

Movement of operating head	Linear
Type of operator	Roller lever plunger spring return metal
Type of approach	Lateral approach, 1 direction

Complementary

Switch actuation	By 30° cam
Positive opening	With
Net weight	0.195 kg
Head material	Metal

Environment

Ambient air temperature for operation	-40...70 °C
Ambient air temperature for storage	-40...70 °C
Environmental characteristic	Low temperature

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations

Contractual warranty

Warranty	18 months
----------	-----------