

Product Information Sheet

COMMISSION DELEGATED REGULATION (EU) 2019/2013 with regard to energy labelling of electronic displays

	Parameter	Parameter or value and precision			Unit
1.	Supplier's name or trademark.	ABUS Security Center			
	Supplier's address.	Compliance, Linker Kreuthweg 5, 86444 86444, Affing, DE			
2.	Model identifier	TVAC10002			
3.	Energy Efficiency Class for Standard Dynamic Range (SDR)	A			
4.	On mode power demand in SDR	10,0			W
5.	Energy Efficiency Class for High Dynamic Range (HDR)	A			
6.	On mode power demand in HDR, if implemented	12,0			W
7.	Off mode, power demand, if applicable	2,0			W
8.	Standby mode power demand, if applicable	n.a.			W
9.	Networked standby mode power demand, if applicable	0,0			W
10.	Electronic display category	Monitor			
11.	Size ratio	4	:	3	
12.	Screen resolution	1 024	x	768	pixels
13.	Screen diagonal	26,4			cm
14.	Screen diagonal	10			inches
15.	Visible screen area	10,0			dm²
16.	Panel technology used	LED LCD			
17.	Automatic Brightness Control (ABC) available	No			
18.	Voice recognition sensor available	No			
19.	Room presence sensor available	No			
20.	Image refresh frequency rate (default)	60			Hz
21.	Minimum guaranteed availability of software and firmware updates (from the date of end of the placement on the market)	2			Years
22.	Minimum guaranteed availability of spare parts (from the date of end of the placement on the market)	2			Years
23.	Minimum guaranteed product support	3			Years
	Minimum duration of the general guarantee offered by the supplier	3			Years
24.	Power supply type	Internal			
25.	External power supply (non standardized and included in the product box)				
	i	-			
	ii	Input voltage	-		V

	<i>iii</i>	Output voltage	-	V
26.	External standardised power supply (or suitable one if not included in the product box)			
	<i>i</i>	-		
	<i>ii</i>	Required output voltage	-	V
	<i>iii</i>	Required delivered current (minimum)	-	A
	<i>iv</i>	Required current frequency	-	Hz

EPREL registration number: 2562414 Model placed on the Union market from 17/11/2025.		 https://eprel.ec.europa.eu/qr/2562414						
Supplier: ABUS Security Center GmbH & Co. KG (Manufacturer) Website: https://abus.com								
Customer care service: <table border="0"> <tr> <td>Name: Compliance</td> <td>Website: www.abus.com</td> </tr> <tr> <td>Email: material.compliance@abus-sc.com</td> <td>Phone: 08207 959900</td> </tr> <tr> <td colspan="2"> Address: Linker Kreuthweg 5 86444 86444, Affing Germany </td> </tr> </table>			Name: Compliance	Website: www.abus.com	Email: material.compliance@abus-sc.com	Phone: 08207 959900	Address: Linker Kreuthweg 5 86444 86444, Affing Germany	
Name: Compliance	Website: www.abus.com							
Email: material.compliance@abus-sc.com	Phone: 08207 959900							
Address: Linker Kreuthweg 5 86444 86444, Affing Germany								