
## Product data sheet





Cordless Circular Saw

### GKS 18 V-LI



Mobile 18 V cordless circular saw for cuts up to 51 mm

#### The most important data

Battery voltage	18 V
Saw blade diameter	165 mm
Max. cutting capacity in wood (90°)	51 mm

Part Number 0 601 66H 006

> More product information

## Technical data

#### Technical data

No-load speed	3,900 rpm
Saw blade diameter	165 mm
Saw blade bore diameter	20 mm
Battery voltage	18 V
Guide rail compatible	no
Packaging dimensions (width x length x height)	355 x 443 x 255 mm
Weight incl. battery	4.1 kg
Cutting depth	
Max. cutting capacity in wood (90°)	51 mm
Max. cutting capacity in wood (45°)	40 mm

## Noise/vibration information

#### Total vibration values

Vibration emission value ah	3 m/s <sup>2</sup>
Uncertainty K	1.5 m/s <sup>2</sup>

# Invented for life

## Product data sheet

#### Power tools for trade & industry

## Advantages:

- Robust circular saw for cuts up to 51 mm
- Electronic Motor Protection for overload protection and a longer lifetime
- Robust base plate for better stability in demanding work environments



