

## 7MH5118-3KD50

Siwarex WL260 Load Cell SP-S SC 300kg C3 MR - Rated Load 300kg - Accuracy class C3 MR acc. to OIML R60 - 3m Cable length, 4 wires - Made of Stainless steel - protection class IP68 / IP69K - with Y = 20.000d

List Price	Show prices
<b>Customer Price</b>	Show prices
Service & Support (Manuals, Certificates, FAQs...)	Download



## Product

Article Number (Market Facing Number)	7MH5118-3KD50
Product Description	Siwarex WL260 Load Cell SP-S SC 300kg C3 MR - Rated Load 300kg - Accuracy class C3 MR acc. to OIML R60 - 3m Cable length, 4 wires - Made of Stainless steel - protection class IP68 / IP69K - with Y = 20.000d
Product family	Load cell
Product Lifecycle (PLM)	PM300:Active Product

## Price data

Price Group	8W5
List Price	Show prices
Customer Price	Show prices
Surcharge for Raw Materials	None
Metal Factor	None

## Delivery information

Export Control Regulations	AL : N / ECCN : N
Standard lead time ex-works	53 Day/Days
Net Weight (kg)	3,140 Kg
Package size unit of measure	Not available
Quantity Unit	1 Piece
Packaging Quantity	1

## Additional Product Information

EAN	Not available
UPC	Not available
Commodity Code	84239010
LKZ_FDB/ CatalogID	WT10
Product Group	4913
Group Code	R3P5
Country of origin	China
Compliance with the substance restrictions according to RoHS directive	Since: 02.07.2013
Product class	A: Standard product which is a stock item could be returned within the returns guidelines/period.
WEEE (2012/19/EU) Take-Back Obligation	Yes
REACH Art. 33 Duty to inform according to the current list of candidates	

## Classifications

	Version	Classification
eClass	6	27-32-03-02
eClass	7.1	27-32-03-02
eClass	8	27-32-03-02
eClass	9	27-32-03-02
eClass	9.1	27-32-03-02
ETIM	5	EC003997
ETIM	8	EC003997
UNSPSC	15	32-15-17-05