

## Features

- 2 Gang
- Switched
- Double Pole
- Twin Earth
- Urea Mouldings
- White
- Stylish smooth profile plate

## RS PRO Plug Sockets

RS Stock No.: 0845482



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## Product Description

- Fits standard 25mm 2 gang back boxes
- Double pole switched
- Urea mouldings make the socket suitable for use in applications where Antibacterial & Antiviral Certified material is required
- Suitable for use with standard UK 13A plug tops

## General Specifications

|                           |                            |
|---------------------------|----------------------------|
| Plate Dimensions (mm)     | 146 (W) x 86 (H) x 9.5 (D) |
| Plate Fixing Centres (mm) | 120.6                      |
| Style                     | Rounded Profile            |
| Anti Microbial Certified  | Yes                        |
| Warranty (Years)          | 25                         |

## Mechanical Specifications

|                                              |                  |
|----------------------------------------------|------------------|
| Termination Type                             | Screw            |
| Terminal Size (mm)                           | Ø5               |
| Terminal Torque Value (Nm)                   | 2                |
| Terminal Capacity - Solid (mm <sup>2</sup> ) | 3 x 2.5 or 2 x 4 |
| Twin Earth Terminals                         | Yes              |
| Double Pole Switch                           | Yes              |
| Minimum Back Box Depth (mm)                  | 25               |
| Ingress Protection                           | IP20             |
| Operational Temperature (°C)                 | -5 to +40        |

## Electrical Specifications

|                           |    |
|---------------------------|----|
| Frequency (Hz)            | 50 |
| Resistive Load Rating (A) | 13 |

## Approvals

|               |           |
|---------------|-----------|
| Standards Met | BS 1363-2 |
|---------------|-----------|