


NO	DESCRIPTION	DATE
⚠	BACKGROUND FORMAT UPDATED	01.21.10'
⚠	DEL PROOF VOLTAGE WORKING VOLTAGE 60 → 85 VOLTAGE RATING	12.31.14'



1.0 ELECTRICAL

- 1.1 FREQUENCY RANGE: DC-1 GHz
- 1.2 NOMINAL IMPEDANCE: 50 OHM
- 1.3 VOLTAGE RATING: 335 VOLTS MAX. ⚠

2.0 MATERIALS

- 2.1 BODIES: BRASS PER JIS-C3604
- 2.2 CENTER CONTACT: BRASS PER JIS-C3604
- 2.3 INSULATION: TEFLON PER ASTM D1457 AND ASTM D1710
- 2.4 CRIMP FERRULE: BRASS PER JIS-C2700

3.1 SEE BELOW TABLE FOR DETAILS.

4.0 MECHANICAL

- 4.1 INTERFACE IN ACCORDANCE WITH: MIL-STD-348A
- 4.2 CABLE RETENTION 15 lbs MIN.

5.0 ENVIRONMENTAL

5.1 OPERATING TEMPERATURE RANGE: -40° C TO +85° C ⚠

NO	DESCRIPTION	Q'TY	FINISH
3	HEAT SHRINK TUBE	2	BLACK
2	CABLE	1	RG/174U
1	19-03-3 174U(50Ω)	2	T.G.G

APPROVED

by _____ DATE: _____



DESCRIPTION		SMA PLUG CRIMP ST.+SMA PLUG CRIMP ST.+RG-174U	
製圖	DRAWN <i>Kristina</i>	TOLERANCE .X ±0.2	品名 YH47-08
檢圖	CHECK <i>Arc</i>	.XX ±0.1	單位 mm(In)
認定	APPROVAL <i>Angela</i>	.XXX ±0.05	比例 4:1
		ANGLE ±5°	
			TITLE ROHS COMPLIANT
			DATE 12.03.03'
			版次 A-2
			DWG.NO. 99-0314