



ENGLISH

Datasheet

Stock No: 429-640

RS Pro Straight Cable Conduit Fitting, Nylon 66 25mm nominal size IP55



Product Details

Fittings

IP55 (with Fittings)

Conduit -50°C → +100°C, fittings -25°C → +50°C operating temperature

Crush resistant to BS6099

1.5mm pitch straight fittings supplied with locking

Self extinguishing nylon to UL94VO

Resistant to: nitric acid, sulphuric acid, detergent, diesel and white spirit

Specifications:

Fitting Type	Straight
Nominal Size	25mm
Material	Nylon 66
Colour	Grey
IP Rating	IP55
Minimum Operating Temperature	-25°C
Maximum Operating Temperature	+50°C