Product catalogue

TABLE OF CONTENTS PAGE

ABOUT RAACO 5
Quality and environment 6
Sustainable development 7

ASSORTMENT BOXES 9
Assorter 10
Boxxser 16
CarryLite Standard 22
CarryMore System 33
CarryLite LMS 36
Foam inlay 48

TOOL BOXES 51
Compact 52
Open Toolbox 55
ToolBag Pro 56
Tool Trolley Proff 58

TOOL CASES
ToolCase 60

TRANSPORT CASES
Solid Box 64
Toolchest 66
FlightCase 68

STORAGE CABINETS 71
Storage Cabinets System 150 72
Storage Cabinets System 250 81

SHELVING SYSTEM 86

TABLE OF CONTENTS PAGE

BINS SYSTEM **94**

TOOL WALL PANEL/CLIPS **100**

INSERTS **107**

Inserts 55-series **108**

Inserts 80-series **110**

Inserts 27-series **111**

System, compatibility and choice **113**

Find and configure inserts for:

- Assorter 4x8 114
- Assorter 4x4 115
- Assorter 6-0 116
- Pocketbox 116
- Boxxser 55 4x4 117
- Boxxser 55 5x5 118
- Boxxser 55 6x6 119
- Boxxser 55 5x10 120
- Boxxser 80 5x10 121
- Boxxser 80 8x8 122
- CarryLite 4x8 123
- CarryLite 5x10 124
- Compact 125
- Drawer 250-3 126
- ToolCase - tray 55 XL 127

RAACOSTAT - ESD PRODUCTS **129**

ESD Cabinets **130**

ESD Bins **134**

ESD Assorter **136**

ESD Compact **137**

ESD Accessories **138**

raaco has specialised in developing the best, simplest storage systems for industry and professional use all over the world since 1956. Our approach is highly focused and simple. It's all about order. Not just for the multitude of components, tools and small items vital to production, but also in the mind. Order gives overview, control and reassurance, enhancing job satisfaction for everyone.

Room for good ideas that last

When the workplace is tidy, with all the important small items and accessories sorted into the right boxes and compartments, thinking clearly is easier. There's room to see things from a new angle and to achieve even better results. That's how we work ourselves at raaco. And that's why we can continue to develop new, innovative and detailed solutions that last.

Design awards have to be lived up to

raaco has been awarded a host of international and Danish awards for excellent industrial design over the years. Naturally, that's something we are proud of. They also have to be lived up to. That's why we are so particular, setting high standards for the durability, function and details of our systems. We always seek to maintain such standards with regard to ideas, the design itself and choice of materials.

Made in Denmark

raaco is designed and produced in Nykøbing Falster, Denmark, and we are immensely proud that our products generate great interest both in Denmark and abroad. raaco is currently used in over 40 countries, creating order in everything from small enterprises to the Airbus Group, which is among Europe´s biggest companies.

A design for the future, caring for the environment

At raaco, we do a lot to ensure environmentally sustainable product development and operations. In practice, this means that we continuously focus on reducing the company's environmental impact by using robust and recyclable materials, and ensure a robust design and construction of the products.

raaco invest heavily in replacing older machines and equipment with less consumption and better working environment as a result.

Certificates
Since 1992, raaco has been ISO 9001 certified and ISO 14001 since 1999 and in 2019 raaco also got the 45001 certification.

You can read our statements and certificates on our website:
www.raaco.com/en/about-raaco/quality-and-environment

THE GLOBAL GOALS
For Sustainable Development

At raaco, we support the UN Global Impact Initiative's 10 principles on human rights, labor rights, the environment and anti-corruption in our efforts for sustainable development.

As a medium-sized production company located on an idyllic island in Denmark, where the main occupation is agriculture, our biggest concern is environmental protection.

We work continuously on various environmental projects using the UN global goals as an inspiration, when focusing on:

Good health and well-being of our workers and surrounding community thru reducing or removing dangerous chemicals in processes, where possible.

Continuously looking for new, "greener" processes and materials we can implement in our manufacturing to reduce energy and water consumption.

Minimizing production waste and discharge of chemicals to groundwater and air.

The energy reducing efforts include implementing new plastic molding machines with more economic energy and water use, installing of LED lightning with sensor switches in warehouses and production units and establishment of powder coating facility in our steel department.

Overall, we reduced our energy consumption with 25% over a period of 3 years.

The most noteworthy was the 43% energy reduction in warehouses, due to exchanging old luminaires with fluorescent lamps for new ones with LED lights with motion sensors.

Installing a new powder coating facility gave us a possibility for about 50% reduction of energy, 40% reduction of LPG gas and 25% reduction of water used in the process.

There is no discharge of chemicals to sewage or air and all chemicals are used in closed circulation.

Working environment conditions are much better – the air is free for chemical particles and the noise from the installation is reduced – as attested by measurements conducted by independent specialists.

As ISO 9001/14001/45001 certified company we are continuously working on introducing better, cleaner, more innovative ways to keep our workers in good health, our community clean and our products in excellent quality.

raaco Assortment Boxes

- Create your own system for complete order

raaco compartment boxes consist of Boxxser, CarryLite and Assorters, each of which have their uses according to individual requirements for keeping things in order.

Order creates results
It's reassuring to know that everything is in its place. The compartment box system is designed for use in the workshop, on-site, on the move or for fitting in service vehicles. They bring order in a functional, durable and simple manner. The order you build from the start can be maintained wherever you go which helps create results at work.

raaco inserts - a unique system
Our inserts not only fit our 3 compartment boxes, but are also used in other raaco products. They represent a unique system with infinite variety to meet individual needs for order.

Designed for strength
These compartment boxes are designed for longterm use and strength at work. Strong, impact-resistant clear lids allows you to see where things are. The boxes are made of impact-resistant polycarbonate and polypropylene, materials that are highly durable and strong, with robust hinges that allow the boxes to be used again and again.

Assorter

Boxxser

CarryLite

Assorter

Environmentally-friendly, made from recyclable materials

Assorter is the only one of our 3 assortment boxes, which is available with fixed compartments. Assorter is a system designed and created specifically for practical sorting.

Assorter was developed according to DFD guidelines (Design for Disassembly), which ensures that the box can be disassembled and the parts replaced/reused.

The range is available in many different sizes. Some of the boxes are equipped with U-profiles on the inside of the lid that keep the contents in place during transportation.

"I use my assortment boxes every time I'm working at a customer's premises it gives me good overview, saving me a lot of time and I don't have to go rooting around for things."

Martin Steen,
electrician at Enelco ApS

Assorter 6-7

Assorter with fixed compartments. Fitted with a sliding lock.
7 fixed compartments.

Made of polypropylene (PP).

Dim (HxWxD, mm): 32 x 175 x 143
Colour: raaco blue
Qt: 18
Carriage load (kg): 1,00

Item No.: 136136

Assorter 6-12

Assorter with fixed compartments. Fitted with a sliding lock.
12 fixed compartments.

Made of polypropylene (PP).

Dim (HxWxD, mm): 32 x 175 x 143
Colour: raaco blue
Qt: 18
Carriage load (kg): 1,00

Item No.: 136143

Assorter 6-0

Assorter with one compartment. Can be divided using inserts A71, A73, A75 and A78 (extra accessory). Fitted with a sliding lock.
Without inserts.

Made of polypropylene (PP).

Dim (HxWxD, mm): 32 x 175 x 143
Colour: raaco blue
Qt: 18
Carriage load (kg): 1,00

Item No.: 136129

Assorter 5-9

Assorter with fixed compartments. Fitted with a sliding lock.
9 fixed compartments.

Made of polypropylene (PP).

Dim (HxWxD, mm): 43 x 240 x 195
Colour: raaco blue
Qt: 12
Carriage load (kg): 2,00

Item No.: 136150

Assorter 5-18

Assorter with fixed compartments. Fitted with a sliding lock.
18 fixed compartments.

Made of polypropylene (PP).

Dim (HxWxD, mm): 43 x 240 x 195
Colour: raaco blue
Qt: 12
Carriage load (kg): 2,00 **Item No.: 136167**

Assorter 55 4x4-0

Assorter. Can be sub-divided using inserts 55 (extra accessory).
Fitted with a sliding lock.

Made of polypropylene (PP).

Dim (HxWxD, mm): 56 x 241 x 195
Colour: raaco blue
Qt: 9
Carriage load (kg): 3,50 **Item No.: 136198**

Assorter 4-15

Assorter with fixed compartments. Equipped with U-profiles inside the lid, which ensures that the contents remain in place during transportation. Fitted with sliding locks.
15 fixed compartments.

Made of polypropylene (PP).

Dim (HxWxD, mm): 57 x 338 x 260
Colour: raaco blue
Qt: 7
Carriage load (kg): 5,00 **Item No.: 136174**

Assorter 4-32

Assorter with fixed compartments. Equipped with U-profiles inside the lid, which ensures that the contents remain in place during transportation. Fitted with sliding locks.
32 fixed compartments.

Made of polypropylene (PP).

Dim (HxWxD, mm): 57 x 338 x 260
Colour: raaco blue
Qt: 7
Carriage load (kg): 5,00 **Item No.: 136181**

Assorter 55 4x8-17

Assorter with inserts. 4 pcs. of type A9-1, 4 pcs. of type A9-2, 8 pcs. of type A8-1, 1 pc. of type A7-1. Equipped with U-profiles inside the lid, which ensures that the contents remain in place during transportation. Fitted with sliding locks and handle.

Made of polypropylene (PP).

Dim (HxWxD, mm): 57 x 338 x 261
Colour: raaco blue
Qt: 7
Carriage load (kg): 5,00 **Item No.: 136228**

Assorter 55 4x8-0

Assorter. Can be sub-divided using inserts 55 (extra accessory). Equipped with U-profiles inside the lid, which ensures that the contents remain in place during transportation. Fitted with sliding locks and handle.

Made of polypropylene (PP).

Dim (HxWxD, mm): 57 x 338 x 261
Colour: raaco blue
Qt: 7
Carriage load (kg): 5,00 **Item No.: 136204**

Assorter 80 4x8-0

Assorter. Can be sub-divided using inserts 80 - extra accessory. Equipped with U-profiles inside the lid, which ensures that the contents remain in place during transportation. Fitted with sliding locks.

Made of polypropylene (PP).

Dim (HxWxD, mm): 78 x 338 x 261
Colour: raaco blue
Qt: 5
Carriage load (kg): 7,00 **Item No.: 136235**

HandyBox 55x4

Portable carrying box with 2 pcs. Assorter 55 4x8-15 and 2 pcs. Assorter 55 4x8-17. Can be freestanding and wall mounted. They can also be stacked or linked together.

Made of polypropylene (PP).

Dim (HxWxD, mm): 310 x 376 x 265
Colour: raaco blue
Qt: 1
Carriage load (kg): 25,00 **Item No.: 136242**

HandyBox 55

Portable carrying box for Assorter 55 4x8, Assorter 4-15 or Assorter 4-17.

Made of polypropylene (PP).

Dim (HxWxD, mm): 310 x 376 x 265
Colour: raaco blue
Qt: 1
Carriage load (kg): 25,00 **Item No.: 136259**

Pocketbox

Pocketbox. Can be divided with the inserts A73, A75 or A78 (extra accessory).

Made of polypropylene (PP).

Dim (HxWxD, mm): 27 x 119 x 95
Colour: Transparent
Qt: 30
Carriage load (kg): 0,50 **Item No.: 113922**

The Assorter is available with removable inserts or fixed compartments

Boxxser

Designed for strength and long term use

Boxxser is a particularly strong box able to tolerate the stresses and strains of the workplace.

Strong, impact resistant clear lids so that you can see where things are. The boxes are made of impact-resistant polycarbonate and polypropylene, materials that are highly durable and strong.

The various sizes and flexibility of the system meet any requirement for optimum function.

The boxes are equipped with O-profiles on the inside of the lid that keep the contents in place during transportation.

"We are totally dependent on order at Pilemand. We have such a wide range of jobs during the year, which means that we have to keep all our materials in order. Boxxser makes it easy to maintain overview, which can clearly be seen in the results."

Martin,
joiner at Pilemand A/S.

German Design Award SPECIAL MENTION 2014

product design award 2012

Boxxser received the IF design award in 2012 and was nominated for the German Design Award in 2014

Boxxser 55 4x4-0

Small assorter box. Can be adapted with removeable inserts of assorted sizes for small parts, tools and accessories (extra accessory). Equipped with O-profiles inside the lid, which ensures that the contents remain in place during transportation.

Made of polypropylene (PP) and lid of polycarbonate (PC).

Dim (HxWxD, mm): 55 x 241 x 225
Colour: raaco blue
Qt: 5
Carriage load (kg): 8,00 **Item No.: 134750**

Boxxser 55 4x4-9

Small assorter box. Fitted with removeable inserts of assorted sizes for small parts, tools and accessories: 4 pcs. of type A9-1, 2 pcs. of type A2-2, 2 pcs. of type A8-1 and 1 pcs. of type A7-1. Equipped with O-profiles inside the lid, which ensures that the contents remain in place during transportation.

Made of polypropylene (PP) and lid of polycarbonate (PC).

Dim (HxWxD, mm): 55 x 241 x 225
Colour: raaco blue
Qt: 15
Carriage load (kg): 8,00 **Item No.: 138277**

Boxxser 55 5x5-15

Assortment box with removable inserts for small parts: 8 pcs. of type A9-1, 1 pcs. of type A9-2, 1 pcs. of type A9-3, 4 pcs. of type A8-1 and 1 pc. of type A7-1. Equipped with O-profiles inside the lid, which ensures that the contents remain in place during transportation. With combined close and lock mechanism.

Made of polypropylene (PP) and lid of polycarbonate (PC).

Dim (HxWxD, mm): 55 x 298 x 284
Colour: raaco blue
Qt: 5
Carriage load (kg): 10,00 **Item No.: 134811**

Boxxser 55 6x6-0

Assortment box for small parts. Can be divided using a combination of inserts 55 (extra accessory). Equipped with O-profiles inside the lid, which ensures that the contents remain in place during transportation. With combined close and lock mechanism.

Made of polypropylene (PP) and lid of polycarbonate (PC).

Dim (HxWxD, mm): 55 x 354 x 323
Colour: raaco blue
Qt: 5
Carriage load (kg): 12,00 **Item No.: 134828**

Boxxser 55 6x6-14

Assortment box with removable inserts for small parts: 6 pcs. of type A9-1, 2 pcs. of type A9-4, 3 pcs. of type A8-1, 2 pcs. of type A7-1 and 1 pc. of type A6-1. Equipped with O-profiles inside the lid, which ensures that the contents remain in place during transportation. With combined close and lock mechanism.

Made of polypropylene (PP) and lid of polycarbonate (PC).

Dim (HxWxD, mm): 55 x 354 x 323
Colour: raaco blue
Qt: 5
Carriage load (kg): 12,00 **Item No.: 134842**

Boxxser 55 5x10-0

Assorter box. Can be adapted with removable inserts of assorted sizes for small parts, tools and accessories (extra accessory). Equipped with O-profiles inside the lid, which ensures that the contents remain in place during transportation. With combined close and lock mechanism.

Made of polypropylene (PP) and lid of polycarbonate (PC).

Dim (HxWxD, mm): 55 x 421 x 361
Colour: raaco blue
Qt: 4
Carriage load (kg): 15,00 **Item No.: 134866**

Boxxser 55 5x10-25

Assorter box. Fitted with 25 removable inserts of type A8-1 for small parts. Equipped with O-profiles inside the lid, which ensures that the contents remain in place during transportation. With combined close and lock mechanism.

Made of polypropylene (PP) and lid of polycarbonate (PC).

Dim (HxWxD, mm): 55 x 421 x 361
Colour: raaco blue
Qt: 4
Carriage load (kg): 15,00 **Item No.: 134873**

Boxxser 55 5x10-45

Assorter box. Fitted with removable inserts: 40 pcs. of type A9-1 and 5 pcs. of type A8-1. Equipped with O-profiles inside the lid, which ensures that the contents remain in place during transportation. With combined close and lock mechanism.

Made of polypropylene (PP) and lid of polycarbonate (PC).

Dim (HxWxD, mm): 55 x 421 x 361
Colour: raaco blue
Qt: 4
Carriage load (kg): 15,00 **Item No.: 134897**

Boxxser 80 5x10-14

Assortment box with removable inserts for small parts: 6 pcs. of type BA8-1, 2 pcs. of type BA8-2, 1 pc. of type BA8-3, 4 pcs. of type BA7-1 and 1 pc. of type BA7-2. Equipped with O-profiles inside the lid, which ensures that the contents remain in place during transportation. With combined close and lock mechanism.

Made of polypropylene (PP) and lid of polycarbonate (PC).

Dim (HxWxD, mm): 78 x 421 x 361
Colour: raaco blue
Qt: 3
Carriage load (kg): 15,00 **Item No.: 134910**

Boxxser 80 5x10-20

Assortment box with removable inserts for small parts: 15 pcs. of type BA8-1 and 5 pcs. of type BA7-1. Equipped with O-profiles inside the lid, which ensures that the contents remain in place during transportation. With combined close and lock mechanism.

Made of polypropylene (PP) and lid of polycarbonate (PC).

Dim (HxWxD, mm): 78 x 421 x 361
Colour: raaco blue
Qt: 3
Carriage load (kg): 15,00 **Item No.: 134934**

Boxxser 80 8x8-0

Assortment box for small parts. Can be divided using inserts 80 (extra accessory). Equipped with O-profiles inside the lid, which ensures that the contents remain in place during transportation. With combined close and lock mechanism.

Made of polypropylene (PP) and lid of polycarbonate (PC).

Dim (HxWxD, mm): 78 x 465 x 401
Colour: raaco blue
Qt: 3
Carriage load (kg): 20,00 **Item No.: 134958**

Boxxser 80 8x8-18

Assortment box with removable inserts for small parts: 8 pcs. of type BA8-1, 2 pcs. of type BA8-2, 2 pcs. of type BA8-3, 5 pcs. of type BA7-1 and 1 pc. of type BA7-2. Equipped with O-profiles inside the lid, which ensures that the contents remain in place during transportation. With combined close and lock mechanism.

Made of polypropylene (PP) and lid of polycarbonate (PC).

Dim (HxWxD, mm): 78 x 465 x 401
Colour: raaco blue
Qt: 3
Carriage load (kg): 20,00 **Item No.: 134972**

Boxxser 80 8x8-20

Assortment box with removable inserts for small parts: 14 pcs. of type BA8-1, 1 pc. of type BA8-2, 2 pcs. of type BA8-3, 1 pc. of type BA7-1 and 2 pcs. of type BA6-1. Equipped with O-profiles inside the lid, which ensures that the contents remain in place during transportation. With combined close and lock mechanism.

Made of polypropylene (PP) and lid of polycarbonate (PC).

Dim (HxWxD, mm): 78 x 465 x 401
Colour: raaco blue
Qt: 3
Carriage load (kg): 20,00 **Item No.: 134989**

HandyBoxxser 4x4x4

HandyBoxxser incl. 4x Boxxser 55 4x4-9. The system allows you to store four boxes together using minimum space, while providing you with easy access to the contents.

Made of polypropylene (PP).

Dim (HxWxD, mm): 342 x 290 x 247
Colour: raaco blue
Qt: 1
Carriage load (kg): 15,00 **Item No.: 137942**

HandyBoxxser 5x5

The HandyBoxxser system allows you to store four boxes together in a minimum of space, while providing you with easy access to the contents.

Made of polypropylene (PP).

Dim (HxWxD, mm): 342 x 347 x 305
Colour: raaco blue
Qt: 1
Carriage load (kg): 20,00 **Item No.: 137959**

HandyBoxxser 4x5x5

HandyBoxxser incl. 4x Boxxser 55 5x5-15. The system allows you to store four boxes together in a minimum of space, while providing you with easy access to the contents.

Made of polypropylene (PP).

Dim (HxWxD, mm): 342 x 347 x 305
Colour: raaco blue
Qt: 1
Carriage load (kg): 20,00 **Item No.: 137966**

Boxxser 4xID-Tag

Boxxser ID-Tag can be used for colour coding, mounting of labels or hand writing. Available in several colours.
Contains 4 pcs./bag.

Made of polystyrene (PS).

Mål (HxB, mm): 27 x 85
Colour: raaco Yellow
Qt: 25
Item No.: 136099

Boxxser 4xID-Tag

Boxxser ID-Tag can be used for colour coding, mounting of labels or hand writing. Available in several colours.
Contains 4 pcs./bag.

Made of polystyrene (PS).

Mål (HxB, mm): 27 x 85
Colour: raaco Grey
Qt: 25
Item No.: 136105

Boxxser 4xID-Tag

Boxxser ID-Tag can be used for colour coding, mounting of labels or hand writing. Available in several colours.
Contains 4 pcs./bag.

Made of polystyrene (PS).

Mål (HxB, mm): 27 x 85
Colour: Green
Qt: 25
Item No.: 136112

Foam



Foam insert to protect special tools or instruments during transportation. Can easily be cut to fit the tools and instruments. The foam insert can be used in an Assorter, CarryLite and Boxxser. One foam insert fits into a Boxxser 5x10. To make it fit to the height of a box, then use 2 pcs. for Boxxser type 55 and 3 pcs. for Boxxser type 80.

Made of polyether.

Dim (HxWxD, mm): 20 x 393 x 273
Colour: Grey
Qt: 6
Item No.: 134583

CarryLite Standard

Lightweight and robust

CarryLite is a lightweight assortment box. Produced specifically for overview and order, which makes the system highly durable.

The range is in two sizes: 55 and 80 mm in height with movable inserts, and 150 mm in height with partitions that can be placed according to requirement.

Choose between a normal or sandwich lid for labels, with or without U-profiles. The U-profiles on the inside of the lid and keep the contents in place during transportation. Both types of lid are made of impact-resistant polycarbonate.

"It's great to have a system that can take the knocks at work. I save hours when different fittings are sorted properly. I have the system in my vans and at the workshop and it always works well. Excellent!"

Sonny Bengtson,
Sonny VVS ApS

ID PRISEN 1995

product design award 1997

CarryLite received the IF design award in 1997 and the ID prize in 1995.

CarryLite 55 4x8-16/DLU

CarryLite with sandwich lid with U-profiles inside, which ensures that the contents remain in place during transportation. The sandwich lid allows for insertion of up to 5 sheets of paper of 80 mg between the two lids. The CarryLite contains 8 pcs. inserts of type A9-1, 4 pcs. of type A8-1, 2 pcs. of type A8-2 and 2 pcs. of type A7-1. Fitted with sliding locks, handle and with red markers to indicate if box is closed correctly.
Made of polypropylene (PP) and lid of polycarbonate (PC).

Dim (HxWxD, mm): 58 x 337 x 278
Colour: raaco blue
Qt: 4
Carriage load (kg): 8,00 **Item No.: 145572**

CarryLite 55 4x8-16

Compartment box with inserts: 8 pcs. of type A9-1, 4 pcs. of type A8-1, 2 pcs. of type A8-2 and 2 pcs. of type A7-1. Fitted with 2 sliding locks, handle and with red markers to indicate if box is closed correctly. Equipped with U-profiles inside the lid, which ensures that the contents remain in place during transportation.

Made of polypropylene (PP) and lid of polycarbonate (PC).

Dim (HxWxD, mm): 57 x 337 x 278
Colour: raaco blue
Qt: 4
Carriage load (kg): 8,00 **Item No.: 143615**

CarryLite 55 4x8-10

Compartment box with inserts: 1 pcs. of type A9-1, 2 pcs. of type A9-2, 1 pcs. of type A9-3, 1 pcs. of type A9-4, 2 pcs. of type A8-1, 1 pcs. of type A8-2, 1 pcs. of type A7-1 and 1 pcs. of type A7-2. Fitted with 2 sliding locks, handle and with red markers to indicate if box is closed correctly. Equipped with U-profiles inside the lid, which ensures that the contents remain in place during transportation.

Made of polypropylene (PP) and lid of polycarbonate (PC).

Dim (HxWxD, mm): 57 x 337 x 278
Colour: raaco blue
Qt: 4
Carriage load (kg): 8,00 **Item No.: 144568**

CarryLite 55 4x8-0/DL

CarryLite 55 with sandwich lid without U-profiles, empty.
The sandwich lid allows for insertion of up to 5 sheets of paper of 80 mg between the two lids. Can be sub-divided using inserts 55 and foam (extra accessory). Fitted with sliding locks, handle and with red markers which indicate if the box is closed correctly.

Made of polypropylene (PP) and lid of polycarbonate (PC).

Dim (HxWxD, mm): 58 x 337 x 278
Colour: raaco blue
Qt: 4
Carriage load (kg): 8,00 **Item No.: 142854**

CarryLite 55 4x8-0/DLU

CarryLite 55 with sandwich lid with U-profiles inside, which ensures that the contents remain in place during transportation. The sandwich lid allows for insertion of up to 5 sheets of paper of 80 mg between the two lids. Can be sub-divided using inserts 55 and foam (extra accessory). Fitted with sliding locks, handle and with red markers which indicate if the box is closed correctly.

Made of polypropylene (PP) and lid of polycarbonate (PC).

Dim (HxWxD, mm): 58 x 337 x 278
Colour: raaco blue
Qt: 4
Carriage load (kg): 8,00 **Item No.: 142847**

CarryLite 55 4x8-0/SL

CarryLite 55. Can be sub-divided using inserts 55 and foam (extra accessory). Fitted with sliding locks, handle and with red markers to indicate if box is closed correctly.

Made of polypropylene (PP) and lid of polycarbonate (PC).

Dim (HxWxD, mm): 57 x 337 x 278
Colour: raaco blue
Qt: 4
Carriage load (kg): 8,00 **Item No.: 144643**

CarryLite 55 4x8-0

CarryLite 55. Can be sub-divided using inserts 55 and foam (extra accessory). Fitted with sliding locks, handle and with red markers to indicate if box is closed correctly. Equipped with U-profiles inside the lid, which ensures that the contents remain in place during transportation.

Made of polypropylene (PP) and lid of polycarbonate (PC).

Dim (HxWxD, mm): 57 x 337 x 278
Colour: raaco blue
Qt: 4
Carriage load (kg): 8,00 **Item No.: 142830**

CarryLite 55 5x10-25/1

CarryLite with 25 inserts of type A8-1. Fitted with sliding locks, handle and with red markers to indicate if box is closed correctly. Equipped with U-profiles inside the lid, which ensures that the contents remain in place during transportation.

Made of polypropylene (PP) and lid of polycarbonate (PC).

Dim (HxWxD, mm): 57 x 413 x 330
Colour: raaco blue
Qt: 4
Carriage load (kg): 10,00 **Item No.: 136297**

CarryLite 55 5x10-25/DLU

CarryLite with sandwich lid with U-profiles inside, which ensures that the contents remain in place during transportation. The sandwich lid allows for insertion of up to 5 sheets of paper of 80 mg between the two lids. The CarryLite contains 10 pcs. inserts of type A9-1, 10 pcs. of type A8-1, 5 pcs. of type A7-1. Fitted with sliding locks, handle and with red markers to indicate if box is closed correctly.
Made of polypropylene (PP) and lid of polycarbonate (PC).

Dim (HxWxD, mm): 58 x 413 x 330
Colour: raaco blue
Qt: 4
Carriage load (kg): 10,00 **Item No.: 145596**

CarryLite 55 5x10-25/2

CarryLite with inserts. Content: 10 pcs. of type A9-1, 10 pcs. of type A8-1, 5 pcs. of type A7-1. Fitted with sliding locks, handle and with red markers to indicate if box is closed correctly. Equipped with U-profiles inside the lid, which ensures that the contents remain in place during transportation.

Made of polypropylene (PP) and lid of polycarbonate (PC).

Dim (HxWxD, mm): 57 x 413 x 330
Colour: raaco blue
Qt: 4
Carriage load (kg): 10,00 **Item No.: 136273**

CarryLite 55 5x10-50

CarryLite with 50 inserts of type A9-1. Fitted with sliding locks, handle and with red markers to indicate if box is closed correctly. Equipped with U-profiles inside the lid, which ensures that the contents remain in place during transportation.

Made of polypropylene (PP) and lid of polycarbonate (PC).

Dim (HxWxD, mm): 57 x 413 x 330
Colour: raaco blue
Qt: 4
Carriage load (kg): 10,00 **Item No.: 136280**

CarryLite 55 5x10-0/DL

CarryLite with sandwich lid without U-profiles. The sandwich lid allows for insertion of up to 5 sheets of paper of 80 mg between the two lids. Can be sub-divided using inserts 55 and foam (extra accessory). Fitted with sliding locks, handle and with red markers to indicate if box is closed correctly.

Made of polypropylene (PP) and lid of polycarbonate (PC).

Dim (HxWxD, mm): 58 x 413 x 330
Colour: raaco blue
Qt: 4
Carriage load (kg): 10,00 **Item No.: 142342**

CarryLite 55 5x10-0/DLU

CarryLite with sandwich lid with U-profiles inside, which ensures that the contents remain in place during transportation. The sandwich lid allows for insertion of up to 5 sheets of paper of 80 mg between the two lids. Can be sub-divided using inserts 55 and foam (extra accessory). Fitted with sliding locks, handle and with red markers to indicate if box is closed correctly.

Made of polypropylene (PP) and lid of polycarbonate (PC).

Dim (HxWxD, mm): 58 x 413 x 330
Colour: raaco blue
Qt: 4
Carriage load (kg): 10,00 **Item No.: 142335**

CarryLite 55 5x10-0

CarryLite with U-profiles inside the lid, which ensures that the contents remain in place during transportation. Can be sub-divided using inserts 55 or foam (extra accessory). Fitted with sliding locks, handle and with red markers to indicate if box is closed correctly.

Made of polypropylene (PP) and lid of polycarbonate (PC).

Dim (HxWxD, mm): 57 x 413 x 330
Colour: raaco blue
Qt: 4
Carriage load (kg): 10,00 **Item No.: 136266**

CarryLite 80 4x8-9

Compartment box with inserts: 4 pcs. of type BA8-1, 1 pc. of type BA8-2, 2 pcs. of type BA7-1 and 2 pcs. of type BA7-1½.
Fitted with 2 sliding locks, handle and with red markers to indicate if box is closed correctly. Equipped with U-profiles inside the lid, which ensures that the contents remain in place during transportation.

Made of polypropylene (PP) and lid of polycarbonate (PC).

Dim (HxWxD, mm): 79 x 337 x 278
Colour: raaco blue
Qt: 3
Carriage load (kg): 10,00 **Item No.: 143608**

CarryLite 80 4x8-12

CarryLite box with inserts: 8 pcs. of type BA8-1 and 4 pcs. of type BA7-1. Fitted with 2 sliding locks, handle and with red markers to indicate if box is closed correctly. Equipped with U-profiles inside the lid, which ensures that the contents remain in place during transportation.

Made of polypropylene (PP) and lid of polycarbonate (PC).

Dim (HxWxD, mm): 79 x 337 x 278
Colour: raaco blue
Qt: 3
Carriage load (kg): 10,00 **Item No.: 144551**

CarryLite 80 4x8-12/DLU

CarryLite with sandwich lid with U-profiles inside, which ensures that the contents remain in place during transportation. The sandwich lid allows for insertion of up to 5 sheets of paper of 80 mg between the two lids. The CarryLite contains 8 pcs. inserts of type BA8-1 and 4 pcs. of type BA7-1. Fitted with sliding locks, handle and with red markers to indicate if box is closed correctly.

Made of polypropylene (PP) and lid of polycarbonate (PC).

Dim (HxWxD, mm): 82 x 337 x 278
Colour: raaco blue
Qt: 3
Carriage load (kg): 10,00 **Item No.: 145589**

CarryLite 80 4x8-0/DL

CarryLite 80 with sandwich lid without U-profiles. The sandwich lid allows for insertion of up to 5 sheets of paper of 80 mg between the two lids. Can be sub-divided using inserts 80 and foam (extra accessory). Fitted with sliding locks, handle and with red markers which indicate if the box is closed correctly.

Made of polypropylene (PP) and lid of polycarbonate (PC).

Dim (HxWxD, mm): 82 x 337 x 278
Colour: raaco blue
Qt: 3
Carriage load (kg): 10,00 **Item No.: 142861**

CarryLite 80 4x8-0/DLU

CarryLite 80 with sandwich lid with U-profiles inside, which ensures that the contents remain in place during transportation. The sandwich lid allows for insertion of up to 5 sheets of paper of 80 mg between the two lids. Can be sub-divided using inserts 80 and foam (extra accessory). Fitted with sliding locks, handle and with red markers which indicate if the box is closed.

Made of polypropylene (PP) and lid of polycarbonate (PC).

Dim (HxWxD, mm): 82 x 337 x 278
Colour: raaco blue
Qt: 3
Carriage load (kg): 10,00 **Item No.: 142786**

CarryLite 80 4x8-0/SL

CarryLite 80. Can be sub-divided using inserts 80 and foam (extra accessory). Fitted with sliding locks, handle and with red markers to indicate if box is closed correctly.

Made of polypropylene (PP) and lid of polycarbonate (PC).

Dim (HxWxD, mm): 79 x 337 x 278
Colour: raaco blue
Qt: 3
Carriage load (kg): 10,00 **Item No.: 144650**

CarryLite 80 4x8-0

CarryLite 80 with U-profiles inside the lid, which ensures that the contents remain in place during transportation. Can be sub-divided using inserts 80 and foam (extra accessory). Fitted with sliding locks, handle and with red markers to indicate if box is closed correctly.

Made of polypropylene (PP) and lid of polycarbonate (PC).

Dim (HxWxD, mm): 79 x 337 x 278
Colour: raaco blue
Qt: 3
Carriage load (kg): 10,00 **Item No.: 142793**

CarryLite 80 5x10-15

CarryLite with inserts. Content: 5 pcs. of type BA8-1, 10 pcs. of type BA7-1. Fitted with sliding locks, handle and with red markers to indicate if box is closed correctly. Equipped with U-profiles inside the lid, which ensures that the contents remain in place during transportation.

Made of polypropylene (PP) and lid of polycarbonate (PC).

Dim (HxWxD, mm): 79 x 413 x 330
Colour: raaco blue
Qt: 3
Carriage load (kg): 13,00 **Item No.: 136310**

CarryLite 80 5x10-20/DLU

CarryLite with sandwich lid with U-profiles inside, which ensures that the contents remain in place during transportation.
The sandwich lid allows for insertion of up to 5 sheets of paper of 80 mg between the two lids. The CarryLite contains 15 pcs. inserts of type BA8-1 and 5 pcs. of type BA7-1. Fitted with sliding locks, handle and with red markers to indicate if box is closed correctly.

Made of polypropylene (PP) and lid of polycarbonate (PC).

Dim (HxWxD, mm): 82 x 413 x 330
Colour: raaco blue
Qt: 3
Carriage load (kg): 13,00 **Item No.: 145619**

CarryLite 80 5x10-25/DLU

CarryLite with sandwich lid with U-profiles inside, which ensures that the contents remain in place during transportation.
The sandwich lid allows for insertion of up to 5 sheets of paper of 80 mg between the two lids. The CarryLite contains 25 pcs. inserts of type BA8-1. Fitted with sliding locks, handle and with red markers to indicate if box is closed correctly.

Made of polypropylene (PP) and lid of polycarbonate (PC).

Dim (HxWxD, mm): 82 x 413 x 330
Colour: raaco blue
Qt: 3
Carriage load (kg): 13,00 **Item No.: 145602**

CarryLite 80 5x10-25

CarryLite with 25 inserts of type BA8-1. Fitted with sliding locks, handle and with red markers to indicate if box is closed correctly. Equipped with U-profiles inside the lid, which ensures that the contents remain in place during transportation.

Made of polypropylene (PP) and lid of polycarbonate (PC).

Dim (HxWxD, mm): 79 x 413 x 330
Colour: raaco blue
Qt: 3
Carriage load (kg): 13,00 **Item No.: 136327**

CarryLite 80 5x10-0/DL

CarryLite with sandwich lid without U-profiles. The sandwich lid allows for insertion of up to 5 sheets of paper of 80 mg between the two lids. Can be sub-divided using inserts 80 and foam (extra accessory). Fitted with sliding locks, handle and with red markers to indicate if box is closed correctly.

Made of polypropylene (PP) and lid of polycarbonate (PC).

Dim (HxWxD, mm): 82 x 413 x 330
Colour: raaco blue
Qt: 3
Carriage load (kg): 13,00 **Item No.: 142366**

CarryLite 80 5x10-0/DLU

CarryLite with sandwich lid with U-profiles inside, which ensures that the contents remain in place during transportation. The sandwich lid allows for insertion of up to 5 sheets of paper of 80 mg between the two lids. Can be sub-divided using inserts 80 and foam (extra accessory). Fitted with sliding locks, handle and with red markers to indicate if box is closed correctly.

Made of polypropylene (PP) and lid of polycarbonate (PC).

Dim (HxWxD, mm): 82 x 413 x 330
Colour: raaco blue
Qt: 3
Carriage load (kg): 13,00 **Item No.: 142359**

CarryLite 80 5x10-0

CarryLite with U-profiles inside the lid, which ensures that the contents remain in place during transportation. Can be sub-divided using inserts 80 or foam (extra accessory). Fitted with sliding locks, handle and with red markers to indicate if box is closed correctly.

Made of polypropylene (PP) and lid of polycarbonate (PC).

Dim (HxWxD, mm): 79 x 413 x 330
Colour: raaco blue
Qt: 3
Carriage load (kg): 13,00 **Item No.: 136303**

CarryLite 150-9

CarryLite 150 with dividers. Fitted with sliding locks, handle and with red markers to indicate if box is closed correctly. Contains 8 dividers.

Made of polypropylene (PP) and lid of polycarbonate (PC).

Dim (HxWxD, mm): 148 x 413 x 330
Colour: raaco blue
Qt: 2

Item No.: 136341

CarryLite 150-9 DL

CarryLite with sandwich lid without U-profiles. The sandwich lid allows for insertion of up to 5 sheets of paper of 80 mg between the two lids. Can be sub-divided using the included dividers. Fitted with sliding locks, handle and with red markers to indicate if box is closed correctly. Contains 8 dividers.

Made of polypropylene (PP) and lid of polycarbonate (PC).

Dim (HxWxD, mm): 148 x 413 x 330
Colour: raaco blue
Qt: 2
Carriage load (kg): 20,00

Item No.: 142380

Dividers for CarryLite, large

Dividers for CarryLite 150.
Each bag contains 2 pcs. long dividers.

Made of polycarbonate (PC).

Dim (HxWxD, mm): 134 x 273 x 10
Colour: Black
Qt: 6

Item No.: 136051

Dividers for CarryLite, small+medium

Dividers for CarryLite 150.
Each bag contains 2 pcs. medium dividers + 4 pcs. short dividers.

Made of polycarbonate (PC).

Dim (HxWxD, mm): Small: 135 x 117 x 10
Dim (HxWxD, mm): Medium: 135 x 153 x 10
Colour: Black
Qt: 6

Item No.: 136044

CL-Transporter

Portable carrying box for 4 pcs. CarryLite 55, 3 pcs. CarryLite 80 or 2 pcs. CarryLite 150. Incl. shoulder strap (40 mm. wide).
Castors can be fitted (extra accessory).

Made of polypropylene (PP).

Dim (HxWxD, mm): 250 x 562 x 361
Colour: raaco blue
Qt: 1
Carriage load (kg): 40,00 **Item No.: 143837**

SafeBox 55x4

SafeBox incl. 2 pcs. CarryLite 55 5x10 - 25/1 and 2 pcs. CarryLite 55 5x10 - 25/2.
Fitted with rails mounted on ball bearing and key-lock.

Made of painted steel.

Dim (HxWxD, mm): 403 x 451 x 330
Colour: raaco blue
Qt: 1
Carriage load (kg): 40,00 **Item No.: 136372**

SafeBox 80x3

Safe Box incl. 3 pcs. CL80 5x10-15.
Fitted with rails mounted on ball bearing and key-lock.

Made of painted steel.

Dim (HxWxD, mm): 403 x 451 x 330
Colour: raaco blue
Qt: 1
Carriage load (kg): 40,00 **Item No.: 136389**

SafeBox 150x2

SafeBox incl. 2 pcs. CarryLite 150-9.
Fitted with rails mounted on ball bearing and keylock.

Made of painted steel.

Dim (HxWxD, mm): 403 x 451 x 330
Colour: raaco blue
Qt: 1
Carriage load (kg): 40,00 **Item No.: 136396**

SafeBox 55 empty

SafeBox for 4 pieces of CarryLite 55 5x10.
Fitted with rails mounted on ball bearing and key-lock.
Without CarryLite.

Made of painted steel.

Dim (HxWxD, mm): 403 x 451 x 330
Colour: raaco blue
Qt: 1
Carriage load (kg): 40,00 **Item No.: 139328**

SafeBox 80 empty

SafeBox for 3 pieces of CarryLite 80.
Fitted with rails mounted on ball bearing and key-lock.
Without CarryLite.

Made of painted steel.

Dim (HxWxD, mm): 403 x 451 x 330
Colour: raaco blue
Qt: 1
Carriage load (kg): 40,00 **Item No.: 139335**

SafeBox 150 empty

SafeBox for 2 pieces of CarryLite 150.
Fitted with rails mounted on ball bearing and key-lock.
Without CarryLite.

Made of painted steel.

Dim (HxWxD, mm): 403 x 451 x 330
Colour: raaco blue
Qt: 1
Carriage load (kg): 40,00 **Item No.: 139342**

CarryMore System

- more than just a box!

CarryMore is an intelligent storage and transport system for storing 2 CarryLite 4x8. CarryMore can be stacked and linked together with several CarryMore units.

The capability of front loading makes for easy access regardless of location and without having to move or lift a CarryMore to get to the tools etc. The CarryMore Trolley is designed for easy transport of several CarryMore units stacked together. The trolley enables easy access to the workplace even through narrow passages.

The CarryMore System is made for professional craftsmen and suitable for daily use along the way.

CarryMore

- Connecting lock-mechanism to link together several units
- Top shelf for placement of one CarryMore 4x8 or one ToolBag Pro 16" whilst in use
- Retainers stop the CarryLite boxes from falling out during transportation
- Retaining lock for added security of contents
- Ergonomic handle making it easier and more comfortable to carry

CarryMore Trolley

- Large practical and ergonomic handle which is reinforced with 4 screws
- Large wheels – also suitable for stairs
- The base can be folded and fixed in an upright position using magnets to minimize need for space in the vehicle
- Coupling lock for attaching the CarryMore. This can be set to various heights, depending on how many CarryMore are transported
- An extra workstation on the top of the CarryMore for the placement of 1 CarryLite 4x8 or for storage and transport of 1 ToolBag Pro 16"
- The CarryMore Trolley stores up to 4 CarryMore 55 or 3 CarryMore 80

CarryMore 55

Storage and transport unit for 2 CarryLite 55 4x8. Equipped with ergonomic handle and lock-mechanism to connect several CarryMore to a larger unit. Retainers prevents the CarryLite boxes from falling out during transportation.
Empty.

Made of polypropylene and copolymer (PP and CO).

Dim (HxWxD, mm): 195 x 386 x 263
Colour: Black
Qt: 1
Carriage load (kg): 25,00 **Item No.: 146388**

CarryMore 55x2

Storage and transport unit with 2 CarryLite 55 4x8. Equipped with ergonomic handle and lock-mechanism to connect several CarryMore to a larger unit. Retainers prevents the CarryLite boxes from falling out during transportation.

Made of polypropylene and copolymer (PP and CO).

Dim (HxWxD, mm): 195 x 386 x 263
Colour: Black
Qt: 1
Carriage load (kg): 25,00 **Item No.: 146395**

CarryMore 80

Storage and transport unit for 2 CarryLite 80 4x8. Equipped with ergonomic handle and lock-mechanism to connect several CarryMore to a larger unit. Retainers prevents the CarryLite boxes from falling out during transportation.
Empty.

Made of polypropylene and copolymer (PP and CO).

Dim (HxWxD, mm): 241 x 386 x 263
Colour: Black
Qt: 1
Carriage load (kg): 25,00 **Item No.: 146401**

CarryMore 80x2

Storage and transport unit with 2 CarryLite 80 4x8. Equipped with ergonomic handle and lock-mechanism to connect several CarryMore to a larger unit. Retainers prevents the CarryLite boxes from falling out during transportation.

Made of polypropylene and copolymer (PP and CO).

Dim (HxWxD, mm): 195 x 386 x 263
Colour: Black
Qt: 1
Carriage load (kg): 25,00 **Item No.: 146418**

TRT-0 CarryMore Trolley

Trolley for easy transport of CarryMore. Equipped with a large practical handle. Base that can be folded up to a vertical position and is held in place by magnets. Coupling lock for attaching the CarryMore, which can be adjusted to different heights. Can store and transport 4 pcs. CarryMore.
Load capacity is 80 kg.

Made of Polypropylene (PP), Copolymer (CO),
Steel and aluminum.

Dim (HxWxD, mm): 1100 x 400 x 570
Colour: Black/Aluminium
Qt: 1
Carriage load (kg): 80,00 **Item No.: 146425**

CarryMore Retaining Lock

Safety lock that helps to maintain and secure the contents during transport. The retaining lock can be locked by using a padlock or a pull-tight seal.

Made of Polypropylene (PP).

Dim (HxWxD, mm): 100 x 148 x 14
Colour: Black
Qt: 1
Item No.: 146494

CarryLite LMS

Location Management System

CarryLite LMS kitboxes come with double lids, which makes it possible to insert a description, layout of content or assembly instructions. The boxes also contain a click grid feature, where all CA-inserts are easily fixed to the bottom of the box to secure the contents during transportation.

CarryLite LMS kitboxes come in 2 different sizes either 4x8 and 5x10, and share the same height.

All boxes can be provided with ID-tags in different colours for colour coding each box to ensure quick identification of the right box and contents.



CL-LMS 80 4x8-0/DLU

CarryLite LMS 80 Compartment box with sandwich lid and U-profiles inside, which ensures that the contents remain in place during transportation. The sandwich lid holds up to 5 sheets of paper of 80 mg. The box has a Click-bottom for attachment of CA-inserts, 2 RFID holders inside the box and fixing holes in the lid and the top of the base for sealing the box. Fitted with sliding locks, handle and with red markers to indicate if box is closed correctly. Made of polypropylene (PP) and lid of polycarbonate (PC).

Dim (HxWxD, mm): 83 x 337 x 278
Colour: raaco blue
Qt: 1
Carriage load (kg): 10,00 **Item No.: 142540**

CL-LMS 80 4x8-0/DL

CarryLite LMS 80 Compartment box with sandwich lid without U-profiles. The sandwich lid holds up to 5 sheets of paper of 80 mg. The box has a Click-bottom for attachment of CA-inserts, 2 RFID holders inside the box and fixing holes in the lid and the top of the base for sealing the box. Fitted with sliding locks, handle and with red markers to indicate if box is closed correctly.

Made of polypropylene (PP) and lid of polycarbonate (PC).

Dim (HxWxD, mm): 83 x 337 x 278
Colour: raaco blue
Qt: 1
Carriage load (kg): 10,00 **Item No.: 142557**

CL-LMS 80 4x8-0

CarryLite LMS 80 4x8 with U-profiles inside the lid, which ensures that the contents remain in place during transportation. The box has a Click-bottom for attachment of CA-inserts, 2 RFID holders inside the box and fixing holes in the lid and the top of the base for sealing the box. Fitted with sliding locks, handle and with red markers to indicate if box is closed correctly.

Made of polypropylene (PP) and lid of polycarbonate (PC).

Dim (HxWxD, mm): 83 x 337 x 278
Colour: raaco blue
Qt: 1
Carriage load (kg): 10,00 **Item No.: 142885**

CL-LMS 80 5x10-0/DLU

CarryLite LMS 80 Compartment box with sandwich lid and U-profiles inside, which ensures that the contents remain in place during transportation. The sandwich lid holds up to 5 sheets of paper of 80 mg. The box has a Click-bottom for attachment of CA-inserts, 2 RFID holders inside the box and fixing holes in the lid and the top of the base for sealing the box. Fitted with sliding locks, handle and with red markers to indicate if box is closed correctly. Made of polypropylene (PP) and lid of polycarbonate (PC).

Dim (HxWxD, mm): 83 x 413 x 330
Colour: raaco blue
Qt: 1
Carriage load (kg): 13,00 **Item No.: 142502**

CL-LMS 80 5x10-0/DL

CarryLite LMS 80 Compartment box with sandwich lid without U-profiles. The sandwich lid holds up to 5 sheets of paper of 80 mg. The box has a Click-bottom for attachment of CA-inserts, 2 RFID holders inside the box and fixing holes in the lid and the top of the base for sealing the box. Fitted with sliding locks, handle and with red markers to indicate if box is closed correctly.

Made of polypropylene (PP) and lid of polycarbonate (PC).

Dim (HxWxD, mm): 83 x 413 x 330
Colour: raaco blue
Qt: 1
Carriage load (kg): 13,00

Item No.: 142519

CL-LMS 80 5x10-0

CarryLite LMS 80 5x10 with U-profiles inside the lid, which ensures that the contents remain in place during transportation. The box has a click bottom for attachment of CA inserts. 2 RFID holders inside the box and fixing holes in the lid and on top of the base for sealing the box. Fitted with sliding locks, handle and with red markers to indicate if box is closed correctly.

Made of polypropylene (PP) and lid of polycarbonate (PC).

Dim (HxWxD, mm): 83 x 413 x 330
Colour: raaco blue
Qt: 1
Carriage load (kg): 13,00

Item No.: 142878

Insert 80 CA8-1

All CA inserts have a click function on the bottom to hold the insert into place in the CarryLite LMS box. Can be used in all CarryLite LMS boxes with click bottom.

Made of polypropylene (PP).

Dim (HxWxD, mm): 69 x 55 x 79
Colour: Transparent
Qt: 32
Item No.: 142892

Insert 80 CA8-2

All CA inserts have a click function on the bottom to hold the insert into place in the CarryLite LMS box. Can be used in all CarryLite LMS boxes with click bottom.

Made of polypropylene (PP).

Dim (HxWxD, mm): 69 x 55 x 157
Colour: Transparent
Qt: 16
Item No.: 145015

Insert 80 CA8-3

All CA inserts have a click function on the bottom to hold the insert into place in the CarryLite LMS box. Can be used in all CarryLite LMS boxes with click bottom.

Made of polypropylene (PP).

Dim (HxWxD, mm): 69 x 55 x 235
Colour: Transparent
Qt: 9
Item No.: 145039

Insert 80 CA7-1

All CA inserts have a click function on the bottom to hold the insert into place in the CarryLite LMS box. Can be used in all CarryLite LMS boxes with click bottom.

Made of polypropylene (PP).

Dim (HxWxD, mm): 69 x 79 x 109
Colour: Transparent
Qt: 16
Item No.: 142908

Insert 80 CA7-1½

All CA inserts have a click function on the bottom to hold the insert into place in the CarryLite LMS box. Can be used in all CarryLite LMS boxes with click bottom.

Made of polypropylene (PP).

Dim (HxWxD, mm): 69 x 79 x 163
Colour: Transparent
Qt: 8
Item No.: 142915

Insert 80 CA7-2

All CA inserts have a click function on the bottom to hold the insert into place in the CarryLite LMS box. Can be used in all CarryLite LMS boxes with click bottom.

Made of polypropylene (PP).

Dim (HxWxD, mm): 69 x 79 x 218
Colour: Transparent
Qt: 8
Item No.: 144063

Insert 80 CA6-1

All CA inserts have a click function on the bottom to hold the insert into place in the CarryLite LMS box. Can be used in all CarryLite LMS boxes with click bottom.

Made of polypropylene (PP).

Dim (HxWxD, mm): 69 x 157 x 109
Colour: Transparent
Qt: 8
Item No.: 142922

Insert 80 CA8-1/55

All CA inserts have a click function on the bottom to hold the insert into place in the CarryLite LMS box. The depth of this insert is reduced to 46 mm and made especially for small parts. Can be used in all CarryLite LMS boxes with click bottom.

Made of polypropylene (PP).

Dim (HxWxD, mm): 69 x 55 x 79
Colour: Transparent
Qt: 32
Item No.: 145350

Insert 80 CA8-1/27

All CA inserts have a click function on the bottom to hold the insert into place in the CarryLite LMS box. The depth of this insert is reduced to 21 mm and made especially for small parts. Can be used in all CarryLite LMS boxes with click bottom.

Made of polypropylene (PP).

Dim (HxWxD, mm): 69 x 55 x 79
Colour: Transparent
Qt: 32
Item No.: 145336

Insert 80 CA9-1/55

All CA inserts have a click function on the bottom to hold the insert into place in the CarryLite LMS box. The depth of this insert is reduced to 46 mm and made especially for small parts. Can be used in all CarryLite LMS boxes with click bottom.

Made of polypropylene (PP).

Dim (HxWxD, mm): 69 x 39 x 55
Colour: Transparent
Qt: 64
Item No.: 145312

Insert 80 CA9-1/27

All CA inserts have a click function on the bottom to hold the insert into place in the CarryLite LMS box. The depth of this insert is reduced to 21 mm and made especially for small parts. Can be used in all CarryLite LMS boxes with click bottom.

Made of polypropylene (PP).

Dim (HxWxD, mm): 69 x 39 x 55
Colour: Transparent
Qt: 64
Item No.: 145299

CA-inserts come in different sizes, which gives a flexible configuration of the compartment box.

The inserts have a click´n grid feature to fix the inserts in to the bottom of the box. Can easily be unclicked from the bottom of the box and repositioned as needed.

Identify the content quickly - all inserts are made of a transparent plastic.

Made of plastic in a high quality plastic and tolerant to many different chemicals.

Inserts for

CarryLite LMS 4x8



CarryLite 4x8 is divided into 32 fields.

The following shows the inserts that can be used and how many fields they cover when combined in the boxes.

LMS inserts



CA8-1



CA8-2



CA8-3



CA7-1



CA7-1 1/2



CA7-2



CA6-1



CA8-1/55



CA8-1/27



CA9-1/55



CA9-1/27

Inserts for

CarryLite LMS 5x10



CarryLite 5x10 is divided into 50 fields.

The following shows the inserts that can be used and how many fields they cover when combined in the boxes.

LMS inserts



CA8-1



CA8-2



CA8-3



CA7-1



CA7-1 1/2



CA7-2



CA6-1



CA8-1/55



CA8-1/27



CA9-1/55



CA9-1/27

Accessories for CarryLite LMS

You can either replace, change or add accessories to your CarryLite LMS as needed.

ID-tags - can be used for colour coding and labelling to ensure quick identification

RFID holders - can securely hold RFID labels/tags free of dust etc.

BinFlag - a simple way for coding of the stock position and availability.

Pull-Tight seals - easy to secure the contents of the kitbox. Each Pull-Tight has its own code so it is easy to identify each kitbox.

CarryLite LMS ID-Tag

ID tags for colour coding and labeling.
Ensures fast identification of contents of Carrylite LMS boxes.
Contains 10 pcs./bag.

Dim (HxWxD, mm): 22 x 22 x 2,5
Colour: Yellow
Qt: 10
Item No.: 144315

CarryLite LMS ID-Tag

ID tags for colour coding and labeling.
Ensures fast identification of contents of Carrylite LMS boxes.
Contains 10 pcs./bag.

Dim (HxWxD, mm): 22 x 22 x 2,5
Colour: Grey
Qt: 10
Item No.: 145374

CarryLite LMS ID-Tag

ID tags for colour coding and labeling.
Ensures fast identification of contents of Carrylite LMS boxes.
Contains 10 pcs./bag.

Dim (HxWxD, mm): 22 x 22 x 2,5
Colour: raaco Grey
Qt: 10
Item No.: 144322

CarryLite LMS ID-Tag

ID tags for colour coding and labeling.
Ensures fast identification of contents of Carrylite LMS boxes.
Contains 10 pcs./bag.

Dim (HxWxD, mm): 22 x 22 x 2,5
Colour: Green
Qt: 10
Item No.: 144339

CarryLite LMS ID-Tag

ID tags for colour coding and labeling.
Ensures fast identification of contents of Carrylite LMS boxes.
Contains 10 pcs./bag.

Dim (HxWxD, mm): 22 x 22 x 2,5
Colour: Blue
Qt: 10
Item No.: 144285

CarryLite LMS ID-Tag

ID tags for colour coding and labeling.
Ensures fast identification of contents of Carrylite LMS boxes.
Contains 10 pcs./bag.

Dim (HxWxD, mm): 22 x 22 x 2,5
Colour: Red
Qt: 10
Item No.: 144292

CarryLite LMS ID-Tag

ID tags for colour coding and labeling.
Ensures fast identification of contents of Carrylite LMS boxes.
Contains 10 pcs./bag.

Dim (HxWxD, mm): 22 x 22 x 2,5
Colour: Orange
Qt: 10
Item No.: 144308

CarryLite LMS ID-Tag

ID tags for colour coding and labeling.
Ensures fast identification of contents of Carrylite LMS boxes.
Contains 10 pcs./bag.

Dim (HxWxD, mm): 22 x 22 x 2,5
Colour: Turquoise
Qt: 10
Item No.: 144346

CarryLite LMS ID-Tag

ID tags for colour coding and labeling.
Ensures fast identification of contents of Carrylite LMS boxes.
Contains 10 pcs./bag.

Dim (HxWxD, mm): 22 x 22 x 2,5
Colour: Black
Qt: 10
Item No.: 144629

Pull-Tight Seal WH/BL

With the Pull-tight seals it is easy to secure the content of the CarryLite. Each Pull-Tight seal has its own code so it is easy to identify each CarryLite.

Dim (length, mm): 180 mm
Colour: White / Blue
Qt: 2000
Item No.: 775007

Pull-Tight Seal WH/YE

With the Pull-tight seals it is easy to secure the content of the CarryLite. Each Pull-Tight seal has its own code so it is easy to identify each CarryLite.

Dim (length, mm): 180 mm
Colour: White / Yellow
Qt: 2000
Item No.: 775014

Pull-Tight Seal WH/RE

With the Pull-tight seals it is easy to secure the content of the CarryLite. Each Pull-Tight seal has its own code so it is easy to identify each CarryLite.

Dim (length, mm): 180 mm
Colour: White / Red
Qt: 2000
Item No.: 775021

BinFlag 4x8

BinFlag for CarryLite LMS 4x8 is a simple way for coding of the stock position and availability. RFID compatible and saves time on the workplace and provides overview and reduces errors.

Dim (HxWxD, mm): 45 x 80 x 10
Colour: Grey
Qt: 25
Item No.: 775045

BinFlag 5x10

BinFlag for CarryLite LMS 5x10 is a simple way for coding of the stock position and availability. RFID compatible and saves time on the workplace and provides overview and reduces errors.

Dim (HxWxD, mm): 50 x 112 x 10
Colour: Grey
Qt: 25
Item No.: 775038

CarryLite LMS RFID-holder 4x8

RFID holders (passive) for the CarryLite LMS 4x8 boxes can securely hold RFID labels/tags free of dust etc.

Dim (HxWxD, mm): 42 x 83 x 8,6
Colour: raaco Grey
Qt: 25
Item No.: 146104

CarryLite LMS RFID-holder 5x10

RFID holders (passive) for the CarryLite LMS 5x10 boxes can securely hold RFID labels/tags free of dust etc.

Dim (HxWxD, mm): 42 x 114 x 8,6
Colour: raaco Grey
Qt: 25
Item No.: 146081

Fastener fixing holes for safety and security

Foam inlay for assortment boxes

Sort out your tools

We can customise your foam inserts for all three systems – Boxxser, CarryLite and Assorter. Protect special tools or instruments during transport – and maintain a good overview.

The foam insert is custom made in our foam configurator as required, and is available in black, blue, red, yellow, green and light grey, combined with anthracite-grey at the top. The foam we use is a high-quality PE foam.

For further information or enquiries about foam and other special solutions, please contact raaco Great Britain on tel. +44 (01993) 776333 or gbmail@raaco.com

Your own combination of consumables, spare parts, screws, rivets, combined with the fitting tools encased foam, all well fitted into a CarryLite Kitbox...

Sample

Sample

Sample

Online box-configurator

Create your own personalised box in just a few steps with our innovative and user-friendly online box-configurator FOAMBOXX. Use our box-configurator to individually fill your personalised box with inserts and /or customized foam-inserts.

Please contact raaco on phone +45 54 88 84 00 or by mail@raaco.com to gain access to our online box-configurator FOAMBOXX – we will instantly create an account for you.

1 Create a new project. Manage as many projects as needed in your project-list.

2 Pick the box that best fits to your project needs from our wide range of available boxes.

3 Plan your box and add the inserts you need. Don´t worry about mix-ups: our editor will only offer inserts to fit your box.

4 If needed, add a custom foam insert to your box and fill in all the tools needed from our database.

5 Alternatively, use the FOAMBOXX scan-mat to add your own tools to the online box-configurators database.

6 The project-list shows all your custom boxes including prices. Shortly after assigning, you will receive your custom box.

raaco

raaco Toolboxes

- with space for productivity

Compact, ToolBag Pro and Open ToolBox are tool boxes that ensure overview and order at work.

Overview and order in day-to-day work
Our toolboxes make it easy to maintain order, as a practical solution to keep the tools you need to hand.

Choose between open or closed series, compact or soft boxes. Whichever you choose, you'll get a system in different sizes that can be customised to your requirements.

You need to keep the tools you require to hand and get the work done quickly, without wasting time looking for things.

Built-in flexibility
The toolbox accessories match the entire raaco product range, making the system future-proof.

Compact

ToolBag Pro

Open ToolBox

Compact

Light and surprisingly robust

Compact is a range of compact, ergonomic tool boxes in surprisingly solid, lightweight quality.

This spacious box has a two-part lid and an intelligently designed lock mechanism that fits completely flat along the sides when the box is open. It simply cannot be more compact and practical.

Compact comes in different sizes and with a wealth of practical accessories.

"Overview is important at work. Things are where they should be, saving me time. I can also stand on it and it can be stacked - really practical ."

Martin Steen,
electrician at Enelco ApS

Compact has won numerous awards -
ID Prize 1994, iF design award in 1991 and 1993,
Design Preis Schweiz 1991, Bundespreis product design 1992,
Annerkennung für Herausragendes produkt 1991 and
Design Zentrum Nordrhein Westfallen 1990.

1991

ID PRISEN 1994

product design award 1993

Compact 15

Compact 15 including dividers for sub-dividing the tote tray.
Contains 10 dividers.

Made of polypropylene (PP).

Dim (HxWxD, mm): 170 x 426 x 215
Colour: raaco blue
Qt: 4
Carriage load (kg): 20,00 **Item No.: 136563**

Compact 20

Compact 20 including assorted inserts. Flexible arrangement of compartments using inserts.
Contains 6 inserts.

Made of polypropylene (PP).

Dim (HxWxD, mm): 190 x 474 x 239
Colour: raaco blue
Qt: 5
Carriage load (kg): 30,00 **Item No.: 136570**

Compact 27

Compact 27 including assorted inserts. Flexible arrangement of compartments using inserts. 2 drawers for small items.
Contains 6 inserts.

Made of polypropylene (PP).

Dim (HxWxD, mm): 248 x 474 x 239
Colour: raaco blue
Qt: 4
Carriage load (kg): 30,00 **Item No.: 136587**

Compact 37

Compact 37 including assorted inserts and dividers. Flexible arrangement of compartments using inserts. Castors or a carrying strap can be fitted (extra accessory).
Contains 7 inserts.

Made of polypropylene (PP).

Dim (HxWxD, mm): 230 x 540 x 296
Colour: raaco blue
Qt: 1
Carriage load (kg): 40,00 **Item No.: 136594**

Compact 47

Compact 47 including assorted inserts and dividers.
Flexible arrangement of compartments using inserts.
2 drawers for small items. Castors or a carrying strap can be fitted (extra accessory).
Contains 7 inserts.

Made of polypropylene (PP).

Dim (HxWxD, mm): 292 x 540 x 296
Colour: raaco blue
Qt: 1
Carriage load (kg): 40,00 **Item No.: 136600**

Compact 50

Compact 50 including 10 assorted inserts and divider.
Flexible arrangement of compartments using inserts.
Castors or a carrying strap can be fitted (extra accessory).
Contains 10 inserts.

Made of polypropylene (PP).

Dim (HxWxD, mm): 260 x 621 x 311
Colour: raaco blue
Qt: 1
Carriage load (kg): 50,00 **Item No.: 136617**

Compact 62

Compact 62 incl. assorted inserts and divider.
Flexible arrangement of compartments using inserts.
4 drawers for small items. Castors or a carrying strap can be fitted (extra accessory).
Contains 10 inserts.

Made of polypropylene (PP).

Dim (HxWxD, mm): 322 x 621 x 311
Colour: raaco blue
Qt: 1
Carriage load (kg): 50,00 **Item No.: 136624**

Wheels for Compact

4 rubber castors for Compact 37, 47, 50, 62.

Dim (HxWxD, mm):
Colour: Black
Qt: 1
Item No.: 113656

Strap for Compact

Adjustable carrying strap for Compact 37, 47, 50 and 62.

Made of polycarbonate (PC).

Dim (HxWxD, mm):
Colour: Black
Qt: 4
Carriage load (kg): 50,00

Item No.: 114059

Open ToolBox

Open ToolBox is 100% functional. Nothing less. Open, simple and with easy access for tools and small items.

Open ToolBox is made of impact resistant quality plastic able to tolerate extreme temperatures. Carrying capacity of 25 kg.

Open ToolBox

Open Toolbox with 3 compartments for storage of tools and a drawer for small items and accessories. Tools not included.

Made of polypropylene (PP).

Dim (HxWxD, mm): 230 x 476 x 228
Colour: raaco blue
Qt: 4
Carriage load (kg): 25,00

Item No.: 137195

ToolBag Pro

Simple, hard-wearing and spacious

ToolBag Pro is made of hard-wearing, tough plastic and polyester. The sides are reinforced with two metal frames for extra stability.

The design is spacious, practical and open for rapid overview of the contents. The handle can be folded down to the side for easy access to the contents.

Available in different sizes.

"When I'm working on the site all day, having a Tool Bag Pro over my shoulder is really handy. I know where I've got all my tools. It's a good mate!"

Kim, joiner at Pilemand A/S

16" ToolBag Pro

16" professional tool bag with a large number of pockets. The tool bag is reinforced with a metal frame for stability, and the long hard plastic feet at the bottom protect the tools against wet surfaces. The bottoms of the pockets are reinforced in order to withstand the weight of tools and sharp objects. The strong metal handle with rubber grip can be tilted to the side providing easy access to content. Including removable, adjustable ergonomic shoulder strap. Tools not included. Made of polyester (PET).

Dim (HxWxD, mm): 264 x 419 x 206
Colour: raaco blue
Qt: 4
Carriage load (kg): 20,00 **Item No.: 760331**

20" ToolBag Pro

20" professional tool bag with a large number of pockets. The tool bag is reinforced with a metal frame for stability, and the long hard plastic feet at the bottom protect the tools against wet surfaces. The bottoms of the pockets are reinforced in order to withstand the weight of tools and sharp objects. The strong metal handle with rubber grip can be tilted to the side providing easy access to content. Including removable, adjustable ergonomic shoulder strap. Tools not included. Made of polyester (PET).

Dim (HxWxD, mm): 285 x 508 x 233
Colour: raaco blue
Qt: 2
Carriage load (kg): 25,00 **Item No.: 760348**

24" ToolBag Pro

24" professional tool bag with a large number of pockets. The tool bag is reinforced with a metal frame for stability, and the long hard plastic feet at the bottom protect the tools against wet surfaces. The bottoms of the pockets are reinforced in order to withstand the weight of tools and sharp objects. The strong metal handle with rubber grip can be tilted to the side providing easy access to content. Including removable, adjustable ergonomic shoulder strap. Tools not included. Made of polyester (PET).

Dim (HxWxD, mm): 324 x 626 x 264
Colour: raaco blue
Qt: 2
Carriage load (kg): 30,00 **Item No.: 760355**

Tool Trolley Proff

Practical and spacious

Tool Trolley Proff

Tool bag with wheels and telescopic handle, which is made of durable and tear-resistant polyester. Hard waterproof bottom and pockets both inside and outside for tools and accessories and fitted with Velcro to attach ToolFix (extra accessory). Tools not included.

Made of polyester (PET).

Dim (HxWxD, mm): 445 x 520 x 310
Colour: raaco blue
Qt: 1
Carriage load (kg): 25,00 **Item No.: 760232**

1/4 Tool Fix

Unique efficient holder for tools of any shape or size (max. Ø 30 mm). The holders core is made of flexible rubber, which allows for the storage of various types of tools side by side. The holder has a strong velcro for mounting inside of Tool Trolley Proff.

Made of polypropylene (PP) and thermoplastic elastomer (TPE).

Dim (HxWxD, mm): 150 x 118 x 40
Colour: Grey
Qt: 4
Item No.: 136020

1/2 Tool Fix

Unique efficient holder for tools of any shape or size (max. Ø 30 mm). The holders core is made of flexible rubber, which allows for the storage of various types of tools side by side. The holder has a strong velcro for mounting inside of Tool Trolley Proff.

Made of polypropylene (PP) and thermoplastic elastomer (TPE).

Dim (HxWxD, mm): 150 x 238 x 40
Colour: Grey
Qt: 2
Item No.: 136037

DEWALT

ToolCase

Designed for unbeatable durability and order

This is a tool case for professionals and discerning users. Overview and functionality are a matter of course. The ToolCase range is a highly robust and strong tool case series made from impact-resistant ABS, with cast aluminium frames. This gives unbeatable strength and durability.

All tool cases are designed for flexible adjustment and replacement of inserts and holders as required. Flexibility and overview are vital to maintaining order during a busy working day.

The series consists of different models - two of which are trolley versions.

"I can't always park close to the customer's address and having a wheeled case is simply fantastic."

Bjarne Ladevig,
Service Engineer, Zolutions ApS.

The ToolCase received the Red Dot Award 2014, the iF design award in 2013 and was nominated for a German Design Award in 2014.

ToolCase Premium XL - 68 / 2F Black

Tool case fitted with gas struts that make it both safe and easy to open and close. Features 2 Open ToolFix tool holders in the tray cover and an assortment of 5 inserts (series 55) within the tray itself. In the tool case there is a double-sided tool panel with 45 (28+17) tool holders plus a further single-sided panel with 23 tool holders plus a document holder. Tools not included.

Made of acrylonitrile butadiene styren (ABS) and aluminium.

Dim (HxWxD, mm): 410 x 485 x 215
Colour: Black
Qt: 1
Carriage load (kg): 35,00 **Item No.: 146340**

ToolCase Premium XL - 23 / 6F Black

Tool case fitted with gas struts that make it both safe and easy to open and close. Features 2 Open ToolFix tool holders in the tray cover and an assortment of 5 inserts (series 55) within the tray itself. In the tool case there is a double-sided tool panel with 45 (28+17) tool holders plus a further single-sided panel with 23 tool holders plus a document holder. Tools not included.

Made of acrylonitrile butadiene styren (ABS) and aluminium.

Dim (HxWxD, mm): 410 x 485 x 215
Colour: Black
Qt: 1
Carriage load (kg): 35,00 **Item No.: 146357**

ToolCase Premium XLT - 68 / 2F Black

Rolling tool case fitted with gas struts that make it both safe and easy to open and close. Features 2 Open ToolFix tool holders in the tray cover and an assortment of 5 inserts (series 55) within the tray itself. In the tool case there is a double-sided tool panel with 45 (28+17) tool holders plus a further single-sided panel with 23 tool holders plus a document holder. Tools not included.

Made of acrylonitrile butadiene styren (ABS) and aluminium.

Dim (HxWxD, mm): 410 x 485 x 250
Colour: Black
Qt: 1
Carriage load (kg): 35,00 **Item No.: 146364**

ToolCase Premium XLT - 23 / 6F Black

Rolling tool case fitted with gas struts that make it both safe and easy to open and close. Features 2 Open ToolFix tool holders in the tray cover and an assortment of 5 inserts (series 55) within the tray itself. In the tool case there is a double-sided tool panel with 4 Open ToolFix tool holders plus a further single-sided panel with 23 tool holders plus a document holder. Tools not included.

Made of acrylonitrile butadiene styren (ABS) and aluminium.

Dim (HxWxD, mm): 410 x 485 x 250
Colour: Black
Qt: 1
Carriage load (kg): 35,00 **Item No.: 146371**

Tool Panel TPDS-28/17-XL

Tool panel. Fitted with two straps to keep tool panel at a 30 degree angle for easy access to tools, 45 elasticated tool holders in two different sizes and a panel holder for simple mounting of tool panel into the case. 28 Tool holders size S (10-20mm). 17 Tool holders size M (20-30mm). Suitable for XL-models only.

Made of polypropylene (PP) and polyester (PET).

Dim (HxW, mm): 295 x 410
Colour: Black
Qt: 1
Item No.: 146890

Tool Panel TPDS-4xOpenFix-XL

Tool panel. Fitted with two straps to keep tool panel at a 30 degree position for easy access to tools, 4 raaco ToolFix tool holders and a panel holder for simple and secure mounting of tool panel into the case. 2 x 2 raaco ToolFix (1-25mm). Suitable for XL-models only.

Made of polypropylene (PP) and polyester (PET).

Dim (HxW, mm): 295 x 410
Colour: Black
Qt: 1
Item No.: 146869

Tool Panel TPSS-23/1-XL

Tool panel. Complete with 23 elasticated tool holders in two sizes, a document holder and a panel holder for simple and secure mounting of tool panel into the case. 14 Tool holders size S (10-20mm). 9 Tool holders size M (20-30mm). 1 document holder. Panel holder with tool guard. Suitable for XL-models only.

Made of polypropylene (PP) and polyester (PET).

Dim (HxW, mm): 295 x 410
Colour: Black
Qt: 1
Item No.: 146876

Tool Panel LP-2xOpenFix-XL

Combined tool holder and lid for bottom tray. Mounted with a strap to keep lid open, foam on the underside to keep contents in place and 2 raaco ToolFix tool holders on top surface of the lid.

Made of polypropylene (PP) and polyester (PET).

Dim (HxW, mm): 340 x 410
Colour: Black
Qt: 1
Item No.: 146883

Divider 55 XL

Divider for ToolCase. For tray 55 XL. Transverse.
Contains 2 pcs./bag.

Dim (HxWxD, mm): 46 x 330 x 7
Colour: Black
Qt: 3
Item No.: 140768

Divider 55 L/XL

Divider for ToolCase. For tray 55 L and XL. Longitudinal.
Contains 2 pcs./bag.

Dim (HxWxD, mm): 46 x 429 x 10
Colour: Black
Qt: 3
Item No.: 140782

TSA Lock for ToolCase

Set consisting of 2 TSA locks making it possible to change standard lock in ToolCase to TSA lock.

Dim (HxWxD, mm):
Colour: Aluminium
Qt: 12
Item No.: 143592

Solid Box

Maximum space utilisation

raaco Solid is a series of boxes you can use for almost anything.

The boxes are made of very strong polypropylene, and are both shock-resistant and resistant towards water and dust.

Solid is designed to ensure maximum space utilization. The boxes can be stacked on top of each other, and they fit perfectly onto transport pallets, which reduces transportation costs.

The boxes are available in three different sizes, and can be both locked and sealed.

Solid 1

Small transport box, which is water, dust and shock resistant. Two click locks and integrated handle. Can be secured with padlock. Solid 1, 2 and 3 can be stacked on top of each other.

Made of polypropylene (PP).

Dim (HxWxD, mm): 125 x 275 x 175
Colour: raaco blue
Qt: 8
Carriage load (kg): 15,00 **Item No.: 136754**

Solid 2

Medium transport box, which is water, dust and shock resistant. Two click locks and integrated handle. Can be secured with padlock. Solid 1, 2 and 3 can be stacked on top of each other.

Made of polypropylene (PP).

Dim (HxWxD, mm): 170 x 370 x 275
Colour: raaco blue
Qt: 4
Carriage load (kg): 25,00 **Item No.: 136761**

Solid 3

Large transport box, which is water, dust and shock resistant. Two click locks and integrated handle. Can be secured with padlock. Solid 1, 2 and 3 can be stacked on top of each other.

Made of polypropylene (PP).

Dim (HxWxD, mm): 170 x 570 x 370
Colour: raaco blue
Qt: 1
Carriage load (kg): 35,00 **Item No.: 136778**

Toolchest

Spacious storage on wheels

The raaco Toolchest is a spacious chest that you can use to store and transport large machinery, tools and much more.

The chest is equipped with wheels and an ergonomic handle, and includes two practical tool trays. It is possible to fasten tools in the lid.

The Toolchest can be locked with a padlock.

Available in different sizes.

Toolchest 75

Large storage box for large equipment and tools.
User-friendly design with wheels and handle. 2 internal tray's and click locks. Can be secured with padlocks. Tools can be mounted inside the lid. Tools not included.

Volume: 75 l.

Made of polypropylene (PP)

Dim (HxWxD, mm): 416 x 675 x 472
Colour: Dark grey / Blue
Qt: 1
Carriage load (kg): 75,00

Item No.: 715706

Toolchest 100

Large storage box for large equipment and tools.
User-friendly design with wheels and handle. 2 internal tray's and click locks. Can be secured with padlocks. Tools can be mounted inside the lid. Maximal storage. Tools not included.

Volume: 100 l.

Made of polypropylene (PP)

Dim (HxWxD, mm): 493 x 775 x 472
Colour: Dark grey / Blue
Qt: 1
Carriage load (kg): 100,00

Item No.: 715720

FlightCase

Practical, water and dust proof case

raaco FlightCase is a series of water and dust proof cases, which meet the requirements of ISO IP67.

The cases are made of high grade plastics (PP) which is resistant to chemicals and suitable for use in the majority of environments and in cold weather (-20 C). The piston valve levels out pressure when the cases are transported in air cargo.

The practical and robust design ensures a light-weight case that is easy to clean, protects the surface agains scratches and is stable when standing upwards. You can both sit and stand on your raaco FlightCase. The locks are easy to open and close - even with one hand. The holes attached to top and bottom makes it possible to lock and seal the case.

FlightCase 3

raaco FlightCase 3 is a water and dust proof case. The piston valve levels out pressure when the cases are transported in air cargo. The holes on both top and bottom makes it possible to lock and seal it. The inner space can be adjusted to accommodate the required items with layers of soft foam.
raaco FlightCase meets the requirements from ISO IP67.

Made of polypropylene (PP)

Dim (HxWxD, mm): 148 x 336 x 300
Colour: Black
Qt: 1
Carriage load (kg): 30,00 **Item No.: 738002**

FlightCase 4

raaco FlightCase 4 is a water and dust proof case. The piston valve levels out pressure when the cases are transported in air cargo. The holes on both top and bottom makes it possible to lock and seal it. The inner space can be adjusted to accommodate the required items with layers of soft foam.
raaco FlightCase meets the requirements from ISO IP67.

Made of polypropylene (PP)

Dim (HxWxD, mm): 176 x 464 x 366
Colour: Black
Qt: 1
Carriage load (kg): 30,00 **Item No.: 738019**

FlightCase 5

raaco FlightCase 5 is a water and dust proof case. The piston valve levels out pressure when the cases are transported in air cargo. The holes on both top and bottom makes it possible to lock and seal it. The inner space can be adjusted to accommodate the required items with layers of soft foam.
raaco FlightCase meets the requirements from ISO IP67.

Made of polypropylene (PP)

Dim (HxWxD, mm): 211 x 555 x 428
Colour: Black
Qt: 1
Carriage load (kg): 30,00 **Item No.: 738026**

raaco Storage Cabinets

- Order, overview and easy access

Despite the simple design, the cabinets are extremely functional and can hold large quantities of small parts. This makes them a good choice when you want to make the most of your space.

All cabinets have the same width, so that you can easily combine them into larger systems, to get the required overview, saved space, mobility and access.

The shelves are made from galvanized, coated steel, which does not rust, with drawers of durable, transparent plastic, making it easy to identify the contents.

Due to investment in a new, environmental friendly paint plant, the quality of the paintwork of the cabinets itself has been further improved.

You can combine the cabinets with raaco's tool panels and storage boxes, to create a comprehensive system that you can expand as required. Choose between stationary and mobile solutions.

Storage Cabinets System 150

Storage Cabinets System 250

Cabinet Tuntable

Cabinet Rack

Storage Cabinet System 150

A solution to every need

raaco's range of 150 cabinets includes shelves of different heights and with different drawer sizes.

The shelves are made from coated steel, with drawers of durable, transparent plastic, making it easy to identify the contents.

You can combine the cabinets with raaco's tool panels and storage boxes, to create a comprehensive system that you can expand as required.

Cabinet 1260-00

Cabinet with drawers of type 150-00.
Each drawer can be divided into 4 compartments using dividers (extra accessory). Contains 60 drawers.

Made of painted steel and drawers of polypropylene (PP).

Dim (HxWxD, mm): 552 x 306 x 150
Colour: raaco blue
Qt: 1
Carriage load (kg): 39,60 **Item No.: 137386**

Cabinet 1248-01

Cabinet with drawers of type 150-01.
Each drawer can be divided into 16 compartments using dividers (extra accessory). Contains 48 drawers.

Made of painted steel and drawers of polypropylene (PP).

Dim (HxWxD, mm): 552 x 306 x 150
Colour: raaco blue
Qt: 1
Carriage load (kg): 39,60 **Item No.: 137393**

Cabinet 1224-02

Cabinet with drawers of type 150-02.
Each drawer can be divided into 3 compartments using dividers (extra accessory). Contains 24 drawers.

Made of painted steel and drawers of polypropylene (PP).

Dim (HxWxD, mm): 552 x 306 x 150
Colour: raaco blue
Qt: 1
Carriage load (kg): 29,70 **Item No.: 137409**

Cabinet 1208-03

Cabinet with drawers of type 150-03.
Each drawer can be divided into 4 compartments using dividers (extra accessory). Contains 8 drawers.

Made of painted steel and drawers of polypropylene (PP).

Dim (HxWxD, mm): 552 x 306 x 150
Colour: raaco blue
Qt: 1
Carriage load (kg): 29,70 **Item No.: 137416**

Cabinet 1216-04

Cabinet with drawers of type 150-04.
Each drawer can be divided into 4 compartments using dividers (extra accessory). Contains 16 drawers.

Made of painted steel and drawers of polypropylene (PP).

Dim (HxWxD, mm): 552 x 306 x 150
Colour: raaco blue
Qt: 1
Carriage load (kg): 26,40 **Item No.: 137423**

Cabinet 1240-123

Cabinet with 40 assorted drawers. 36 pcs. of type 150-01, 3 pcs. of type 150-02 and 1 pc. Of type 150-03.
Drawers can be divided using dividers (extra accessory).
Contains 40 drawers.

Made of painted steel and drawers of polypropylene (PP).

Dim (HxWxD, mm): 552 x 306 x 150
Colour: raaco blue
Qt: 1
Carriage load (kg): 36,30 **Item No.: 137430**

Cabinet Turntable 1200

Turntable. Can be fitted with any 12x1200 series cabinets.

Without cabinets.

Made of steel.

Dim (HxØ, mm): 1760 x 680
Colour: raaco blue
Qt: 1
Carriage load (kg): 480,00 **Item No.: 137447**

Cabinet 945-00

Cabinet with drawers of type 150-00.
Each drawer can be divided into 4 compartments using dividers (extra accessory). Contains 45 drawers.

Made of painted steel and drawers of polypropylene (PP).

Dim (HxWxD, mm): 417 x 306 x 150
Colour: raaco blue
Qt: 1
Carriage load (kg): 30,00 **Item No.: 137454**

Cabinet 936-01

Cabinet with drawers type of 150-01.
Each drawer can be divided into 16 compartments using dividers (extra accessory). Contains 36 drawers.

Made of painted steel and drawers of polypropylene (PP).

Dim (HxWxD, mm): 417 x 306 x 150
Colour: raaco blue
Qt: 1
Carriage load (kg): 30,00 **Item No.: 137461**

Cabinet 918-02

Cabinet with drawers of type 150-02.
Each drawer can be divided into 3 compartments using dividers (extra accessory). Contains 18 drawers.

Made of painted steel and drawers of polypropylene (PP).

Dim (HxWxD, mm): 417 x 306 x 150
Colour: raaco blue
Qt: 1
Carriage load (kg): 20,00 **Item No.: 137478**

Cabinet 906-03

Cabinet with drawers of type 150-03.
Each drawer can be divided into 4 compartments using dividers (extra accessory). Contains 6 drawers.

Made of painted steel and drawers of polypropylene (PP).

Dim (HxWxD, mm): 417 x 306 x 150
Colour: raaco blue
Qt: 1
Carriage load (kg): 20,00 **Item No.: 137485**

Cabinet 928-123

Cabinet with 28 assorted drawers. 24 pcs. of type 150-01, 3 pcs. of type 150-02 and 1 pc. Of type 150-03.
Each drawer can be divided using dividers (extra accessory).
Contains 28 drawers.

Made of painted steel and drawers of polypropylene (PP).

Dim (HxWxD, mm): 417 x 306 x 150
Colour: raaco blue
Qt: 1
Carriage load (kg): 26,40 **Item No.: 137492**

Cabinet Turntable 900



Turntable. Can be fitted with any 12x900 series cabinets.

Without cabinets.

Made of steel.

Dim (HxØ, mm): 1600 x 680
Colour: raaco blue
Qt: 1
Carriage load (kg): 480,00

Item No.: 137515

Cabinet Rack 900

Free-standing rack. Can be fitted with 12 pcs. of 900 series cabinets. Handles & Castors also available (extra accessory).

Without cabinets.

Made of steel.

Dim (HxWxD, mm): 1600 x 622 x 570
Colour: raaco blue
Qt: 1
Carriage load (kg): 450,00

Item No.: 137522

Cabinet 630-00

Cabinet with drawers of type 150-00.
Each drawer can be divided into 4 compartments using dividers (extra accessory). Contains 30 drawers.

Made of painted steel and drawers of polypropylene (PP).

Dim (HxWxD, mm): 283 x 306 x 150
Colour: raaco blue
Qt: 1
Carriage load (kg): 19,80 **Item No.: 137539**

Cabinet 624-01

Cabinet with drawers of type 150-01.
Each drawer can be divided into 16 compartments using dividers (extra accessory). Contains 24 drawers.

Made of painted steel and drawers of polypropylene (PP).

Dim (HxWxD, mm): 283 x 306 x 150
Colour: raaco blue
Qt: 1
Carriage load (kg): 19,80 **Item No.: 137546**

Cabinet 612-02

Cabinet with drawers of type 150-02.
Each drawer can be divided into 3 compartments using dividers (extra accessory). Contains 12 drawers.

Made of painted steel and drawers of polypropylene (PP).

Dim (HxWxD, mm): 283 x 306 x 150
Colour: raaco blue
Qt: 1
Carriage load (kg): 13,00 **Item No.: 137553**

Cabinet 616-123

Cabinet with 16 assorted drawers. 12 pcs. of type 150-01, 3 pcs. of type 150-02 and 1 pc. of type 150-03.
Each drawer can be divided using dividers (extra accessory). Contains 16 drawers.

Made of painted steel and drawers of polypropylene (PP).

Dim (HxWxD, mm): 283 x 306 x 150
Colour: raaco blue
Qt: 1
Carriage load (kg): 16,50 **Item No.: 137560**

Drawer 150-00

Drawer type 150-00, which can be used in cabinet type 1260-00, 945-00 and 630-00. The drawer can be sub-divided using dividers (extra accessory). Made of polypropylene (PP).

Dim (HxWxD, mm): 41 x 55 x 153 Carriage load (kg): 0,50
Colour: Transparent
Qt: 120 **Item No.: 108980**

Divider 150-00

Dividers for drawer type 150-00. Contains 60 pcs/bag.
Made of polypropylene (PP).

Dim (HxWxD, mm): 32 x 52 x 1,6
Colour: Transparent
Qt: 25 **Item No.: 101981**

Label 150-00

Label for drawer type 150-00.
Contains 60 pcs/bag.

Dim (HxWxD, mm): 10 x 52 x 1
Colour: White
Qt: 25 **Item No.: 109024**

Drawer 150-01

Drawer type 150-01. Can be used in cabinet type 1248-01, 1240-123, 936-01, 928-123, 624-01 and 616-123. The drawer can be sub-divided using dividers (extra accessory). Made of polypropylene (PP).

Dim (HxWxD, mm): 41 x 67 x 153 Carriage load (kg): 0,80
Colour: Transparent
Qt: 96 **Item No.: 104692**

Divider 150-01 small

Dividers for drawer type 150-01. Contains 72 pcs/bag.
Made of polypropylene (PP).

Dim (HxWxD, mm): 31 x 32 x 1,4
Colour: Transparent
Qt: 25 **Item No.: 111393**

Divider 150-01 medium

Dividers for drawer type 150-01. Contains 48 pcs/bag.
Made of polypropylene (PP).

Dim (HxWxD, mm): 31 x 64 x 1,4
Colour: Transparent
Qt: 25 **Item No.: 101998**

Divider 150-01 large

Dividers for drawer type 150-01. Contains 24 pcs/bag.
Made of polypropylene (PP).

Dim (HxWxD, mm): 49 x 87 x 4,8
Colour: Transparent
Qt: 25 **Item No.: 111386**

Label 150-01

Label for drawer type 150-01.
Contains 48 pcs/bag.

Dim (HxWxD, mm): 10 x 64 x 1
Colour: White
Qt: 25 **Item No.: 107761**

Drawer 150-02

Drawer type 150-02, which can be used in cabinet type 1224-02, 1240-123, 918-02, 928-123, 612-02 and 616-123. The drawer can be sub-divided using dividers (extra accessory). Made of polypropylene (PP).

Dim (HxWxD, mm): 64 x 154 x 91 Carriage load (kg): 1,00
Colour: Transparent
Qt: 48 **Item No.: 104715**

Divider 150-02

Dividers for drawer type 150-02. Contains 24 pcs/bag.
Made of polypropylene (PP).

Dim (HxWxD, mm): 49 x 87 x 2
Colour: Transparent
Qt: 25 **Item No.: 102032**

Label 150-02

Label for drawer 150-02.
Contains 24 pcs/bag.

Dim (HxWxD, mm): 18 x 87 x 1
Colour: White
Qt: 25 **Item No.: 107778**

Drawer 150-03

Drawer type 150-03, which can be used in cabinet type 1208-03, 1240-123, 906-03, 928-123 and 616-123. The drawer can be sub-divided using dividers (extra accessory). Made of polypropylene (PP).

Dim (HxWxD, mm): 64 x 279 x 155 Carriage load (kg): 3,30
Colour: Transparent
Qt: 16 **Item No.: 104708**

Divider 150-03/04

Dividers for drawer type 150-03 and 150-04. Contains 16 pcs/bag.
Made of polypropylene (PP).

Dim (HxWxD, mm): 50 x 134 x 1,8
Colour: Transparent
Qt: 25 **Item No.: 102049**

Label 150-03

Label for drawer type 150-03. Contains 8 pcs/bag.
Made of polypropylene (PP).

Dim (HxWxD, mm): 18 x 275 x 1
Colour: White
Qt: 25 **Item No.: 107785**

Drawer 150-04

Drawer type 150-04, which can be used in cabinet type 1216-04.
The drawer can be sub-divided using dividers (extra accessory).
Made of polypropylene (PP).

Dim (HxWxD, mm): 64 x 139 x 155 Carriage load (kg): ???
Colour: Transparent
Qt: 32 **Item No.: 109178**

Label 150-04

Label for drawer type 150-04. Contains 16 pcs/bag.
Made of polypropylene (PP).

Dim (HxWxD, mm): 18 x 135 x 1
Colour: White
Qt: 25 **Item No.: 109017**

Handles & Castors with brake

4 rubber tyred castors (2 fitted with brakes) and 2 handles for fitting on Cabinet Rack 900.

Dim (HxWxD, mm):
Colour: Black
Qt: 1 **Item No.: 112369**

Storage Cabinet System 250

A solution to every need

raaco's range of 250 cabinets includes drawers in different sizes.

The shelves are made from coated steel, with drawers of durable, transparent plastic, making it easy to identify the contents.

You can combine the cabinets with raaco's tool panels and storage boxes, to create a comprehensive system that you can expand as required.

Cabinet 250 / 24-1

Cabinet with drawers of type 250-1.
Each drawer can be divided into 4 compartments using dividers (extra accessory). Contains 24 drawers.

Made of painted steel and drawers of polypropylene (PP).

Dim (HxWxD, mm): 435 x 357 x 255
Colour: raaco blue
Qt: 1
Carriage load (kg): 75,00 **Item No.: 137577**

Cabinet 250 / 8-2

Cabinet with drawers of type 250-2.
Each drawer can be divided into 4 compartments using dividers (extra accessory). Contains 8 drawers.

Made of painted steel and drawers of polypropylene (PP).

Dim (HxWxD, mm): 435 x 357 x 255
Colour: raaco blue
Qt: 1
Carriage load (kg): 50,00 **Item No.: 137584**

Cabinet 250 / 6-3

Cabinet with drawers of type 250-3 drawers.
Each drawer can be sub-divided using inserts (extra accessory).
Contains 6 drawers.

Made of painted steel and drawers of polypropylene (PP).

Dim (HxWxD, mm): 435 x 357 x 255
Colour: raaco blue
Qt: 1
Carriage load (kg): 75,00 **Item No.: 137591**

Handles & Castors with brake

4 rubber tyred castors (2 fitted with brakes) and 2 handles for fitting on Rack Cabinet 250.

Dim (HxWxD, mm):
Colour: Black
Qt: 1
Carriage load (kg): **Item No.: 112369**

Cabinet Turntable 250

Turntable. Can be fitted with any 12x250 series cabinets.

Without cabinets.

Made of steel.

Dim (HxØ, mm): 1600 x 880
Colour: raaco blue
Qt: 1
Carriage load (kg): 480,00

Item No.: 137607

Rack Cabinet 250

Free standing rack. Can be fitted with any 12x 250 series cabinets. Handles & Castors are also available.

Without cabinets.

Made of steel.

Dim (HxWxD, mm): 1600 x 705 x 570
Colour: raaco blue
Qt: 1
Carriage load (kg): 450,00

Item No.: 137614

Drawer 250-01

Drawer, type 250-1 for cabinet type 250/24-1.
Can be subdivided using dividers (extra Accessory).

Made of polypropylene (PP).

Dim (HxWxD, mm): 58 x 80 x 239
Colour: Transparent
Qt: 48
Carriage load (kg): 1,60 **Item No.: 107273**

Divider 250-01

Dividers for drawer type 250-01.
Contains 36 pcs./bag.

Made of polypropylene (PP).

Dim (HxWxD, mm): 46 x 75 x 3,2
Colour: Transparent
Qt: 24
Item No.: 106757

Label 250-01

Label for drawer 250-01.
Contains 24 pcs./bag.

Dim (HxWxD, mm): 15 x 75 x 1
Colour: White
Qt: 25
Item No.: 107792

Drawer 250-02

Drawer, type 250-2 for cabinet type 250-8/2.
Can be subdivided using dividers (extra accessory).

Made of polypropylene (PP).

Dim (HxWxD, mm): 92 x 159 x 239
Colour: Transparent
Qt: 16
Carriage load (kg): 3,10 **Item No.: 107259**

Divider 250-02

Dividers for drawer type 250-02.
Contains 12 pcs./bag.

Made of polypropylene (PP).

Dim (HxWxD, mm): 80 x 154 x 3,2
Colour: Transparent
Qt: 12
Item No.: 106764

Label 250-02

Label for drawer 250-02.
Contains 8 pcs./bag.

Dim (HxWxD, mm): 32 x 155 x 1
Colour: White
Qt: 25
Item No.: 107815

Drawer 250-03

Drawer, type 250-3 for cabinet type 250/6-3.
Can be sub-divided using any inserts 55 (extra accessory).

Made of polypropylene (PP).

Dim (HxWxD, mm): 57 x 320 x 240
Colour: Transparent
Qt: 7
Carriage load (kg):
Item No.: 103114

Label 250-03

Label for drawer 250-03.
Contains 6 pcs./bag.

Dim (HxWxD, mm): 15 x 315 x 1
Colour: White
Qt: 25
Item No.: 107822

Shelving System

An extremely stable system

Shelving system 450 basically consists of two parts: shelves and posts.

The very sturdy structure means that the individual sections can be assembled without any need for cross bracing. The shelves are mounted with just one screw and one bracket per corner – it couldn't be simpler!

Start with a single section and then add two extra posts and a number of shelves – to get 2 sections. In principle, you can expand your system indefinitely. The more you build, the more stable your shelving will be.

To make the most of your space, combine the shelving with the accessory shelving bins and drawers.

Both drawers and bins have handles for easy carrying. They also have a restraining edge to allow them to be pulled fully out without falling from the shelving. By adding partitions to your drawers, you can sort and mark the contents clearly for each compartment.

raaco has developed several different fixed shelving systems. Before you choose which version you require, you should consider how much your shelving bins need to hold. Then you can find an appropriate solution within the range.

S450-31 1M Set5+8

Shelving in 200 cm. with
5 shelves. Easy to assemble.
Carrying capacity 100 kg.
per shelf evenly loaded.
Can be constructed in either
1 full height or 2 half height
bays.

Unassembled.

Made of galvanized steel.

Dim (HxWxD, mm): 2000 x 920 x 340
Colour: Galvanized
Qt: 1
Carriage load (kg): 500,00 **Item No.: 144728**

S450-40 1M Set5+8

Shelving in 200 cm. with
5 shelves. Easy to assemble.
Carrying capacity 100 kg.
per shelf evenly loaded.
Can be constructed in either
1 full height or 2 half height
bays.

Unassembled.

Made of galvanized steel.

Dim (HxWxD, mm): 2000 x 920 x 430
Colour: Galvanized
Qt: 1
Carriage load (kg): 500,00 **Item No.: 144735**

Post 1000 x 4

4 uprights with 1 m height, 2 units can be connected to make a
2 m pole. Supplied with connectors and end caps.

Made of galvanized steel.

Dim (HxWxD, mm): 1000 x 31 x 31
Colour: Galvanized
Qt: 4
Item No.: 136853

Shelf 90-31 x 3

Shelf, 310 mm deep.
Load capacity 100 kg per shelf, weight evenly distributed.
(Safety factor 2).

Made of galvanized steel.

Dim (HxWxD, mm): 36 x 885 x 310
Colour: Galvanized
Qt: 3
Carriage load (kg): 100,00 **Item No.: 125543**

Shelf 90-31 x 5

Shelf, 310 mm deep.
Load capacity 100 kg per shelf, weight evenly distributed.
(Safety factor 2).

Made of galvanized steel.

Dim (HxWxD, mm): 36 x 885 x 310
Colour: Galvanized
Qt: 5
Carriage load (kg): 100,00 **Item No.: 118835**

Shelf 90-40 x 3

Shelf, 400 mm deep.
Load capacity 100 kg per shelf, weight evenly distributed.
(Safety factor 2).

Made of galvanized steel.

Dim (HxWxD, mm): 36 x 885 x 400
Colour: Galvanized
Qt: 3
Carriage load (kg): 100,00 **Item No.: 118842**

Shelf 90-40 x 5

Shelf, 400 mm deep.
Load capacity 100 kg per shelf, weight evenly distributed.
(Safety factor 2).

Made of galvanized steel.

Dim (HxWxD, mm): 36 x 885 x 400
Colour: Galvanized
Qt: 5
Carriage load (kg): 100,00 **Item No.: 126182**

Shelf Bin 4-800

Shelf bin for 310 mm shelf (type 90-31).
There must be a distance of 4 holes between the shelves.
The bin can be divided using dividers and can be fixed with a front plate and label (extra accessory).

Made of polypropylene (PP).

Dim (HxWxD, mm): 100 x 280 x 375
Colour: raaco blue
Qt: 12
Carriage load (kg): 15,00 **Item No.: 136693**

Shelf Bin 5-600

Shelf bin for 310 mm shelf (type 90-31), with rear grip.
There must be a distance of 5 holes between the shelves.
The bin can be fixed with a label (extra accessory).

Made of polypropylene (PP).

Dim (HxWxD, mm): 111 x 168 x 375
Colour: raaco blue
Qt: 15
Carriage load (kg): 10,00 **Item No.: 136709**

Shelf Bin 6-1100

Shelf bin for 310 mm shelf (type 90-31), with rear grip.
There must be a distance of 6 holes between the shelves.
The bin can be fixed with a label (extra accessory).

Made of polypropylene (PP).

Dim (HxWxD, mm): 136 x 210 x 375
Colour: raaco blue
Qt: 12
Carriage load (kg): 15,00 **Item No.: 136716**

Shelf Bin 8-2000

Shelf bin for 310 mm shelf (type 90-31), with rear grip.
There must be a distance of 8 holes between the shelves.
The bin can be fixed with a label (extra accessory).

Made of polypropylene (PP).

Dim (HxWxD, mm): 186 x 280 x 375
Colour: raaco blue
Qt: 6
Carriage load (kg): 30,00 **Item No.: 136723**

Shelf Bin 7-1600

Shelf bin for 400 mm shelf (type 90-40), with rear grip.
There must be a distance of 7 holes between the shelves.
The bin can be fixed with a label (extra accessory).

Made of polypropylene (PP).

Dim (HxWxD, mm): 161 x 210 x 465
Colour: raaco blue
Qt: 12
Carriage load (kg): 25,00 **Item No.: 136730**

Shelf Bin 9-2800

Shelf bin for 400 mm shelf (type 90-40), with rear grip.
There must be a distance of 9 holes between the shelves.
The bin can be fixed with a label (extra accessory).

Made of polypropylene (PP).

Dim (HxWxD, mm): 211 x 280 x 465
Colour: raaco blue
Qt: 6
Carriage load (kg): 45,00 **Item No.: 136747**

Divider 4-800 small

Divider for Shelf Bin 4-800, Small.
Contains 36 pcs./bag.

Made of polystyrene (PS).

Dim (HxWxD, mm): 77 x 84 x 20
Colour: Transparent
Qt: 12
Item No.: 108010

Divider 4-800 medium



Divider for Shelf Bin 4-800, Medium.
Contains 24 pcs./bag.

Made of polystyrene (PS).

Dim (HxWxD, mm): 77 x 128 x 20
Colour: Transparent
Qt: 12
Item No.: 108003

Divider 4-800 large



Divider for Shelf Bin 4-800, Large.
Contains 12 pcs./bag.

Made of polystyrene (PS).

Dim (HxWxD, mm): 77 x 317 x 8
Colour: Transparent
Qt: 12
Item No.: 107617

Front 4-800 / label



Front plate/label for 4-800 shelf drawer.
Contains 6 pcs./bag.

Made of polystyrene (PS).

Dim (HxWxD, mm): 50 x 260 x 0
Colour: Transparent
Qt: 8
Item No.: 107600

Label for Shelf Bins

Labels for shelf bins.
Contains 12 pcs./bag.

Dim (HxWxD, mm): 26 x 104 x 1
Colour: White
Qt: 25
Item No.: 111362

Shelving 8-2000

Shelving with 9 pcs. shelf 90-31. 8 pcs. 1000 post and 24 pcs. Shelf Bin 8-2000. Unassembled.

Dim (HxWxD, mm): 2000 x 920 x 340
Colour: Galvanized / raaco blue
Qt: 1
Item No.: 181112

Shelving 4-800

Shelving with 14 pcs. Shelf 90-31. 8 pcs. Post 1000 and 36 pcs. Shelf Bin 4-800. Front plates can be ordered seperately. Unassembled.

Dim (HxWxD, mm): 2000 x 920 x 340
Colour: Galvanized / raaco blue
Qt: 1
Item No.: 181129

Shelving 6-1100

Shelving with 11 pcs. Shelf 90-31, 36 pcs. Shelf Bin 6-1100 and 8 pcs. Post 1000. Unassembled.

Dim (HxWxD, mm): 2000 x 920 x 340
Colour: Galvanized / raaco blue
Qt: 1
Item No.: 181136

Shelving MIX A/31

Shelving with 12 pcs. Shelf 90-31, 8 pcs. Post 1000, 30 pcs. Shelf Bin 5-600, 12 pcs. Shelf Bin 6-1100 and 6 pcs. Shelf Bin 8-2000. Unassembled.

Dim (HxWxD, mm): 2000 x 920 x 340
Colour: Galvanized / raaco blue
Qt: 1
Item No.: 181143

Shelving MIX B/31

Shelving with 13 pcs. Shelf 90-31, 8 pcs. Post 1000, 30 pcs. Shelf Bin 5-600 and 24 pcs. Shelf bin 6-1100. Unassembled.

Dim (HxWxD, mm): 2000 x 920 x 340
Colour: Galvanized / raaco blue
Qt: 1
Item No.: 181150

Shelving 5-600

Shelving with 13 pcs. Shelf 90-31, 8 pcs. Post 1000 and 60 pcs. Shelf Bin 5-600. Unassembled.

Dim (HxWxD, mm): 2000 x 920 x 340
Colour: Galvanized / raaco blue
Qt: 1
Item No.: 181167

Shelving 9-2800



Shelving with 8 pcs. Shelf 9040-4, 8 pcs. Posts 1000 and 18 pcs. Shelf bin 9-2800. Unassembled.

Dim (HxWxD, mm): 2000 x 920 x 430
Colour: Galvanized / raaco blue
Qt: 1
Item No.: 181174

Shelving MIX C/40

Shelving with 9 pcs. Shelf 90-40, 8 pcs. Post 1000, 12 pcs. Shelf bin 7-1600 and 12 pcs. Shelf bin 9-2800. Unassembled.

Dim (HxWxD, mm): 2000 x 920 x 430
Colour: Galvanized / raaco blue
Qt: 1
Item No.: 181181

Shelving 7-1600

Shelving with 10 pcs. Shelf 90-40, 8 pcs. Post 1000 and 36 pcs. Shelf Bin 7-1600. Unassembled.

Dim (HxWxD, mm): 2000 x 920 x 430
Colour: Galvanized / raaco blue
Qt: 1
Item No.: 181198

Make the most of your space by using shelving bins and drawers

raaco Bins

Easy access to more content

If you need storage space, but space-saving storage for small parts, raaco's storage bins are the perfect solution.

The open bins give a quick overview and direct access to the contents, so you can work efficiently throughout the day. The storage bins are available in several different sizes and are designed to give easy access to the contents, even with the smallest bins.

You can use raaco's storage bins systems to create customised storage solutions for your workplace.

Before you decide on a solution, you should consider how much space you have available. The turntable and the floor stand only take up little space and can be placed in the middle of the room, while the wall panels require a relatively large amount of wall space.

Choose between stationary and mobile solutions.

Bin 2-80

Bin 2-80. Covers a total of 2 slots in height on Bin Wall Panel.

Made of polypropylene (PP).

Dim (HxWxD, mm): 50 x 125 x 133
Colour: raaco blue
Qt: 48
Carriage load (kg): 5,00 **Item No.: 136631**

Bin 3-160

Bin 3-160. Covers a total of 3 slots in height on Bin Wall Panel.

Made of polypropylene (PP).

Dim (HxWxD, mm): 75 x 125 x 173
Colour: raaco blue
Qt: 32
Carriage load (kg): 5,00 **Item No.: 136648**

Bin 4-280

Bin 4-280. Covers a total of 4 slots in height on Bin Wall Panel.

Made of polypropylene (PP).

Dim (HxWxD, mm): 101 x 125 x 228
Colour: raaco blue
Qt: 24
Carriage load (kg): 5,00 **Item No.: 136655**

Bin 5-460

Bin 5-460. Covers a total of 5 slots in height on Bin Wall Panel.

Made of polypropylene (PP).

Dim (HxWxD, mm): 126 x 125 x 300
Colour: raaco blue
Qt: 16
Carriage load (kg): 10,00 **Item No.: 136662**

Bin 13

Bin 16-1800. Covers a total of 16 slots in height on Bin Wall Panel.

Made of polypropylene (PP).

Dim (HxWxD, mm): 200 x 256 x 365
Colour: raaco blue
Qt: 6
Carriage load (kg): 15,00 **Item No.: 136679**

Bin Wall Panel

Wall panel for bins with 48 slots.

Made of galvanized steel.

Dim (HxWxD, mm): 440 x 520 x 11
Colour: Galvanized
Qt: 6
Carriage load (kg): 18,00 **Item No.: 118330**

Bin Wall Panel x2/2-80

2 x wall panels with type 2-80 bins.
Contains 48 bins.

Made of galvanized steel and bins of polypropylene (PP).

Dim (HxWxD, mm): 440 x 1040 x 144
Colour: Galvanized / raaco blue
Qt: 1
Item No.: 181204

Bin Wall Panel x2/3-160

2 wall panels with type 3-160 bins.
Contains 32 bins.

Made of galvanized steel and bins of polypropylene (PP).

Dim (HxWxD, mm): 440 x 1040 x 184
Colour: Galvanized / raaco blue
Qt: 1
Item No.: 181211

Bin Wall Panel x2/4-280

2 wall panels with type 4-280 bins.
Contains 24 bins.

Made of galvanized steel and bins of polypropylene (PP).

Dim (HxWxD, mm): 440 x 1040 x 239
Colour: Galvanized / raaco blue
Qt: 1
Item No.: 181228

Bin Table Rack Mix

Table rack with 16 bins of 3 sizes. 8 pcs. of type 2-80. 4 pcs. of type 3-160. 4 pcs. of type 4-280.
Contains 16 bins.

Made of polystyrene (PS) and bins of polypropylene (PP).

Dim (HxWxD, mm): 388 x 500 x 360
Colour: raaco blue
Qt: 1
Carriage load (kg): 24,00 **Item No.: 136686**

Handles & Castors with Brake

4 rubber tyred castors (2 fitted with brakes) and 2 handles for fitting on racks.

Dim (HxWxD, mm):
Colour: Grey / Black
Qt: 1
Item No.: 112369

Label for Bins

Labels for bin 2-80, 3-160, 4-280, 5-460.
Contains 16 pcs./bag.

Dim (HxWxD, mm): 10 x 125 x 1
Colour: White
Qt: 25
Item No.: 107839

Bins Carousel

Bin carousel. 3 cartons of bins type 2-80, 3-160. 4-280 and 5-460 can be fitted in any combination. 288 slots. (12-1100 Bin does not fit on the bin carousel).
Without bins.

Made of galvanized steel.

Dim (HxØ, mm): 1600 x 665
Colour: raaco blue
Qt: 1
Carriage load (kg): 450,00 **Item No.: 137362**

Bin Rack

Bin rack. 3 cartons of bins type 2-80, 3-160, 4-280 or 16-1800 can be fitted in any combination. 288 slots. Handles and castors can be fitted in (extra accessory).
Without bins.

Made of galvanized steel.

Dim (HxWxD, mm): 1600 x 571 x 570
Colour: raaco blue
Qt: 1
Carriage load (kg): 450,00 **Item No.: 137379**

raaco SuperClip

Tool Wall Panel/Clips

raaco's SuperClip System is a simple, but truly practical storage system consisting of a perforated panel and various clip varieties. With SuperClip, you can create manageable storage solutions for tools, accessories and much more, so you always have easy access to everything.

The smart clips are made from durable polyacetal and galvanised steel, with high bearing capacity. The clips can be placed anywhere in the perforated panel, attached without using tools with just one touch – and moved again just as easily. Choose between many different types of hooks and holders.

You can use SuperClip on different raaco perforated panel systems. Choose between wall-mounted and free-standing SuperClip systems. The wall-mounted systems can be expanded in horizontal and vertical series, while the free-standing systems can be mobilised with wheels and handles.



Clip 1-30 mm Single Hook

Clip 1. Length 30 mm.
Contains 5 pcs./bag. Made of steel and polyacetal (POM).

Dim (HxWxD, mm): 60 x 27 x 47
Colour: Black
Carriage load (kg): 5,00
Qt: 10 **Item No.: 110709**

Clip 1-60 mm Single Hook

Clip 1. Length 60 mm.
Contains 5 pcs./bag. Made of steel and polyacetal (POM).

Dim (HxWxD, mm): 60 x 27 x 79
Colour: Black
Carriage load (kg): 5,00
Qt: 10 **Item No.: 110716**

Clip 1-90 mm Single Hook

Clip 1. Length 90 mm.
Contains 5 pcs./bag. Made of steel and polyacetal (POM).

Dim (HxWxD, mm): 60 x 27 x 107
Colour: Black
Carriage load (kg): 5,00
Qt: 10 **Item No.: 110723**

Clip 2-30 mm Double Hook

Clip 2. Length 30 mm.
Contains 3 pcs./bag. Made of steel and polyacetal (POM).

Dim (HxWxD, mm): 60 x 27 x 47
Colour: Black
Carriage load (kg): 5,00
Qt: 10 **Item No.: 110730**

Clip 2-60 mm Double Hook

Clip 2. Length 60 mm.
Contains 3 pcs./bag. Made of steel and polyacetal (POM).

Dim (HxWxD, mm): 60 x 27 x 79
Colour: Black
Carriage load (kg): 5,00
Qt: 10 **Item No.: 110747**

Clip 3-25 mm Angled Hook

Clip 3. Length 25 mm.
Contains 5 pcs./bag. Made of steel and polyacetal (POM).

Dim (HxWxD, mm): 60 x 27 x 47
Colour: Black
Carriage load (kg): 5,00
Qt: 10 **Item No.: 110754**

Clip 3-50 mm Angled Hook

Clip 3. Length 50 mm.
Contains 5 pcs./bag. Made of steel and polyacetal (POM).

Dim (HxWxD, mm): 60 x 27 x 71
Colour: Black
Carriage load (kg): 5,00
Qt: 10 **Item No.: 110761**

Clip 3-75 mm Angled Hook

Clip 3. Length 75 mm.
Contains 5 pcs./bag. Made of steel and polyacetal (POM).

Dim (HxWxD, mm): 60 x 27 x 96
Colour: Black
Carriage load (kg): 5,00
Qt: 10 **Item No.: 110778**

Clip 4-40 mm Hammer Holder

Clip 4. Length 40 mm.
Contains 3 pcs./bag. Made of steel and polyacetal (POM).

Dim (HxWxD, mm): 61 x 44 x 70
Colour: Black
Carriage load (kg): 5,00
Qt: 10 **Item No.: 110785**

Clip 4-50 mm Hammer Holder

Clip 4. Length 50 mm.
Contains 3 pcs./bag. Made of steel and polyacetal (POM).

Dim (HxWxD, mm): 60 x 50 x 79
Colour: Black
Carriage load (kg): 5,00
Qt: 10 **Item No.: 110792**

Clip 5-17 mm Pliers Holder

Clip 5. Length 17 mm.
Contains 3 pcs./bag. Made of steel and polyacetal (POM).

Dim (HxWxD, mm): 60 x 45 x 53
Colour: Black
Carriage load (kg): 5,00
Qt: 10 **Item No.: 110808**

Clip 5-20 mm Pliers Holder

Clip 5. Length 20 mm.
Contains 3 pcs./bag. Made of steel and polyacetal (POM).

Dim (HxWxD, mm): 60 x 62 x 61
Colour: Black
Carriage load (kg): 5,00
Qt: 10 **Item No.: 110815**

Clip 6-12 mm Spring Clip

Clip 6. Diameter 12 mm.
Contains 6 pcs./bag.
Made of polyacetal (POM).

Dim (HxWxD, mm): 60 x 27 x 37
Colour: Black
Carriage load (kg): 5,00
Qt: 10 **Item No.: 110631**

Clip 6-18 mm Spring Clip

Clip 6. Diameter 18 mm.
Contains 6 pcs./bag.
Made of polyacetal (POM).

Dim (HxWxD, mm): 60 x 27 x 46
Colour: Black
Carriage load (kg): 5,00
Qt: 10 **Item No.: 110648**

Clip 6-24 mm Spring Clip

Clip 6. Diameter 24 mm.
Contains 6 pcs./bag.
Made of polyacetal (POM).

Dim (HxWxD, mm): 60 x 33 x 56
Colour: Black
Carriage load (kg): 5,00
Qt: 10 **Item No.: 110655**

Clip 8-30 mm Pipe Holder

Clip 8. Diameter 30 mm.
Contains 4 pcs./bag.
Made of polyacetal (POM).

Dim (HxWxD, mm): 80 x 37 x 57
Colour: Black
Carriage load (kg): 0,30
Qt: 10 **Item No.: 110679**

Clip 8-50 mm Pipe Holder

Clip 8. Diameter 50 mm.
Contains 1 pcs./bag.
Made of polyacetal (POM).

Dim (HxWxD, mm): 114 x 59 x 77
Colour: Black
Carriage load (kg): 1,30
Qt: 10 **Item No.: 103169**

Clip 9 Box

Clip 9 Bin.
Contains 1 pc./bag.
Made of polypropylene (PP).

Dim (HxWxD, mm): 58 x 108 x 83
Colour: Black
Carriage load (kg): 2,20
Qt: 10 **Item No.: 104562**

Clip 10 Power Drill Holder

Clip 10 Power Drill Holder.
Contains 4 pcs./bag. Made of steel and polyacetal (POM).

Dim (HxWxD, mm): 60 x 27 x 93
Colour: Black
Carriage load (kg): 5,00
Qt: 10 **Item No.: 108928**

Clip 11 Spanner Holder

Clip 11 - Spanner Holder.
Contains 1 pc./bag.
Made of polypropylene (PP).

Dim (HxWxD, mm): 145 x 237 x 46
Colour: Black
Carriage load (kg): 5,00
Qt: 10 **Item No.: 114165**

Clip 12 Drill Bit Holder

Clip 12 - Drill Bit Holder.
Contains 1 pc./bag.
Made of polypropylene (PP).

Dim (HxWxD, mm): 65 x 94 x 77
Colour: Black
Carriage load (kg): 5,00
Qt: 10 **Item No.: 114172**

Clip 13 Can Holder

Clip 13 - Can Holder.
Contains 1 pc./bag.
Made of aluminium.

Dim (HxWxD, mm): 80 x 310 x 100
Colour: Aluminium
Carriage load (kg):
Qt: 10 **Item No.: 770002**

Clip Mix 53

Bag of 53 assorted Super Clips.
Containing:

- 10 x 1-30
- 2 x 1-60
- 1 x 1-90
- 1 x 2-30
- 1 x 2-60
- 6 x 3-25
- 3 x 3-50
- 2 x 4-40
- 1 x 4-50
- 2 x 5-17
- 1 x 5-20
- 4 x 6-12
- 4 x 6-18
- 4 x 6-24
- 6 x 8-30
- 1 x 8-50
- 2 x 10
- 1 x 11
- 1 x 12

Made of steel and polyacetal (POM).

Dim (HxWxD, mm):
Colour: Black
Qt: 1
Item No.: 110532

Clip 14 Angle Grinder Holder

Clip 14 - Angle Grinder Holder.
Contains 1 pcs./bag.
Made of aluminium.

Dim (HxWxD, mm): 15 x 177 x 60
Colour: Aluminium
Carriage load (kg):
Qt: 10 **Item No.: 770019**

Clip Mix 84

Bag of 84 assorted Super Clips.
Containing:

- 18 x 1-30
- 2 x 1-60
- 1 x 1-90
- 2 x 2-30
- 2 x 2-60
- 12 x 3-25
- 3 x 3-50
- 2 x 3-75
- 2 x 4-40
- 2 x 4-50
- 4 x 5-17
- 2 x 5-20
- 6 x 6-12
- 6 x 6-18
- 6 x 6-24
- 8 x 8-30
- 1 x 8-5
- 1 x 9
- 2 x 10
- 1 x 11
- 1 x 12

Made of steel and polyacetal (POM).

Dim (HxWxD, mm):
Colour: Black
Qt: 1
Item No.: 110549

raacoFix Large

Large raacoFix cassette for storing tools.
Can be mounted on a perforated panel.

Made of polypropylene (PP) and thermoplastic elastomer (TPE).

Dim (HxWxD, mm): 140 x 242 x 38
Colour: raaco Grey
Qt: 1
Item No.: 136822

raacoFix Small

Small raacoFix cassette for storing tools.
Can be mounted on a perforated panel and to large raacoFix.

Made of polypropylene (PP) and thermoplastic elastomer (TPE).

Dim (HxWxD, mm): 100 x 242 x 38
Colour: raaco Grey
Qt: 1
Item No.: 136839

Tool Wall Panel 440x520mm

Perforated panel for Super Clip.
Without Super Clip.

Made of galvanized steel.

Dim (HxWxD, mm): 440 x 520 x 11
Colour: Galvanized
Qt: 6
Carriage load (kg): 75,00 **Item No.: 118347**

Tool Wall Panel x2/Clips



2 perforated panels with 28 assorted Super Clips. Containing:

- 3 x Clip 1-30
- 1 x Clip 1-60
- 1 x Clip 1-90
- 1 x Clip 2-30
- 1 x Clip 2-60
- 1 x Clip 3-25
- 2 x Clip 3-50
- 1 x Clip 4-40
- 1 x Clip 4-50
- 1 x Clip 5-17
- 1 x Clip 5-20
- 2 x Clip 6-12
- 2 x Clip 6-18
- 2 x Clip 6-24
- 1 x Clip 8-50
- 3 x Clip 8-30
- 2 x Clip 10
- 1 x Clip 11
- 1 x Clip 12

Made of galvanized steel and polyacetal (POM).

Dim (HxWxD, mm): 440 x 1040 x 11
Colour: Galvanized / Black
Qt: 1
Item No.: 109642

Tool Wall Panel x3/Clips

3 perforated panels with 44 assorted Super Clips. Containing:

- 7 x Clip 1-30
- 1 x Clip 1-60
- 1 x Clip 1-90
- 1 x Clip 2-30
- 1 x Clip 2-60
- 4 x Clip 3-25
- 2 x Clip 3-50
- 2 x Clip 4-40
- 1 x Clip 4-50
- 2 x Clip 5-17
- 1 x Clip 5-20
- 4 x Clip 6-12
- 4 x Clip 6-18
- 4 x Clip 6-24
- 4 x 8-30
- 1 x 8-50
- 2 x Clip10
- 1 x Clip11
- 1 x Clip12

Made of galvanized steel and polyacetal (POM).



Dim (HxWxD, mm): 440 x 1560 x 11
Colour: Galvanized / Black
Qt: 1
Item No.: 109659

Tool Rack

Double rack with 6 perforated panels. Handles & castors not included (extra accessory).
Without Super Clip.

Made of steel and galvanized steel.

Dim (HxWxD, mm): 1600 x 571 x 570
Colour: Galvanized / raaco blue
Carriage load (kg): 450,00
Qt: 10 **Item No.: 137621**

Tool Bin Rack

Double rack with 4 perforated panels and 2 Bin Wall Panels. Handles & castors not included (extra accessory).
Without Super Clip/bins.

Made of steel and galvanized steel.

Dim (HxWxD, mm): 1600 x 571 x 570
Colour: Galvanized / raaco blue
Carriage load (kg): 450,00
Qt: 10 **Item No.: 137638**

Handles & Castors with brake

4 rubber-tyred castors (2 fitted with brakes) and 2 handles for fitting on racks.

Dim (Ø, mm): 70
Colour: Black / Grey
Qt: 1
Item No.: 112369

raaco

raaco Inserts

- create the order and overview you need

With raaco inserts, you can group and sort items to match your own requirements – easy, fast and efficiently.

A world of possibilities
There are 20 insert versions that fit the 3 systems in height, width and depth: Boxxser, CarryLite and Assorter. By using the wide range of inserts, you can organise your raaco product to suit your own requirements – and change it whenever you like. The inserts and contents stay in place, thanks to the special fitting system. The loose inserts also make it easy to get hold of even the smallest items.

Move any insert to where you need to use it. The transparent, high-quality plastic makes it easy to identify the contents and get an overview when time is tight. The inserts are extremely sturdy and tolerant of many different chemicals.

Our inserts can be used across the entire raaco product range. Read more on pages 113 - 127 about which inserts can be used in the various raaco products.

Inserts 55-series

Inserts 80-series

Inserts 27-series

Inserts 55-series

The inserts in the 55 series are available in 10 different versions, and can be used for e.g. Assorter 55, Boxxser 55, CarryLite 55, Compact, drawer 250-3 and the tray in ToolCase.

Available as either individual items or in handy trays. The trays have an embossed grid in the base, which keeps the inserts in place.

Insert 55 A9-1

The Insert 55 A9-1 can be used for Assorter 55, Boxxser 55, CarryLite 55, Compact, drawer 250-3 and tray in ToolCase. Made of polypropylene (PP).

Dim (HxWxD, mm): 47 x 39 x 55
Colour: Transparent
Qt: 96 **Item No.: 100274**

Insert 55 A9-2

The Insert 55 A9-2 can be used for Assorter 55, Boxxser 55, CarryLite 55, Compact, drawer 250-3 and tray in ToolCase. Made of polypropylene (PP).

Dim (HxWxD, mm): 47 x 39 x 109
Colour: Transparent
Qt: 48 **Item No.: 114578**

Insert 55 A9-3

The Insert 55 A9-3 can be used for Assorter 55, Boxxser 55, CarryLite 55, Compact, drawer 250-3 and tray in ToolCase. Made of polypropylene (PP).

Dim (HxWxD, mm): 47 x 39 x 163
Colour: Transparent
Qt: 30 **Item No.: 114653**

Insert 55 A9-4

The Insert 55 A9-4 can be used for Assorter 55, Boxxser 55, CarryLite 55, Compact, drawer 250-3 and tray in ToolCase. Made of polypropylene (PP).

Dim (HxWxD, mm): 47 x 39 x 218
Colour: Transparent
Qt: 24 **Item No.: 114585**

Insert 55 A8-1

The Insert 55 A8-1 can be used for Assorter 55, Boxxser 55, CarryLite 55, Compact, drawer 250-3 and tray in ToolCase. Made of polypropylene (PP).

Dim (HxWxD, mm): 47 x 55 x 79
Colour: Transparent
Qt: 48 **Item No.: 105590**

Insert 55 A8-2

The Insert 55 A8-2 can be used for Assorter 55, Boxxser 55, CarryLite 55, Compact, drawer 250-3 and tray in ToolCase. Made of polypropylene (PP).

Dim (HxWxD, mm): 47 x 55 x 157
Colour: Transparent
Qt: 24 **Item No.: 114592**

Insert 55 A8-3

The Insert 55 A8-3 can be used for Assorter 55, Boxxser 55, CarryLite 55, Compact, drawer 250-3 and tray in ToolCase. Made of polypropylene (PP).

Dim (HxWxD, mm): 47 x 55 x 235
Colour: Transparent
Qt: 15 **Item No.: 114608**

Insert 55 A7-1

The Insert 55 A7-1 can be used for Assorter 55, Boxxser 55, CarryLite 55, Compact, drawer 250-3 and tray in ToolCase. Made of polypropylene (PP).

Dim (HxWxD, mm): 47 x 79 x 109
Colour: Transparent
Qt: 24 **Item No.: 105583**

Insert 55 A7-2

The Insert 55 A7-2 can be used for Assorter 55, Boxxser 55, CarryLite 55, Compact, drawer 250-3 and tray in ToolCase. Made of polypropylene (PP).

Dim (HxWxD, mm): 47 x 79 x 218
Colour: Transparent
Qt: 12 **Item No.: 103695**

Insert 55 A6-1

The Insert 55 A6-1 can be used for Assorter 55, Boxxser 55, CarryLite 55, Compact, drawer 250-3 and tray in ToolCase. Made of polypropylene (PP).

Dim (HxWxD, mm): 47 x 109 x 157
Colour: Transparent
Qt: 12 **Item No.: 105576**

Inserts 80-series

The inserts in the 80 series are available in 6 different variants, and can be used for Assorter 80, Boxxser 80, CarryLite 80 and the tray in the ToolCase.

Available either singly or in handy trays. The trays have an embossed grid at the bottom, which keep the inserts in place.

Insert 80 BA8-1

Insert 80 BA8-1 can be used for Assorter 80, Boxxser 80, CarryLite 80 and tray in ToolCase.
Made of polypropylene (PP).

Dim (HxWxD, mm): 69 x 55 x 79
Colour: Transparent
Qt: 32 **Item No.: 119276**

Insert 80 BA8-2

Insert 80 BA8-2 can be used for Assorter 80, Boxxser 80, CarryLite 80 and tray in ToolCase.
Made of polypropylene (PP).

Dim (HxWxD, mm): 69 x 55 x 157
Colour: Transparent
Qt: 16 **Item No.: 119283**

Insert 80 BA8-3

Insert 80 BA8-3 can be used for Assorter 80, Boxxser 80, CarryLite 80 and tray in ToolCase.
Made of polypropylene (PP).

Dim (HxWxD, mm): 69 x 55 x 235
Colour: Transparent
Qt: 9 **Item No.: 119290**

Insert 80 BA7-1

Insert 80 BA7-1 can be used for Assorter 80, Boxxser 80, CarryLite 80 and tray in ToolCase.
Made of polypropylene (PP).

Dim (HxWxD, mm): 69 x 79 x 109
Colour: Transparent
Qt: 16 **Item No.: 119306**

Insert 80 BA7-2

Insert 80 BA7-2 can be used for Assorter 80, Boxxser 80, CarryLite 80 and tray in ToolCase.
Made of polypropylene (PP).

Dim (HxWxD, mm): 69 x 79 x 218
Colour: Transparent
Qt: 8

Item No.: 119313

Insert 80 BA6-1

Insert 80 BA6-1 can be used for Assorter 80, Boxxser 80, CarryLite 80 and tray in ToolCase.
Made of polypropylene (PP).

Dim (HxWxD, mm): 69 x 109 x 157
Colour: Transparent
Qt: 8

Item No.: 119320

Inserts 27-series

The inserts in the 27 series are available in 4 different versions, and can be used for division of Pocketbox, Assorter, Boxxser, CarryLite, Compact and Drawer 250-3.

Insert A71

Half-height insert with 1 compartment. Can be used to sub-divide 250-3 drawer, Pocketbox, Assorter and the Compact series.
Made of polypropylene (PP).

Dim (HxWxD, mm): 24 x 79 x 109
Colour: Transparent
Qt: 48

Item No.: 115735

Insert A73

Half-height insert with 3 compartment. Can be used to sub-divide 250-3 drawer, Pocketbox, Assorter and the Compact series.
Made of polypropylene (PP).

Dim (HxWxD, mm): 24 x 79 x 109
Colour: Transparent
Qt: 48

Item No.: 115742

Insert A75

Half-height insert with 5 compartment. Can be used to sub-divide 250-3 drawer, Pocketbox, Assorter and the Compact series.
Made of polypropylene (PP).

Dim (HxWxD, mm): 24 x 79 x 109
Colour: Transparent
Qt: 48 **Item No.: 115759**

Insert A78

Half-height insert with 8 compartment. Can be used to sub-divide 250-3 drawer, Pocketbox, Assorter and the Compact series.
Made of polypropylene (PP).

Dim (HxWxD, mm): 24 x 79 x 109
Colour: Transparent
Qt: 48 **Item No.: 115766**

Inserts - system, compatibility and choice

The flexibility and choices don´t just exist within the individual systems, but also between them. The inserts ensure many combinations between the Assorter Boxes in A4, A5 and A6 size, Pocketboxes, CarryLites, Boxxser, Compact, ToolCase and the 250-3 drawers for cabinets.

The wide range of inserts ensures that you can customise your raaco product to suit particular requirements - and just as easily move it again. The inserts and the contents stay in place thanks to a special installation system. Furthermore - it also makes even the smallest items easy to get hold of.

On the following pages there are guides which illustrate, how assortment boxes, drawers, toolboxes and toolcases can be arranged. The type and size of the inserts depends on the product to be arranged.

In the illustrations of the individual insert, a field is marked in grey which indicates how much the insert takes up and how it should be placed.

A template showing the bottom of a CarryLite 55 4x8

An example of a combination with 3 types of inserts



The illustrations show how many fields each insert cover the bottom of the box.

Arrange the raaco products to suit your needs

Inserts for

Assorter 4x8

Assorter 55 4x8

Assorter 80 4x8



Assorter 4x8 is divided into 32 fields.

The following shows the inserts that can be used and how many fields they cover when combined in the boxes.

Insert 55-series

...to be used with Assorter 55 4x8



A9-1



A9-2



A9-3



A9-4



A8-1



A8-2



A8-3



A7-1



A7-2



A6-1

Insert 80-series

...to be used with Assorter 80 4x8



BA8-1



BA8-2



BA8-3



BA7-1



BA7-2



BA6-1

Inserts for

Assorter 4x4



Assorter 4x4 is divided into 16 fields.

The following shows the inserts that can be used and how many fields they cover when combined in the boxes.

Insert 55-series



A9-1



A9-2



A9-3



A9-4



A8-1



A8-2



A7-1



A7-2



A6-1

Inserts for
Assorter 6x0

Assorter 6x0 is without division.

The following shows the inserts that can be used and how many fields they cover when combined in the boxes.

Insert 27-series


A71


A73


A75


A78

Inserts for
Pocketbox



Pocketbox is without division.

The following shows the inserts that can be used and how many fields they cover when combined in the boxes.

Insert 27-series


A71


A73


A75


A78

Inserts for

Boxxser 55 4x4



Boxxser 55 4x4 is divided into 16 fields.

The following shows the inserts that can be used and how many fields they cover when combined in the boxes.

Insert 55-series



Inserts for

Boxxser 55 5x5



Boxxser 55 5x5 is divided into 25 fields.

The following shows the inserts that can be used and how many fields they cover when combined in the boxes.

Insert 55-series



A9-1



A9-2



A9-3



A9-4



A8-1



A8-2



A7-1



A7-2



A6-1

Inserts for

Boxxser 55 6x6



Boxxser 55 6x6 is divided into 36 fields.

The following shows the inserts that can be used and how many fields they cover when combined in the boxes.

Insert 55-series



A9-1



A9-2



A9-3



A9-4



A8-1



A8-2



A8-3



A7-1



A7-2



A6-1

Inserts for

Boxxser 55 5x10



Boxxser 55 5x10 is divided into 50 fields.

The following shows the inserts that can be used and how many fields they cover when combined in the boxes.

Insert 55-series



A9-1



A9-2



A9-3



A9-4



A8-1



A8-2



A8-3



A7-1



A7-2



A6-1

Inserts for

Boxxser 80 5x10



Boxxser 80 5x10 is divided into 50 fields.

The following shows the inserts that can be used and how many fields they cover when combined in the boxes.

Insert 80-series



BA8-1



BA8-2



BA8-3



BA7-1



BA7-2



BA6-1

Inserts for

Boxxser 80 8x8



Boxxser 80 8x8 is divided into 64 fields.

The following shows the inserts that can be used and how many fields they cover when combined in the boxes.

Insert 55-series



BA8-1



BA8-2



BA8-3



BA7-1



BA7-2



BA6-1

Inserts for

CarryLite 4x8

CarryLite 55 4x8

CarryLite 80 4x8



CarryLite 4x8 is divided into 32 fields.

The following shows the inserts that can be used and how many fields they cover when combined in the boxes.

Insert 55-series

...to be used with CarryLite 55 4x8



A9-1



A9-2



A9-3



A9-4



A8-1



A8-2



A8-3



A7-1



A7-2



A6-1

Insert 80-series

...to be used with CarryLite 80 4x8



BA8-1



BA8-2



BA8-3



BA7-1



BA7-2



BA6-1

Inserts for

CarryLite 5x10

CarryLite 55 5x10

CarryLite 80 5x10



CarryLite 5x10 is divided into 50 fields.

The following shows the inserts that can be used and how many fields they cover when combined in the boxes.

Insert 55-series

...to be used with CarryLite 55 5x10



A9-1



A9-2



A9-3



A9-4



A8-1



A8-2



A8-3



A7-1



A7-2



A6-1

Insert 80-series

...to be used with CarryLite 80 5x10



BA8-1



BA8-2



BA8-3



BA7-1



BA7-2



BA6-1

Inserts for
Compact

Whichever Compact you choose, you get a toolbox that can be customized to your needs.

The toolbox can be arranged and divided by movable inserts. These can make it easy to store, and to get a system and overview of the items stored.

Insert 55-series + Insert 27-series

Compact 20 - 28 fields

Tray



Compact 27 - 40 fields

Tray



Drawer



Compact 37 - 40 fields

Tray



Compact 47 - 55 fields

Tray



Drawer



Compact 50 - 48 fields

Tray



Compact 62 - 68 fields

Tray



Drawer



Inserts for

Drawer 250-3



Drawer 250-3 is divided into 32 fields.

The following shows the inserts that can be used and how many fields they cover when combined in the drawers.

Insert 55-series



A9-1



A9-2



A9-3



A9-4



A8-1



A8-2



A8-3



A7-1



A7-2



A6-1

Inserts for

ToolCase - Tray 55 XL



Tray 55 XL is divided into 54 fields.

The following shows the inserts that can be used and how many fields they cover when combined in the tray in the bottom of the ToolCase.

Insert 55-series



A9-1



A9-2



A9-3



A9-4



A8-1



A8-2



A8-3



A7-1



A7-2



A6-1

raaco ESD Products

- Full protection of electronics

Raacostat provides effective anti-static protection of sensitive equipment.

Today, a rapidly increasing number of products, spare parts, tools, etc. are based on electronic components. They are often extremely sensitive to damage caused by static electricity. This damage not only occurs during the actual production process, but also during storage, transportation, etc.

Raacostat is a full range of boxes, toolboxes, cabinets and drawers that provide 100% protection from static electricity. Like all other raaco products, the Raacostat series is also distinguished by many different combination options, to meet almost any individual requirements.

All solutions are made from a special plastic with carbon fibres, which makes them permanently antistatic. This means that there is no reduction of protection over time, or due to intensive use.

Raacostat naturally complies with the EN 61340-5-1 standard and all other international requirements.

Surface resistance 1x10^4 - 1x10^11 Ω.

ESD Cabinets

ESD Bins

ESD Asoortment Boxes

ESD Toolbox

raacostat

Cabinets

ESD Cabinet 1260-00

ESD Cabinet with drawers, type 150-00.
Each drawer can be divided into 2 compartments using dividers (extra accessory). Earth wire included.
Contains 60 drawers.

Made of galvanized steel and drawers of ESD polypropylene (PP).

Dim (HxWxD, mm): 552 x 306 x 150
Colour: Black (ESD)
Qt: 1
Carriage load (kg): 40,00 **Item No.: 102513**

ESD Cabinet 1248-01

ESD Cabinet with drawers, type 150-01.
Each drawer can be divided into 8 compartments using dividers (extra accessory). Earth wire included.
Contains 48 drawers.

Made of galvanized steel and drawers of ESD polypropylene (PP).

Dim (HxWxD, mm): 552 x 306 x 150
Colour: Black (ESD)
Qt: 1
Carriage load (kg): 40,00 **Item No.: 102520**

ESD Cabinet 1224-02

ESD Cabinet with drawers, type 150-02.
Each drawer can be divided into 3 compartments using dividers (extra accessory). Earth wire included.
Contains 24 drawers.

Made of galvanized steel and drawers of ESD polypropylene (PP).

Dim (HxWxD, mm): 552 x 306 x 150
Colour: Black (ESD)
Qt: 1
Carriage load (kg): 26,40 **Item No.: 102537**

ESD Cabinet 945-00

ESD Cabinet with drawers, type 150-00.
Each drawer can be divided into 2 compartments using dividers (extra accessory). Earth wire included.
Contains 45 drawers.

Made of galvanized steel and drawers of ESD polypropylene (PP).

Dim (HxWxD, mm): 417 x 306 x 150
Colour: Black (ESD)
Qt: 1
Carriage load (kg): 30,00 **Item No.: 118231**

ESD Cabinet 936-01

ESD Cabinet with drawers, type 150-01.
Each drawer can be divided into 8 compartments using dividers (extra accessory). Earth wire included.
Contains 36 drawers.

Made of galvanized steel and drawers of ESD polypropylene (PP).

Dim (HxWxD, mm): 417 x 306 x 150
Colour: Black (ESD)
Qt: 1
Carriage load (kg): 30,00 **Item No.: 109246**

ESD Cabinet 918-02

ESD Cabinet with drawers, type 150-02.
Each drawer can be divided into 3 compartments using dividers (extra accessory). Earth wire included.
Contains 18 drawers.

Made of galvanized steel and drawers of ESD polypropylene (PP).

Dim (HxWxD, mm): 417 x 306 x 150
Colour: Black (ESD)
Qt: 1
Carriage load (kg): 19,80 **Item No.: 102544**

ESD Cabinet 250/6-3

ESD Cabinet with drawers, type 250-3.
Each drawer can be sub-divided using inserts (extra accessory).
Earth wire included.
Contains 6 drawers.

Made of galvanized steel and drawers of ESD polypropylene (PP).

Dim (HxWxD, mm): 435 x 357 x 255
Colour: Black (ESD)
Qt: 1
Carriage load (kg): 37,50 **Item No.: 103725**

ESD Cabinet Turntable 1200

Turntable. Can be fitted with any 12 pcs. ESD 1200 series cabinets. Earth wire included.

Without cabinets.

Made of galvanized steel.

Dim (H, mm): 1760
Colour: Black (ESD)
Qt: 1
Carriage load (kg): 480,00

Item No.: 102568

ESD Cabinet Turntable 900

Turntable. Can be fitted with any 12 pcs. ESD 900 series cabinets. Earth wire included.

Without cabinets.

Made of galvanized steel.

Dim (H, mm): 1600
Colour: Black (ESD)
Qt: 1
Carriage load (kg): 480,00

Item No.: 102964

ESD Cabinet Turntable 250

Turntable. Can be fitted with any 12 pcs. ESD 250 series cabinets. Earth wire included.

Without cabinets.

Made of galvanized steel.

Dim (H, mm): 1600
Colour: Black (ESD)
Qt: 1
Carriage load (kg): 480,00 **Item No.: 103749**

ESD Bin Carousel

Bins carousel. 3 cartons of ESD bins can be fitted in any combination. 288 slots. Earth wire included.

Without bins.

Made of galvanized steel.

Dim (H, mm): 1600
Colour: Black (ESD)
Qt: 1
Carriage load (kg): 450,00 **Item No.: 114158**

raacostat

Bins

ESD Bin Wall Panel

Wall panel for ESD bins. 48 slots. Earth wire included.
Without bins.

Made of galvanized steel.

Dim (HxWxD, mm): 440 x 520 x 11
Colour: Black (ESD)
Qt: 6
Carriage load (kg): 75,00 **Item No.: 106573**

ESD Bin 2-80

ESD Bin 2-80.
Covers a total of 2 slots on Bin Wall Panel and Carousel.

Made of ESD polypropylene (PP).

Dim (HxWxD, mm): 50 x 125 x 133
Colour: Black (ESD)
Qt: 48
Carriage load (kg): 5,00 **Item No.: 109277**

ESD Bin 3-160

ESD Bin 3-160.
Covers a total of 3 slots on Bin Wall Panel and Carousel.

Made of ESD polypropylene (PP).

Dim (HxWxD, mm): 75 x 125 x 173
Colour: Black (ESD)
Qt: 32
Carriage load (kg): 5,00 **Item No.: 109291**

ESD Bin 4-280

ESD Bin 4-280.
Covers a total of 4 slots on Bin Wall Panel and Carousel.

Made of ESD polypropylene (PP).

Dim (HxWxD, mm): 101 x 125 x 228
Colour: Black (ESD)
Qt: 24
Carriage load (kg): 5,00 **Item No.: 109314**

ESD Bin 5-460

ESD Bin 5-460.
Covers a total of 5 slots on Bin Wall Panel and Carousel.

Made of ESD polypropylene (PP).

Dim (HxWxD, mm): 126 x 125 x 300
Colour: Black (ESD)
Qt: 16
Carriage load (kg): 10,00 **Item No.: 113021**

ESD Bin Table Rack/Bins

ESD Table rack with 16 bins. 8 pcs. of type 3-160 and 8 pcs. of type 2-80. Earth wire included.
Contains 16 pcs. bins.

Made of ESD polystyrene (PS) and galvanized steel.
Bins of ESD polypropylene (PP).

Dim (HxWxD, mm): 388 x 500 x 305
Colour: Black (ESD)
Qt: 6
Carriage load (kg): 24,00 **Item No.: 106825**

raacostat

Assortment Boxes

ESD Assorter 55 4x8-0

ESD Assorter 55 4x8-0 fitted with sliding locks and handle.
Can be sub-divided using ESD inserts (extra accessory).
Equipped with U-profiles inside the lid, which ensures that the contents remain in place during transportation.
Without inserts.

Made of ESD polypropylene (PP).

Dim (HxWxD, mm): 57 x 338 x 261
Colour: Black (ESD)
Qt: 1
Carriage load (kg): 5,00

Item No.: 104203

ESD Assorter 4-15

ESD Assorter 4-15 fitted with sliding locks. Equipped with U-profiles inside the lid, which ensures that the contents remain in place during transportation.
Contains 15 fixed compartments.

Made of ESD polypropylene (PP).

Dim (HxWxD, mm): 57 x 338 x 260
Colour: Black (ESD)
Qt: 1
Carriage load (kg): 5,00

Item No.: 104111

ESD Assorter 4-32

ESD Assorter 4-32 fitted with sliding locks. Equipped with U-profiles inside the lid, which ensures that the contents remain in place during transportation.
Contains 32 fixed compartments.

Made of ESD polypropylene (PP).

Dim (HxWxD, mm): 57 x 338 x 260
Colour: Black (ESD)
Qt: 1
Carriage load (kg): 5,00

Item No.: 104173

raacostat

Toolbox

ESD Compact 15

ESD Toolbox including removable tote tray with handle.
Tools not included.

Made of ESD polypropylene (PP).

Dim (HxWxD, mm): 170 x 426 x 215
Colour: Black (ESD)
Qt: 1
Carriage load (kg): 20,00 **Item No.: 104432**

+ Raacostat - effective, anti-static protection

raacostat

Accessories

ESD 150-00 Drawer

ESD Drawer, type 150-00.
Can be subdivided using dividers (extra accessory).

Made of ESD polypropylene (PP).

Dim (HxWxD, mm): 41 x 55 x 153
Colour: Black (ESD)
Qt: 120
Item No.: 112260

ESD Divider 150-00

ESD Dividers 35/52 for drawer 150-00.
Contains 60 pcs./bag.

Made of ESD polypropylene (PP).

Dim (HxWxD, mm): 32 x 52 x 2
Colour: Black (ESD)
Qt: 25
Item No.: 118248

ESD 150-01 Drawer

ESD Drawer, type 150-01.
Can be subdivided using dividers (extra accessory).

Made of ESD polypropylene (PP).

Dim (HxWxD, mm): 41 x 67 x 153
Colour: Black (ESD)
Qt: 96
Item No.: 105910

ESD Divider 150-01

ESD Dividers 35/64 for drawer 150-01.
Contains 48 pcs./bag.

Made of ESD polypropylene (PP).

Dim (HxWxD, mm): 31 x 64 x 1
Colour: Black (ESD)
Qt: 25
Item No.: 103985

ESD 150-02 Drawer

ESD Drawer, type 150-02.
Can be subdivided using dividers (extra accessory).

Made of ESD polypropylene (PP).

Dim (HxWxD, mm): 60 x 91 x 154
Colour: Black (ESD)
Qt: 48
Item No.: 107853

ESD Divider 150-02

ESD Dividers 57/87 for drawer 150-02.
Contains 24 pcs./bag.

Made of ESD polypropylene (PP).

Dim (HxWxD, mm): 49 x 87 x 2
Colour: Black (ESD)
Qt: 25
Item No.: 113298

ESD 250-3 Drawer

ESD Drawer, type 250-3.
Can be subdivided using inserts (extra accessory).

Made of ESD polypropylene (PP).

Dim (HxWxD, mm): 57 x 320 x 240
Colour: Black (ESD)
Qt: 7
Item No.: 111775

ESD A9-1 Insert

ESD A9-1 inserts. Can be used to sub-divide 250-3 drawer and ESD Assorter 55 4x8-0.

Made of ESD polypropylene (PP).

Dim (HxWxD, mm): 47 x 39 x 55
Colour: Black (ESD)
Qt: 96
Item No.: 104555

ESD A8-1 Insert

ESD A8-1 inserts. Can be used to sub-divide 250-3 drawer and ESD Assorter 55 4x8-0.

Made of ESD polypropylene (PP).

Dim (HxWxD, mm): 47 x 55 x 79
Colour: Black (ESD)
Qt: 48
Item No.: 104630

ESD A7-1 Insert

ESD A7-1 inserts. Can be used to sub-divide 250-3 drawer and ESD Assorter 55 4x8-0.

Made of ESD polypropylene (PP).

Dim (HxWxD, mm): 47 x 79 x 109
Colour: Black (ESD)
Qt: 24
Item No.: 125109

ESD Insert A71

ESD A71 insert. Half-height insert - 1 compartment. Can be used to sub-divide 250-3 drawer and ESD Assorter 55 4x8-0.

Made of ESD polypropylene (PP).

Dim (HxWxD, mm): 24 x 79 x 109
Colour: Black (ESD)
Qt: 21
Item No.: 118187

ESD Insert A75

ESD A75 insert. Half-height insert - 5 small compartments. Can be used to sub-divide 250-3 drawer and ESD Assorter 4x8-0.

Made of ESD polypropylene (PP).

Dim (HxWxD, mm): 24 x 79 x 109
Colour: Black (ESD)
Qt: 21
Item No.: 118200

ESD Insert 55 16xA9-1

ESD Insert 55 16xA9-1. Can be used in ESD Assorter 55 4x8-0 and drawer type 250-3.
Tray with 16 pc.

Made of ESD polypropylene (PP).

Dim (HxWxD, mm): 47 x 220 x 160
Colour: Black (ESD)
Qt: 12
Item No.: 142007

ESD Insert 55 8xA8-1



ESD Insert 55 8xA8-1. Can be used in ESD Assorter 55 4x8-0 and drawer type 250-3.
Tray with 8 pc.

Made of ESD polypropylene (PP).

Dim (HxWxD, mm): 47 x 220 x 160
Colour: Black (ESD)
Qt: 12
Item No.: 142014


GRADIENTS

raaco and order are interrelated
Since 1956, raaco has developed and manufactured innovative, streamlined and space-saving storage systems for both industry and professional craftsmen all over the world.

Philosophy - You create the order and overview you need
raaco's products and storage systems give you possibilities – while you define the solution that suits you best.
The product range is characterised by innovative quality solutions that are easy to use.

Great flexibility with the possibility of:
• individual adjustment of products to match personal needs
• combined use of different products
• construction or expansion of systems over time

raaco - professional storage systems since 1956

raaco A/S · Platanvej 19 · DK-4800 Nykøbing F. · Danmark
Phone +45 54 88 84 00 · mail@raaco.com · www.raaco.com

02.2021 – GB