

Metal drill bit sets HSS PointTeQ

| PRODUCT PROPERTIES | | | ORDERING INFORMATION | | | | |
|--------------------|-------------------|-----------------|----------------------|---------------|------------------------|---------|-------------|
| Diameter mm | Working length mm | Total length mm | Packaging type | Pack quantity | Minimum order quantity | Barcode | Part number |



10-piece Metal HSS PointTeQ Twist Drill Bit Set

Shank diameter equal to drill bit diameter

| | | | | | | | |
|----|----|-----|-----|----|---|---------------|---------------|
| 1 | 12 | 34 | P1k | 10 | 1 | 3165140917667 | 2 608 577 348 |
| 2 | 24 | 49 | | | | | |
| 3 | 33 | 61 | | | | | |
| 4 | 43 | 75 | | | | | |
| 5 | 52 | 86 | | | | | |
| 6 | 57 | 93 | | | | | |
| 7 | 69 | 109 | | | | | |
| 8 | 75 | 117 | | | | | |
| 9 | 81 | 125 | | | | | |
| 10 | 87 | 133 | | | | | |



13-piece Metal HSS PointTeQ Twist Drill Bit Set

Shank diameter equal to drill bit diameter

| | | | | | | | |
|-----|----|-----|-----|----|---|---------------|---------------|
| 1.5 | 18 | 40 | P1k | 13 | 1 | 3165140917674 | 2 608 577 349 |
| 2 | 24 | 49 | | | | | |
| 2.5 | 30 | 57 | | | | | |
| 3 | 33 | 61 | | | | | |
| 3.2 | 36 | 65 | | | | | |
| 3.5 | 39 | 70 | | | | | |
| 4 | 43 | 75 | | | | | |
| 4.5 | 47 | 80 | | | | | |
| 4.8 | 52 | 86 | | | | | |
| 5 | 52 | 86 | | | | | |
| 5.5 | 57 | 93 | | | | | |
| 6 | 57 | 93 | | | | | |
| 6.5 | 63 | 101 | | | | | |



18-piece Metal HSS PointTeQ Twist Drill Bit Set

Shank diameter equal to drill bit diameter

| | | | | | | | |
|-----|----|-----|-----|----|---|---------------|---------------|
| 1 | 12 | 34 | M0a | 18 | 1 | 3165140917681 | 2 608 577 350 |
| 1.5 | 18 | 40 | | | | | |
| 2 | 24 | 49 | | | | | |
| 2 | 24 | 49 | | | | | |
| 2.5 | 30 | 57 | | | | | |
| 3 | 33 | 61 | | | | | |
| 3 | 33 | 61 | | | | | |
| 3.5 | 39 | 70 | | | | | |
| 4 | 43 | 75 | | | | | |
| 4 | 43 | 75 | | | | | |
| 4.5 | 47 | 80 | | | | | |
| 5 | 52 | 86 | | | | | |
| 5.5 | 57 | 93 | | | | | |
| 6 | 57 | 93 | | | | | |
| 7 | 69 | 109 | | | | | |
| 8 | 75 | 117 | | | | | |
| 9 | 81 | 125 | | | | | |
| 10 | 87 | 133 | | | | | |