



A22NE-M-P202-C

Emergency stop switch, Push-in, 24 VAC/DC illuminated, 40 mm dia, push-lock/turn-reset, 2NC

Specifications

Number of contacts, normally-open	0
Number of contacts, normally-closed	2
Unlocking method	Turn unlatching mechanism
Diameter cap	40 mm
Hole diameter	22 mm
Mounting method	Build-in
With lighting	✓
With lock lever contact function	✗
Button text	None
Text color	Not Applicable
Lighting voltage	24 VAC/DC
Connection type auxiliary circuit	Spring clamp connection
Degree of protection (IP)	IP65

Accessories



A22NZ-A-B01Y

Pushbutton accessory A22NZ 22 dia. Control Box



A22NZ-S-P2A

A22N Contact blocks, DPST-NO, push-in terminal



A22NZ-S-P2B

A22N contact blocks, DPST-NC, push-in terminal



A22NZ-S-P2C

A22N Contact blocks, SPST-NO + SPST-NC, push-in terminal



A22Z-3466-1

Legend plate, emergency stop, 60 mm dia., round, yellow



A22Z-3905

Tightening wrench



A22Z-EG1

E-stop shroud, EMERGENCY OFF legend included.



A22Z-EG10

E-stop shroud, EMERGENCY OFF legend not included.

CAD Library



A22NE Emergency Stop Push Button Switches Datasheet

EN PDF 20.4 MB



EAC Mark removal Discontinuation Notice

EN PDF 221 KB



Innovation in Control Panel Building Brochure

EN PDF 4.38 MB



Machine Safety Catalogue

EN PDF 9.91 MB



Pushbutton Switches Brochure

EN PDF 2.78 MB



Safety Component Selection Guide EU Brochure

EN PDF 5.26 MB



Safety Solution Advanced Guide Guide

EN PDF 2.57 MB



Safety Solution Basic Guide Guide

EN PDF 14.4 MB