

# WT-STEEL S 7,9X259 - Cable tie



3240814

<https://www.phoenixcontact.com/gb/products/3240814>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cable binders, made from rust-free stainless steel (AISI 304), suitable for harsh ambient conditions, with ball lock, for quick and secure bundling and fastening

## Commercial data

|                                      |                     |
|--------------------------------------|---------------------|
| Item number                          | 3240814             |
| Packing unit                         | 100 pc              |
| Minimum order quantity               | 100 pc              |
| Sales key                            | BE7132              |
| Product key                          | BE7132              |
| Catalog page                         | Page 620 (C-3-2019) |
| GTIN                                 | 4046356705622       |
| Weight per piece (including packing) | 5.87 g              |
| Weight per piece (excluding packing) | 5.87 g              |
| Customs tariff number                | 73269098            |
| Country of origin                    | GB                  |

# WT-STEEL S 7,9X259 - Cable tie

3240814

<https://www.phoenixcontact.com/gb/products/3240814>



## Technical data

### Product properties

|                      |             |
|----------------------|-------------|
| Product type         | Cable tie   |
| Type                 | Steel strip |
| Tensile strength GRP | 1335 N      |

### Dimensions

|                         |         |
|-------------------------|---------|
| Width                   | 7.9 mm  |
| Length                  | 259 mm  |
| Max. material thickness | 0.25 mm |

### Material specifications

|                |                                 |
|----------------|---------------------------------|
| RoHS compliant | yes                             |
| Color          | silver-colored                  |
| Material       | Stainless steel 1.4301/AISI 304 |
| Components     | free from silicone and halogen  |

### Cable/line

|                         |            |
|-------------------------|------------|
| External cable diameter | ≤ 69.00 mm |
| Tensile strength        | 1335 N     |

### Environmental and real-life conditions

#### Ambient conditions

|                                 |                   |
|---------------------------------|-------------------|
| Ambient temperature (operation) | -80 °C ... 538 °C |
| Ambient temperature (assembly)  | -80 °C ... 538 °C |
| Resistance to UV radiation      | yes               |

### Mounting

|               |                   |
|---------------|-------------------|
| Mounting type | Cannot be removed |
|---------------|-------------------|

# WT-STEEL S 7,9X259 - Cable tie



3240814

<https://www.phoenixcontact.com/gb/products/3240814>

## Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/gb/products/3240814>



**cULus Listed**

Approval ID: E328576

# WT-STEEL S 7,9X259 - Cable tie



3240814

<https://www.phoenixcontact.com/gb/products/3240814>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27140702 |
|-------------|----------|

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC000046 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121700 |
|-------------|----------|

# WT-STEEL S 7,9X259 - Cable tie

3240814

<https://www.phoenixcontact.com/gb/products/3240814>



## Environmental product compliance

### EU RoHS

|                                         |                    |
|-----------------------------------------|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|-----------------------------------------|--------------------|

### China RoHS

|                                        |                                          |
|----------------------------------------|------------------------------------------|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|                                        | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd  
Halesfield 13, Telford  
Shropshire, TF7 4PG  
01952 681700  
[info@phoenixcontact.co.uk](mailto:info@phoenixcontact.co.uk)