

NPR-1000-MT

Line interactive UPS Netys PR MT 1000VA/700W 230V with AVR, 4 IEC sockets



The NETYS PR is the ideal solution for protecting small servers and high performance CAD or graphic workstations

Strong points

- Professional line interactive UPS
- A solution for network power cuts and voltage fluctuations
- Easy to use
- Simplified connection
- Protection for your data line

General characteristics

- Minitower case to easily fit close to the IT load.
- Sine Wave, AVR function (Automatic Voltage Regulation).
- Control panel with LCD display.
- LOCAL VIEW software for local UPS monitoring.
- NTP data line suppressor.
- Up to 6 UPS output sockets.

Compliance with standards

- IEC/EN 62040-1, IEC/EN 62040-2
- AS 62040.1.1, AS 62040.1.2, AS 62040.2
- CE
- RCM (E2376)

Link to the reference



<https://emea.socomec.com/en/reference/NPR-1000-MT>

Classification

UNSPSC	39121011
ETIM Class	EC000382
IGCC	4149

Commerce

Description	NeTYS PR-MT 1000VA/700W 230V 50/60Hz WITH AVR, SINEWAVE,LCD PLUGS PROTECTED RJ45,USB BATTERY INCLUDED
Effective date	2012-09-01
Offer Life Cycle Code	40
Country of origin	CN

ETIM - Electrical characteristics

Input voltage [V]	170..280
Primary frequency [Hz]	45..66
Number of phases primary	1
Output voltage [V]	230..230
Secondary frequency [Hz]	50..60
Output effective power [W]	700
Output apparent power [VA]	1000
Number of phases secondary	1
SNMP	Yes
Voltage type	AC
Output power factor	0.7

ETIM - Mechanical characteristics

Height [mm]	165
Width [mm]	145
Depth [mm]	345
Weight [kg]	9.2
Construction type	Freestanding model
Input connection	C14
Number of output connections C13	4

ETIM - Technical features

USB interface	Yes
Bridging time full load [min]	7.6
Suitable for network-management	Yes
USV- technology	Line-interactive
Overall efficiency [%]	98
Efficiency in eco-mode [%]	98
Potential free switch contact	Yes
Auto shut down function	Yes

Logistics

GTIN/EAN	8027122515245
Customs number	8504409590
Price unit	PC

Weight of the packing unit [kg]	9.2
Length of the packing unit [m]	0.345
Width of the packing unit [m]	0.145
Depth of the packing unit [m]	0.165
Norms	
Conformity to standards	IEC
Technical Characteristics	
Height [mm]	165
Width [mm]	145
Depth [mm]	345
Weight [kg]	9.2
In/out	1/1
Output voltage	230
Rated frequency	50/50
Sn [kVA]	1
Pn [kW]	0.7
Conf	M2
Input voltage	230
Rate (min)	1
Rate (max)	1
Battery Life Time [Year]	03-05
Typical Backup Time [min]	4
Configuration	Line-Interactive UPS with AVR