

Product information

M Class Dust Extractor 30L



Satisfying the professional's needs

VC3012M

Power take off wattage (240V)	1800 W
Dust Bag Capacity	23.5 litres
Max Sealed Suction	23-25 kPa
Tank Capacity	30 litres
Tank capacity Wet	19 litres
Noise sound pressure	59 dB(A)
Max Airflow	3.2 - 3.7 m ³ /min
Input Wattage 110v	1000 w
Input Wattage 240v	1200 w
Net weight	10.0 kg



STANDARD EQUIPMENT: 4.0m x 32mm hose, Adaptor x2, Fleece filter bag, Disposal bag,, Power-tool box, Crevice nozzle

- Push and clean system: takes just seconds to clean the filter.
- Washable PET cartridge filter protects turbine by holding back fine dust and debris.
- Robust plastic container with 2 wheels and 2 castors for excellent stability and mobility
- The motor head design integrates an area for tool storage during use and transportation.
- Innovative hose storage solution with two clamps on the backside of the tool box
- Power cable storage with 3 fixation points on the motor head and tool box
- Floor nozzles and extension tubes can be fixed onto the body for convenient storage
- Automatic On/Off function: machine activates when a connected power tool is used. 240V only
- Lightweight plastic container
- Air flow sensor beeps when air flow is reduced by clogged filter, full tank etc.
- Approved for Dust Classes M in accordance with the EU standard.
- Compact size

Details correct as of: 31-7-2018

Makita reserve the right to change specifications at any time owing to their policy of constant improvement.

Accessories shown are not necessarily supplied.

www.makita.com