

product type designation

Split Connect Terminator (Ex)

PROFIBUS PA SplitConnect Terminator (Ex) for terminating PROFIBUS PA segments, use in hazardous area possible 1 pack=5 units.



transfer rate

transfer rate	
<ul style="list-style-type: none"> with PROFIBUS PA 	31.25 kbit/s

design, dimensions and weights

net weight	600 g
------------	-------

ambient conditions

ambient temperature	
<ul style="list-style-type: none"> during operation during storage during transport 	-40 ... +85 °C

protection class IP	IP67
---------------------	------

product features, product functions, product components / general

product feature	
<ul style="list-style-type: none"> silicon-free 	Yes

further information / internet links

internet link	
<ul style="list-style-type: none"> to web page: selection aid TIA Selection Tool to website: Industrial communication to website: Industry Mall to website: Information and Download Center to website: Image database to website: CAx-Download-Manager to website: Industry Online Support 	http://www.siemens.com/tia-selection-tool http://www.siemens.com/simatic-net https://mall.industry.siemens.com http://www.siemens.com/industry/infocenter http://automation.siemens.com/bilddb http://www.siemens.com/cax https://support.industry.siemens.com

last modified: 11/9/2023 