

911002 AIRFLEX “L” HOSE

A spiral hose with a smooth internal surface. Highly light and flexible and used for suction, fumes, dusts and air-conditioning.



- Working temperature -10 °C to +60 °C
- Light and flexible
- Weight tolerance $\pm 5\%$
- Tolerance on dimensions: ISO 1307

MPN	Internal Dia mm	External Dia mm	Wall Thickness ± 0.2 mm	Bend Radius mm	Spiral Pitch ± 0.5 mm	Weight $\pm 5\%$ g/m	Length m
911002050000	50	57	3.5	50	9.5	450	5
9110020630000	63.5	70	3.5	63.5	10	580	5
9110020750000	75	84	4	75	12	720	5
9110020800000	80	89	4.5	80	12	780	5
91100210092005	100	110	5	100	13.5	1000	5
9110021200000	120	130	5	120	15	1200	5
9110021500000	150	160	5	150	17	1700	5
9110020250000	25	29.6	2.3	25	7.6	150	10
9110020320000	32	37	2.5	32	8.5	230	10
9110020380000	38	43.8	2.9	38	8.8	300	10
9110020500000	50	57	3.5	50	9.5	450	10
9110020630010	63.5	70	3.5	63.5	10	580	10
91100207500010	75	84	4	75	12	720	10
91100208000010	80	89	4.5	80	12	780	10
9110021009200	100	110	5	100	13.5	1000	10
91100212000010	120	130	5	120	15	1200	10
9110215000000	150	160	5	150	17	1700	10