

Features

- Angular Contact Ball Bearing
- Polymer Cage
- Both Sides Sealed
- Rubber Seal on both sides
- 40° Contact angle

RS PRO Ball Bearings

RS Stock No.: 0291577



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

RS PRO double row angular contact ball bearings are highly versatile and robust components designed to handle significant radial and axial loads in various industrial applications. Their compact design, combined load capacity, and durability make them an ideal choice for applications requiring high performance and reliability.

General Specifications

Ball Bearing Type	Double Row Angular Contact Ball Bearing
End Type	Both Sides Sealed
Number of Rows	2
Material	Steel
Ball Material	Steel
Cage Material	Polyamide
Race Material	Steel
Race Type	Plain
Bore Type	Parallel
Seals / Shields	Sealed
Clearance	CN
Bearing Series	3 Medium
Contact Angle	40°

Mechanical Specifications

Inside Diameter (d)	40mm
Outside Diameter (D)	80mm
Race Width (B)	30.2mm
Static Load Rating	34kN
Dynamic Load Rating	47.5kN
Limiting Speed	5600
Weight	0.608 Kg

