

NSG „uClean“ Series
UCLEAN LD-1435 PZ



Noise-insulated cleaning vacuum cleaner of the uClean series with professional equipment. For demanding wet / dry professional cleaning in buildings (industrial, warehouse...), for large area cleaning and machine cleaning. Equipped with PZ accessories , which can be completely stored on the vac. User-friendly due to a large foot switch ON/OFF (gentle start) and parking position for the accessory. The ECO mode is also adjustable by the foot switch, for energy-efficient and quiet operation. Rubber wheels and castors provide extra smooth running and noise reduction. With additional blowing function.



Order no.

017389

Scope of delivery

Accessory set	PZ professional accessories
Additional filter	1 x FSS 1200 (foam material), Art. no. 413297
Filter bag	1 x FBV 25-35, Art. no. 411231 (5 pcs)

Features

Main filter	FPP 3600 (polyester) dust retention capacity 99,9%, Art. no. 415109
Pulse filter cleaning	no
Appliance socket	no
Speed controller	2-level with eco mode
Noise reduction	yes
Blowing function	yes
Carry handle with cable hook	yes
Hose fixing	yes
Hose winding and connector fixture	yes
Park position	yes
Gentle start	yes
After-running	no
Water level detection	yes
Antistatic prepared	no
Push handle	no
Rubber wheels and castors	yes
SmartStop	no
Accessory storage	yes

Technical specifications

Power consumption (max.)	1400 Watt
Volume flow (max.)	69 l/s
Vacuum (max.)	259 mbar
Container volume (max.) Gross-Dust-Water	35/30/23 l

Sound pressure level Schalldruckpegel	68.5 db(A)
Dimensions L/W/H	46 x 44 x 70 cm
Weight	9.9 kg
Power cable length	12,0 (PVC, rot) m
Reach	15,2 - 16,2 m