

**BOSCH**

Invented for life

Product data sheet

Power tools for trade & industry

ANGLE EXACT 12V-6-600

INDUSTRIAL ANGLE EXACT 12V-6-600



Smaller, shorter, lighter – The most ergonomic production screwdriver!

The most important data

Torque (hard)	2 – 6 Nm
Speed	120 – 600 rpm

Part Number 0 602 496 601

Technical data

Technical data

Torque, from (hard)	2 Nm
Torque, to (hard)	6 Nm
Torque (hard)	2 – 6 Nm
Torque, from (soft)	2 Nm
Torque, to (soft)	6 Nm
Torque (soft)	2 – 6 Nm
Speed, from	120 rpm
Speed, up to	600 rpm
Speed	120 – 600 rpm
Direction of rotation	R/L
Weight	1 kg
Comment	No load speed with Power Boost up to 800 rpm Below 50% speed setting eventually lower power Machine capability testing is done at 600 rpm according to VDI 2647. Changes to the tool speed and torque may also affect accuracy. Please verify machine capability at your specific setting.

Battery	GBA 12V
Drive type	Battery
Design	Angle
Connector type	Shut-off clutch

Noise/vibration information

Screwdriving

Vibration emission value ah	2.5 m/s ²
Uncertainty K	1.5 m/s ²

Product data sheet

Power tools for trade & industry



BOSCH
Invented for life



You can find more information about the deviations in the following link: <https://www.bosch-professional.com/gb/en/wac/>

