

Eaton 24TXMEJ160

Catalog Number: 24TXMEJ160

Eaton Bussmann series medium voltage DIN fuse, 160 A, AC 24 kV, 3.5", 88 x 442 mm, backup, DIN, with striker

General specifications



Product Name	Catalog Number
Eaton Bussmann series medium voltage DIN fuse	24TXMEJ160
	EAN
	5027590225762
UPC	Product Length/Depth
051712186391	442 mm
Product Height	Product Width
88 mm	88 mm
Product Weight	Compliances
5855 g	DIN 43625
	VDE 0670-4
	IEC 60282-1
Certifications	
UL	
VDE	

Product specifications

Type

Fuse

Special features

Back-up, Transformer protection, Indoor or outdoor use

Application

transformer protection

indoor or outdoor use

Amperage Rating

160 A

Fuse indicator

With Striker

Breaking capacity

31.5 kA

Installation technique

Air

Performance Cat According To IEC 60282-1

Back-up

Product application

Primary side transformer protection

Rated frequency - max

50 Hz

Rated frequency - min

50 Hz

Release characteristic

Other

Standard

DIN

Utilization category

Other

Voltage type

AC

With striker

Yes

Class

Class back-up

Resources

Technical data sheets

[720106 24kV DIN medium voltage fuses](#)

[720104 12kV DIN medium voltage fuses](#)

[720105 17.5kV DIN medium voltage fuses](#)

Barrels

1

Construction type

Bolt-on

Pre arc (I2T)

1.3 x 105

Resistance

9.6 Ohms

Watt losses

515 W

Fuse diameter

76 mm

Color

Brown

Interrupt rating

31.5 kAIC

Construction size

88 x 442 mm

Mounting method

Clip-in

Packaging type

Standard

Quantity

1

Voltage rating

24 kV

Fuse type

TXMEJ



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are
property of their respective
owners.



Eaton.com/socialmedia