

900L
chiavi a bussola con attacco quadro femmina 1/4", tipo lungo bocca esagonale, cromate


UNI/ISO 2725 DIN 3124


art.	mm	Ø mm	L mm	Ø1 mm	A mm	g
009000181	4	6,5	50	12,0	5,0	23
009000182	4,5	7,0	50	12,0	5,0	24
009000183	5	7,5	50	12,0	5,0	24
009000184	5,5	8,5	50	12,0	6,0	21
009000185	6	9,5	50	12,0	7,0	25
009000186	7	10,5	50	12,0	7,0	24
009000187	8	12,0	50	12,0	8,0	24
009000188	9	13,0	50	13,0	9,0	27
009000189	10	14,0	50	14,0	10,0	36
009000190	11	16,0	50	16,0	11,0	50
009000191	12	17,5	50	17,5	13,0	52
009000192	13	17,5	50	17,5	13,0	67
009000193	14	20,0	50	20,0	13,0	81

