

PVC SET HOSE EXTENSION

DIFLEX PVC hose extension with PREVOS1 safety quick couplers



Part number	Length (m)	Temperature min/max (°C)	Max. operating pressure (bar)	Net weight (Kg)	Profile
RAL DISB810	10.00	-15.00 / 60.00	12.00	1,4	ISO 6150B

Part number	Ø int/ext (mm)
RAL DISB810	8.00 / 14.00