



Main

| | |
|------------------------------------|----------------------|
| Range | Acti 9 |
| Product or component type | Comb busbar |
| Accessory / separate part category | Connection accessory |
| Lines description | 1L + N |
| Total number of 18 mm modules | 24 |

Complementary

| | |
|--------------------------------|--|
| Number of ways | 12 ways N + 1 L |
| Poles configuration for 1 way | 1 x 1P + N 1 x 2P |
| Connection pitch | 18 mm |
| Connector type | Tooth |
| Distance between way | 36 mm |
| Marking | N L |
| Insulation | Insulated |
| Device presentation | Cuttable |
| [Ie] rated operational current | 100 A (40 °C) |
| [Ue] rated operational voltage | 415 V AC |
| [Ui] rated insulation voltage | 500 V AC conforming to IEC 61439-2 |
| Mounting mode | Horizontal |
| Mounting location | Top or bottom on tunnel type terminals Top or bottom on double terminal |
| 9 mm pitches | 48 |
| Width | 430 mm |
| Colour | White (RAL 9003) |
| Range compatibility | Multi 9 C60 Acti 9 iK60 Acti 9 iC60 Acti 9 iID |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Environment

| | |
|-------------------------|---|
| Standards | IEC 61439-2 IEC 60947-7-1 |
| Fire resistance | 960 °C (30 s) conforming to IEC 60695-2-1 |
| Pollution degree | 3 conforming to IEC 60947-7-1 |
| IP degree of protection | IP20 with end-pieces and tooth covers |

Offer Sustainability

| | |
|----------------------------------|---|
| Sustainable offer status | Green Premium product |
| RoHS (date code: YYWW) | Compliant - since 1336 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity |
| REACH | Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold |
| Product environmental profile | Available |
| Product end of life instructions | Need no specific recycling operations |

Contractual warranty

| | |
|-----------------|-----------|
| Warranty period | 18 months |
|-----------------|-----------|