



Specification

CP301 110V 16A CT Industrial Check Plug



Electrical

Operating voltage range: 110V AC rms
(55V-0-55V centre tapped only)
Frequency response: 30Hz to 70Hz
Power consumption: <0.9W
Power: from mains socket under test

General

Plug type: yellow, 16A/32A, 3-pin plug to BS
EN 60309 (BS 4343)
Dimensions: 65 x 65 x 47mm (check plug
body)
Weight: approx. 195g

Environmental

Temperature (Operating & Storage): -10°C to 40°C, at max. 60% RH
Altitude: up to 2000m
Pollution degree 2

Safety

Conforms to BS EN 61010-1, CAT II 150V
Class II, double insulation

EMC

Conforms to BS EN 61326-1

Check out what else you can get from Martindale:

- 17th Edition Testers
- Accessories
- Calibration Equipment
- Continuity Testers
- Electricians' Kits
- Environmental Products
- Full Calibration & Repair Service
- Fuse Finders
- Digital Clamp Meters
- Digital Multimeters
- Labels
- Microwave Leakage Detectors
- Motor Maintenance Equipment
- Multifunction Testers
- Non-trip Loop Testers
- Pat Testers & Accessories
- Phase Rotation Testers
- Proving Units
- Socket Testers
- Thermometers & Probes
- Test Leads
- Voltage Indicators
- Specialist Metrohm Testers (4 & 5kV)
- Specialist Drummond Testers



Martindale Electric Company Limited
Metrohm House, Penfold Trading Estate, Imperial Way, Watford WD24 4YY, UK
Tel: +44 (0)1923 441717 Fax: +44 (0)1923 446900
E-mail: sales@martindale-electric.co.uk
Website: www.martindale-electric.co.uk



© 2016 Martindale Electric Company Ltd.
Registered in England No. 3387451. Rev 3 LITCP301