

High Speed HDMI Cable M/M - 4K @ 30Hz - No Signal Booster Required - 15 m

Product ID: HDMM15M



This HDMI cable lets you connect your Ultra HD devices at distances of up to 15 meters, with no external power or active circuitry.

The cable fully supports 1080p+ resolutions at up to 120Hz refresh rate, with life-like color. To accommodate the demands of future high-definition devices, such as increased resolutions and higher frame rates, this Ultra HD cable supports resolutions up to 4K x 2K.

The cable combines crystal-clear image resolutions with high-bandwidth video and multi-channel digital audio into a single cable.

The HDMM15M from StarTech.com is backed by a lifetime warranty for guaranteed reliability.

Certifications, Reports and Compatibility



Applications

- Connect high-definition A/V devices such as streaming media players, Blu-Ray Disc™ players, HDTVs, DVD Players, DVRs, game consoles, projectors etc.

Features

- Supports Ultra HD Resolutions up to 3840x2160 (4K x 2K)
- Provides connection distances up to 15 meters away
- Guaranteed reliability with our lifetime warranty

Hardware	Warranty	Lifetime
	Cable Jacket Type	PVC - Polyvinyl Chloride
	Cable Shield Type	Aluminum-Mylar Foil with Braid
	Connector Plating	Gold
Performance	Maximum Digital Resolutions	4K x 2K @ 30 Hz
Connector(s)	Connector A	1 - HDMI (19 pin) Male
	Connector B	1 - HDMI (19 pin) Male
Physical Characteristics	Cable Length	15 m [49.2 ft]
	Color	Black
	Connector Style	Straight
	Product Height	10.700
	Product Length	15 m [49.2 ft]
	Product Weight	1849.7 g [65.3 oz]
	Product Width	20.000
	Wire Gauge	24 AWG
Packaging Information	Package Quantity	1
	Shipping (Package) Weight	1.9 kg [4.2 lb]
What's in the Box	Included in Package	1 - 15 m High Speed HDMI® Cable - HDMI - M/M

Product appearance and specifications are subject to change without notice.