



## DWE4057

### 800W 125mm Slide Switch SAG No-Volt

#### Selling Proposition

- Small girth allows comfortable gripping resulting in superior ergonomics
- No-volt release switch prevents the unit from starting unintentionally when locked on. Switch must be consciously reset before power is delivered
- Independent box and spring brush holder design increases brush life
- Soft start reduces movement of the tool on startup increasing user control
- The low profile gear case allows access in confined areas
- Fully leaded stator windings for increased motor durability

#### Standard Equipment

- Protective guard
- Multi-position side handle
- Inner and outer disc flange
- Spanner

#### Warranty Specifications

- DEWALT 3 year European PT Guarantee (subject to registration)

| Specifications                |                      |
|-------------------------------|----------------------|
| Power Input                   | 800 Watts            |
| No Load Speed                 | 11800 rpm            |
| Max. Disc Diameter            | 125 mm               |
| Spindle Thread                | M14                  |
| Weight                        | 1.8 kg               |
| Length                        | 270 mm               |
| Height                        | 80 mm                |
| Hand/Arm Vibration - Grinding | 9.4 m/s <sup>2</sup> |