

Linetrimmer XGT®

UR003G

40V max • 0 - 3 500 / 5 300 / 6 500 min⁻¹

Highly efficient cordless Grass Trimmer XGT®. With a loop handle.

UR003G is made for demanding use. Equipped with an automatic speed control for adjusting speed in line with load. Low vibration and noise levels and good ergonomics ensure a good user experience.



XGT **BL** **ADT** **AFT**
MOTOR

Technical specifications

Voltage XGT	✓
Nominal Battery Voltage	40 V
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
No load speed	0 - 3500 / 5300 / 6500 min ⁻¹
Cutting width	230 / 255 / 350 mm
Spindle Thread	M10 x 1,25 LH
Handle Type	L
Sound Power Level (L _{WA})	85,3 - 89,7 dB(A)
Sound Pressure Level (L _{pA})	72,2 - 74,4 dB(A)
Noise Uncertainty (K Factor)	0,3 - 2,2 dB(A)
Product net weight	3,4 kg
Tool weight with battery	4,1 - 5,3 kg
Product Dimensions (L x W x H):	1760 x 355 x 230 mm
Nylon line- Diameter	2,0 mm

User benefits

- Brushless maintenance-free and long-life motor
- ADT (Automatic torque Drive Technology) adjusts speed and torque during operation for optimum performance
- Active Feedback sensing Technology (AFT) stops the engine if the rotation suddenly stops
- eXtreme Protection Technology (XPT) is engineered for improved dust and water resistance for operation in harsh conditions
- Battery protection circuit protects against overloading, over-discharging and over-heating

Link to product - www.makitauk.com



Related products

Optional AC

127508-0

Band Assembly



198383-1

Plastic Blade set, 255 mm



198893-8

Trimmer Head 2,0 mm, M10 x 1.25



783013-3

Box Driver 16 - 17 Mm



783202-0

Hex Wrench 4Mm



831304-7

Accessory Bag



D-66008

4-Tooth Blade, 230 x 25,4 mm



Other

User manual

Parts drawing