

FEATURES

- Large and quick opening
- Handle Locks in both forward and reverse position
- Stainless steel rivets
- The clamps are self-arresting, they remain locked, resisting the force produced when machining components
- Heavy duty with 1200kg holding force
- Malleable iron construction

RS PRO 50mm Toggle Clamp

RS Stock No.: 254-939



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

This Push Pull Toggle Clamp from our own RS PRO brand offers the advantage of having a low profile, using side or end clamping and are most suitable for applications having a height restriction. With large power transmission and minimum operating effort, this toggle clamp gives you maximum clamping force to help you out in any job.

General Specifications

Type	Toggle Clamp
Application	Metalworking industry, wood and plastic industry

Mechanical Specifications

Jaw Opening	50mm
Nominal holding force	1200Kg

Approvals

Compliance/Certifications	EN61340
----------------------------------	---------





Dimensions:

