



ENGLISH

Datasheet

Stock No: 211-711

RS Pro Swivel Plate Castor



Product Details

Pneumatic Tyre Castors

Robust castors with roller bearings for smooth running and shock resistance

Pressed steel centre

Rubber tyre

Wide tread makes them suitable for soft surfaces

Soft Tread - Pneumatic Tyre

Soft tread wheels are kinder to floors and quieter in use but are not quite so easy to move from a standing start. For light, medium and heavy duty loads, soft tread wheels offer many benefits. Softer tread tyres are also particularly suitable for power towing applications. For very high load manual handling applications, soft tread wheels should be ruled out as, although they may be capable of carrying a very high load, the force required to move equipment from a standstill would require the efforts of several men.



Specifications:

Wheel Diameter	200mm
Load Capacity	75kg
Overall Height	240mm
Wheel Width	50mm
Fixing Plate Dimensions	135 x 110mm
Rotation	Swivel
Tyre Material	Rubber
Fixing Centres	105 x 80mm
Features	Shock Absorbing, Smooth Running
Number of Fixing Holes	4
Fixing Hole Size	11mm
Hub Material	Steel
Hub Bearing Type	Roller Bearing
Fixing Centres Length	105mm
Fixing Plate Width	110mm
Fixing Plate Length	135mm
Fixing Centres Width	80mm