



## KR DIN 16-12

E0812797

Cable Lug KR DIN, 16mm<sup>2</sup>, M12



### Product Properties:

Suitable for Class 2 conductor	Yes
Suitable for Class 5 conductor	Yes
Insulated	No
Number of mounting holes	1 .
Flange shape	Ring shape
Colour insulation	Other
Slender flange model	No
With sight-hole	No
Conductor category	Several
Surface protection	Tinned
Material	Copper
Connecting angle	180° (horizontal)

### Dimensions:

HS	13 mm
ID	5.5 mm
OD	8.5 mm
T	1.9 mm
P1	14 mm
P2	14 mm
L	51 mm
N	20 mm

<b>W</b>	17 mm
<b>MOQ</b>	100 .
<b>Unit</b>	pcs
<b>Bolt dimension (metric)</b>	12 .
<b>Nominal cross section</b>	16 mm <sup>2</sup>

### **Approvals:**

<b>Approved according to CE</b>	Yes
<b>Approved according to UKCA</b>	Ja

### **Compliance:**

<b>Conflict Minerals</b>	Contain "Tin"
<b>Extended Minerals</b>	Contain "Copper"
<b>PFAS</b>	No PFAS
<b>REACH</b>	No SVHC (Latest. 05 Nov 2025)
<b>RoHS</b>	RoHS 3 (2015/863)
<b>SCIP</b>	Not Applicable

### **Other information:**

<b>ETIM-Class</b>	EC001051 - Tube cable lug for copper conductors
<b>ETIM-Release</b>	9.0
<b>Trademark</b>	NEMIQ
<b>Product Group</b>	Cable lugs
<b>Search Description</b>	SKH2023ERIK2, ENR2025V, NYB04
<b>Alternative SKU</b>	KRDIN16-12
<b>E-no</b>	E0812797

### **Logistic information:**

<b>Barcode</b>	733117641264
<b>Country of origin</b>	CN
<b>E-no</b>	E0812797
<b>Item status</b>	Stock item, normally in stock with reservation for in between sales.
<b>MOQ</b>	100 .
<b>Stock code</b>	KRDIN 16-12
<b>Taric code</b>	85369010
<b>Unit</b>	pcs

\*We reserve the right to make technical changes and disclaim any typographical errors.