

1760PT/N

Voltage and continuity tester, 1000 V

CE


Up to 1000V power.

Equipped with a high-visibility digital screen and a convenient self-test function, the tool ensures both accuracy and reliability in each measurement.

 312 g

Features:

- Voltage: 24÷1000VAC / 6÷1000VDC
- Bar voltage indicator: 6-12-24-50-120-230-400-690-1000
- Accuracy: $\pm (3\% + 3)V$
- Response time: $< 1s (09\%)$
- Maximum absorbed current @1000V: $< 3,5mA$
- Contact-free voltage detection: $> 90VAC$
- Phase rotation test: 100÷1000VAC (50/60Hz)
- Phase angle: $120^\circ \pm 5^\circ$
- Continuity test: $0 \pm 1.3 M\Omega$
- Current (continuity test): $\leq 5 \mu A$
- Pollution level:
- Power supply:

	art.	H mm	L mm	P mm	L1 mm
017600155	1760PT/N	250	70	30	850

