

MSA V-TEC® PFLs

Technical Data Sheet



Product Specifications

HOUSING MATERIAL	Polycarbonate
HARDWARE MATERIALS	Steel or Aluminum
LIFELINE MATERIAL	
6 ft. (1.8 m)	17 mm (2/3 in) wide / 1.4 mm (0.06 in) thick HMPE
10 ft. (3 m)	19 mm (3/4 in) wide / 1.75 mm (0.07 in) thick HMPE
WEIGHT	See tables
UNIT LENGTH	
6 ft. (1.8 m)	647.2 – 747.3 mm
10 ft. (3 m)	653.8 – 753.9 mm
UNIT WIDTH	
6 ft. (1.8 m)	76.2 mm
10 ft. (3 m)	88.9 mm
UNIT DEPTH	56.70 mm
ENERGY ABSORBING TECHNOLOGY	1200 mm (47 in) Tear Tape
CAPACITY	35 - 140 kg (77-310 lb)
APPROVALS	
6 ft. (1.8 m)	EN 360, DIN 19427
10 ft. (3 m)	EN 360



6 ft. (1.8 m)

10 ft. (3 m)

Specifications & Ordering Information

V-TEC 1.8 m (6 ft) Mini Web PFL			V-TEC 3 m (10 ft) Web PFL		
Part Number	Snaphook	Item Weight	Part Number	Snaphook	Item Weight
VTOHW-011-DH-E	AL36CLS	1.33 kg	VTOHW-031-DH-E	AL36CLS	1.58 kg
VTOHW-011-DM-E	36CLS	1.45 kg	VTOHW-031-DM-E	36CLS	1.71 kg
VTOHW-011-DE-E	36CS	1.31 kg	VTOHW-031-DE-E	36CS	1.52 kg
VTOHW-011-DC-E	ALTAKS	1.02 kg	VTOHW-031-DC-E	ALTAKS	1.27 kg

Snap Hooks & Top Connectors

AL36CLS Aluminum 60 mm Gate	36CLS Steel 50 mm Gate	36CS Steel 21 mm Gate	ALTAKS Aluminium Triple lock 19 mm Gate	Top Carabiner Aluminium Triple lock 20mm Gate

Note: This Bulletin contains only a general description of the products shown. While product uses and performance capabilities are generally described, the products shall not, under any circumstances, be used by untrained or unqualified individuals. The products shall not be used until the product instructions/user manual, which contains detailed information concerning the proper use and care of the products, including any warnings or cautions, have been thoroughly read and understood. Specifications are subject to change without prior notice. MSA is a registered trademark of MSA Technology, LLC in the US, Europe, and other Countries. For all other trademarks visit <https://us.msasafety.com/Trademarks>.

MSA operates in over 40 countries worldwide. To find an MSA office near you, please visit [MSAsafety.com/offices](https://www.msasafety.com/offices).