



Heat



Welding



Heavy Duty

Heavy-duty TIG welding gloves, combining thermal hand protection with dexterous tactility

- **Specialized protection:** ActivArm® 43-217 work gloves satisfy EN 12477 Type B standards, ensuring effective protection from heat, flames, sparks and weld spatter and making them ideal for welding and thermal applications, as well as grinding, brazing, metal fabrication and maintenance
- **Enhanced features:** Their long-split cowhide cuff offers additional forearm and wrist protection, while a three-dimensional thumb design grants wearers greater dexterity, for safer, more precise welding gloves
- **Improved durability:** ActivArm® 43-217 safety gloves' premium full-grain goatskin, welted seams and para-aramid thread also enhance their durability and wear life



Industries

- Machinery and Equipment
- Automotive
- Oil and gas
- Utilities

Applications

- Grinding
- Welding
- Brazing
- Metal Fabrication
- Maintenance
- Welding, bonding, riveting
- Equipment repair & maintenance
- Metalworking & assembly operations

Key Features

- **EN 12477 Type B compliance:** Superb welding* and thermal** capabilities
- **Three-dimensional thumb design:** For highly precise welding gloves
- **Premium full-grain goatskin and welted seams:** Heightened durability
*suitable for TIG welding, as well as grinding, brazing, metal fabrication and maintenance
**protection from heat, flames, sparks and weld spatter

Performance Standards & Regulatory Compliance

ANSI/ISEA 105-2024



0493



EN388: 2016



2111A

EN 407



41XX4X

Specifications

BRAND STYLE	DESCRIPTION	Gauge	SIZE	LENGTH	COATING COLOR	PACKAGE
ActivArm® 43-217	Coating Material: Goatskin Cuff Style: Gauntlet	N/A	9, 10	340mm, 350mm, 360mm	White	6 pairs/bag, 6 bags/carton

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 900
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Canada

Ansell Canada
105 Lauder
Cowansville, QC J2K 2K8
Canada
T: +1 800 363 8340
F: +1 800 267 3551

Australia

Ansell Limited
Level 3,678 Victoria Street,
Richmond, Vic, 3121
Australia
T: +61 1800 337 041
F: +61 1800 803 578

Asia Pacific Region

Ansell Global Trading Center
(Malaysia) Sdn Bhd
Prima 6, Prima Avenue
Block 3512, Jalan Teknokrat 6
T: +603 8310 6688
F: +603 8310 6699